

Eaton EMA107-10

Catalog Number: EMA107-10

Eaton Managed rack PDU, 0U, L6-30P input, 5.76 kW max, 200-240V, 24A, 10 ft cord, Single-phase, TAA compliant

General specifications

| | |
|-------------------|----------------------|
| Product Name | Catalog Number |
| Eaton managed PDU | EMA107-10 |
| UPC | Product Length/Depth |
| 743172069184 | 2 in |
| Product Height | Product Width |
| 66.5 in | 2.1 in |
| Product Weight | Warranty |
| 17.3 lb | 3 year |
| Compliances | Certifications |
| TAA Compliant | UL Listed |



Product specifications

Form factor

0U (Vertical)

Outlet control

Yes

Phase

Single-phase

Wattage

5.76 kW max

Amperage Rating

24A

Input voltage

200-240V

Input connection

L6-30P

Outlets

(20) C13 Outlet grip, (4) C19 Outlet grip

Cord length

10 ft

Frequency rating

50-60 Hz

Serial interface

RS-232

Operating Temperature

0° to 60°C (32° to 140°F)

Resources

Certification reports

[Eaton ePDU certificate of volatility](#)

[Eaton RoHS Declaration of Conformity: ePDU G3](#)

Drawings

[Eaton ePDU Managed EMA107-10 technical drawing](#)

[Eaton Advanced Monitored and Managed ePDU visio stencil](#)

Manuals and user guides

[Eaton ePDU G3 replace and configure eNMC module](#)

[Eaton ePDU G3 1U and 2U installation addendum](#)

[Eaton Double-wide G3 ePDU installation and connectivity quick start guide](#)

[Eaton ePDU G3 operations manual](#)

[Eaton ePDU G3 instruction set - system objects](#)

Service and troubleshooting

[EMA107-10 eNMC replacement configuration file](#)