



## Novanex Model ONT4BK-P-G

### Power-over-Ethernet (PoE) Digital Clock Black ABS Injection Molded Plastic Case

#### Specifications

DIMENSIONS	CASE: 12" (30cm) width; 6" (15cm) height; 2.28" (5.8cm) depth LEDs: 4 inch (10.2cm) height, seven segment green LEDs
WEIGHT	1.6 lb (.07kg)
FEATURES	12/24 hour display; service light indicator, auto DST adjustment, DHCP or Static IP addressable, monitoring system available; colon display on/off
TIME SYNCHRONIZATION	SNTP (Simple Network Time Protocol); time server configurable
VIEWING DISTANCE	150+ feet (50+ meters)
OPERATING ENVIRONMENT	32-104 degrees F (0-40 C) 95% max humidity, non-condensing
ACCURACY	Within + / - 200ms
POWER CONSUMPTION	8 watts
TECHNICAL STANDARDS	UL 62638-1:2019 Ed.3; CSA C22.2#62638-1:2019 Ed.3 IEEE 802.3af-2003; IEEE 802.3 at (PoE+) 2009; IP65; ETL listed, CE marked
SUPPORT	<a href="https://support.novanexsolutions.com">https://support.novanexsolutions.com</a>
WARRANTY	5 years
COUNTRY OF ORIGIN	USA