

Product data sheet

Specifications



APC NetShelter 24U Wallmount Rack Enclosure Cabinet Side Mount UPS Depth

AR124SM

Overview

Lead time	Usually Ships within 2 Weeks
-----------	------------------------------

Main

Product or Component Type	Rack enclosure
Number of rack unit	24U

Physical

Height	45.5 in (1156 mm)
Width	23.6 in (600 mm)
Depth	40.8 in (1037 mm)
Net Weight	176.4 lb(US) (80 kg)
Mounting preference	No preference
Material	Steel
Maximum Mounting Depth	32.9 in (835 mm)
Minimum Mounting Depth	7.5 in (190 mm)
Rack Width	19"
Permanent permissible load	348.3 lb(US) (158 kg)

Conformance

Product Certifications	UL/cUL listed
Marking	CULus
Standards	UL 2416

Ordering and shipping details

GTIN	731304632665
Country of origin	TH

Packing Units

Unit Type of Package 1	PCE
Nbr. of units in pkg.	1
Package 1 Height	52.4 in (133 cm)
Package 1 Width	52.0 in (132 cm)
Package 1 Length	33.5 in (85 cm)

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Package weight(Lbs)	246.9 lb(US) (112 kg)
---------------------	-----------------------

Contractual warranty

Warranty	5 years
----------	---------

Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained](#) >

Use Better

 Materials and Substances	
Packaging made with recycled cardboard	No
Packaging without single use plastic	No
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)
REACH Regulation	REACH Declaration

Use Again

 Repack and remanufacture	
Take-back	No

Image of product / Alternate images

Alternative



