



Part Number: CAT5E UTP CMP PATCH CORDS

CAT5E UTP CMP Patch Cords

Product Description

CAT5E UTP CMP Patch Cords

Technical Specifications

Product Overview

Environmental Space:	Plenum
Suitable Applications:	IBDN System 1200, TIA Category 5E, ISO Class D, 1000BASE-T, 100BASE-T

Physical Characteristics (Overall)

Total Number of Pairs:	4
Conductor Size:	24 AWG
Overall Nominal Diameter:	0.22 in
Wiring Scheme:	T568A/B-T568A/B
Packaging:	Individually packaged in a clear plastic bag.

Connectors

Materials

Description	Material	Color
Boot	Elastomer	Translucent
Conductor	BC - Bare Copper	
Front Connection	Blades Phosphor Bronze with 50u inch Gold over Nickel Plating	
Inner Jacket	PVC - Polyvinyl Chloride	
Insulation	PO - Polyolefin	
Outer Jacket	PVC - Polyvinyl Chloride	

Electrical Characteristics

Dielectric Strength:	1,000 V RMS @ 60 Hz for 1 minute
Current Rating:	1.500 A
Insulation Resistance:	500 M-Ohm Minimum
Max Contact Resistance:	20 mOhm

Temperature Range

Installation Temp Range:	-10°C To +60°C
Storage Temp Range:	-40°C To +70°C
Operating Temp Range:	-10°C To +60°C

Mechanical Characteristics

Min Bend Radius (Overall Cable):	1.040 in
Plug /Jack Compatibility:	RJ45

Termination Interface

Connection	Durabilities
Mated Connection	750 Cycles

Standards

UL Rating:	Riser
Data Category:	Category 5e
Telecommunications Standards:	Category 5E - TIA 568-C.2, Class D - ISO/IEC 11801:2002 Ed.2 Amendment 2
Other Standards:	FCC Part 68, Subpart F, IEC 60603-7

Applicable Environmental and Other Programs

EU Directive 2002/95/EC (RoHS):	Yes
EU RoHS Compliance Date (yyyy-mm-dd):	2006-01-01
MII Order #39 (China RoHS):	EUP 50

Flammability, LS0H, Toxicity Testing

Safety Listing:	c(UL)us Listed
-----------------	----------------

Part Number

Related Parts:	CAT5E Modular Jacks and Couplers, CAT5E Patch Panels
----------------	--

Variants

Item #	Color	Length
C502100102	Black	102 ft
C502100092	Black	92 ft
C502100085	Black	85 ft
C502100082	Black	82 ft
C502100079	Black	79 ft
C502100072	Black	72 ft
C502100069	Black	69 ft
C502100066	Black	66 ft
C502100062	Black	62 ft
C502100059	Black	59 ft
C502100056	Black	56 ft
C502100052	Black	52 ft
C502100049	Black	49 ft
C502100046	Black	46 ft
C502100043	Black	43 ft
C502100040	Black	40 ft
C502100036	Black	36 ft
C502100033	Black	33 ft
C502100030	Black	30 ft
C502106080	Blue	80 ft
C502106075	Blue	75 ft
C502106090	Blue	90 ft
C502106030	Blue	30 ft
C502106005	Blue	5 ft
C502106006	Blue	6 ft
C502106050	Blue	50 ft
C502106025	Blue	25 ft
C502106020	Blue	20 ft
C502106015	Blue	15 ft
C502106012	Blue	12 ft
C502106010	Blue	10 ft
C502106007	Blue	7 ft
C502106004	Blue	4 ft
C502106002	Blue	2 ft
C502108066	Gray	66 ft
C502108050	Gray	50 ft
C502108035	Gray	35 ft
C502108025	Gray	25 ft
C502108010	Gray	10 ft
C502108007	Gray	7 ft
C502108005	Gray	5 ft

C502108004	Gray	4 ft
C502105080	Green	80 ft
C502105075	Green	75 ft
C502105070	Green	70 ft
C502105050	Green	50 ft
C502105150	Green	150 ft
C502105100	Green	100 ft
C502103020	Orange	20 ft
C502103015	Orange	15 ft
C502103010	Orange	10 ft
C502107025	Purple	25 ft
C502116050	TIA Blue	50 ft
C502116025	TIA Blue	25 ft
C502109050	White	50 ft
C502109025	White	25 ft
C502109020	White	20 ft
C502109015	White	15 ft
C502109012	White	12 ft
C502109010	White	10 ft
C502109007	White	7 ft
C502109004	White	4 ft
C502109003	White	3 ft
C502104035	Yellow	35 ft

Product Notes

Labeling:	Belden Part Number, Performance Acronym, Wiring Scheme and Cord Length.
-----------	---

© 2019 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.