



Part Number: REVConnect Dust Caps for Jacks

REVConnect Dust Cover Caps for Jacks

Product Description

REVConnect Dust Caps for Jacks are available in several colors in a bulk pack of 24.

Technical Specifications

Product Overview

Environmental Space:	Indoor
----------------------	--------

Physical Characteristics (Overall)

Height:	0.634 m
Width:	0.571
Depth:	0.181
Packaging:	24 covers bulk packaged in a cardboard box.
Weight:	0.001 lbs

Connectors

Materials

Material
Plastic - UL94V-0

Temperature Range

Installation Temp Range:	-10°C To +60°C
Storage Temp Range:	-40°C To +70°C
Operating Temp Range:	-10°C To +60°C

Mechanical Characteristics

Footprint/Type:	KeyConnect
-----------------	------------

Standards

Data Category:	N/A
----------------	-----

Applicable Environmental and Other Programs

EU Directive 2002/95/EC (RoHS):	Yes
EU RoHS Compliance Date (yyyy-mm-dd):	2006-07-01
MII Order #39 (China RoHS):	EUP 50

Part Number

Related Parts:	Compatible with Belden's REVConnect jacks
----------------	---

Variants

Item #	Color
RVUDCAL-B24	Almond
RVUDCBK-B24	Black
RVUDCBL-B24	Blue

RVUDCBR-B24	Brown
RVUDCGY-B24	Gray
RVUDCGN-B24	Green
RVUDCIV-B24	Ivory
RVUDCOR-B24	Orange
RVUDCPR-B24	Purple
RVUDCRD-B24	Red
RVUDCTB-B24	TIA Blue
RVUDCTN-B24	TIA Brown
RVUDCTG-B24	TIA Green
RVUDCTO-B24	TIA Orange
RVUDCTP-B24	TIA Purple
RVUDCTR-B24	TIA Red
RVUDCTY-B24	TIA Yellow
RVUDCEW-B24	White
RVUDCYL-B24	Yellow

© 2019 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.