



3600U

Electromagnetic Locks



3600U Electromagnetic Locks

Schlage introduces the integrators an answer to the practical needs for electromagnetic locks. These compact electromagnetic locks are easy to stock, easy to select and easy to install. Schlage 3600U with 1200 lbs of holding force.

The Variety and flexibility of Schlage 3600U family electromagnetic locks can meet your demands for high security, traffic control, or narrow line applications throughout your facility.

All models are ideal for open architecture and easily interface with electronic access control systems, automatic door operators, and fire or other hazard sensing systems for egress and emergency egress.

Benefits of using 3600U Electromagnetic Locks

- Field Selectable 12 or 24 VDC operation
- Simplified armature installation
- Variety of installation brackets available to adapt All kinds of environment
- Single magnet available with 3600U Series
- UL294 and UL10C certification
- 500,000 Times life-cycle

3600U Electromagnetic Locks

How to order 3600U

3600U

Select model

1. Select Model

3600U High security, single lock

Specifications

3600U

Holding force	1200lbs.
Input voltage	12/24VDC field selectable
Current draw	0.5A@12VDC; 0.25A@24VDC.
Dimension	Lock body 268x73x40mm Armature plate 185x61x16mm Armature plate W/ DSM 252x61x16mm
Weight	10.75lbs.

About Allegion

Allegion(NYSE: ALLE) is a global pioneer in seamless access, with leading brands like CISA®, Interflex®, LCN®, Schlage®, SimonsVoss® and Von Duprin®. Focusing on security around the door and adjacent areas, Allegion secures people and assets with a range of solutions for homes, businesses, schools and institutions. Allegion had \$2.7 billion in revenue in 2018, and sells products in almost 130 countries. For more, visit www.allegion.com/mea

