



Flexible Conduits & Fittings

T&B Catalog Number:

BVIRB-U202

UPC Number:

78620995031

Status:

Active

Description:

PMAFIX black female thread adapter with UNEF threads. Material - polyamide 6, thread size - 13/16 in. - 20, nominal width/conduit size - 12.

Application

For use in machine, vehicle and traction building

Characteristics

Very high impact resistance

Vibration proof connection to PMAFLEX conduits

High conduit pull-out strength

Very good chemical properties

Free from halogens and cadmium

Fits both conduit profiles - Fine (T) and coarse (G)

General

Material Polyamide 6

Color Black

Thread Type UNEF

Compatible With PMAFLEX/ Souriau connector series UTG-6 / ITT Cannon Trident

Dimension Information

Fits to Conduit Size (NW) 12

Fits to Conduit Size (metric) 16

Fits to Conduit Size (inches) 3/8

Thread Size (UNEF) 13/16" - 20

Technical Information

Temperature Range-Continuous (Celsius) -40 degree C to +105 degree C

Temperature-Short-Term (Celsius) +160 degree C

Technical Data Sheet Available on Website

Chemical Resistance Chart Available on Website

Specifications

3dmodel Available on Website

IP Ratings

IP Rating IP 68 stat. / IP 67 dyn. On conduit side

Packaging

T&B Inner Pack 50

Package in Units 400

T&B Sold in UOM Each

T&B Weight Per UOM 0.27 lbs. Each

Application Support

PMA Reference Guide Available on Website

Product Overview-PMAFIX Connectors Available on Website

PMAFIX Connectors-Safety and Sealing Systems Available on Website

Systems

Certifications

RoHS Compliance Yes

Certifications



For further technical assistance, please contact us...

Thomas & Betts - USA
8155 T&B Blvd.
Memphis, TN 38125
www.tnb.com

T&B Technical Support
MS 3B-50
8155 T&B Blvd.
Memphis, TN 38125

Hours: 7AM - 6PM CDT
Monday-Friday
Phone: (888) 862-3289
Fax: (901) 252-1321
Email: techsupport@tnb.com