

## DUAL DRIVE

### USB 3.0 STORAGE AND BACKUP



Buffalo's DriveStation Duo USB 3.0 Hard Drive Array is a two hard drive, RAID enabled USB 3.0 storage solution for small servers, creative professionals, offices and consumers who need redundant and high performance external storage. RAID 0 and RAID 1 support offers flexible capacity and redundant configurations or both drives can remain independent of one another. With USB 3.0 support and backward compatibility with USB 2.0, DriveStation Duo USB 3.0 works with almost any PC or Mac<sup>®</sup> computer and provides interface speeds up to 5 Gbps\*. Equipped with NovaBACKUP<sup>®</sup> Business Essentials software, DriveStation Duo USB 3.0 can back up any PC including Windows<sup>®</sup> Servers and Exchange and SQL datastores. Plus, user replaceable hard drives offer easy maintenance with no tools required.

## FEATURES

### EASY TO USE STORAGE

With terabytes of storage, DriveStation Duo USB 3.0 provides a reliable, easy to use storage for your PC and Mac<sup>®</sup> computer. Quickly expand the capacity of your computer for your favorite music, photos, videos and more. The simple USB 3.0 interface offers plug and play setup and universal connectivity.

### EASY SCHEDULED BACKUP

DriveStation Duo USB 3.0 is perfect for backing up your important files. Disaster and hard drive failures can occur unexpectedly; don't leave your important files and treasured memories in the hands of chance. Schedule regular backups for your PC with Buffalo Backup Utility or use Time Machine for your Mac. Protect all of your data, down to the last byte.

### BUFFALO TOOLS

Buffalo Tools is a feature-rich suite of optional software included on many Buffalo DriveStation and MiniStation storage products. Any or all of the following components of Buffalo Tools may be installed on Windows PCs.

- Buffalo's Backup Utility for Windows PCs and can be used to back up one or multiple computers with a single Buffalo external hard drive.
- eco Manager is an energy efficiency tool used to conserve energy and reduce battery consumption.
- RAMDISK is a simple utility that allows you to create a RAM disk on your Windows PC.
- SecureLock for Windows<sup>®</sup> provides complete control of the data encryption on your Buffalo external hard drive, providing password protection and software data encryption.

### NOVABACKUP<sup>®</sup> BUSINESS ESSENTIALS

DriveStation Duo USB 3.0 comes with one license of NovaBACKUP<sup>®</sup> Business Essentials, an easy to use, complete backup solution for Windows<sup>®</sup> PCs, Windows<sup>®</sup> Servers, and SQL/Exchange databases.

### MEDIA STORAGE CAPACITY

HDD Size↓	Photos*	Movies†	Songs‡
1 TB	450,000	1,000	250,000
2 TB	900,000	2,000	500,000
4 TB	1,800,000	4,000	1,000,000
6 TB	2,700,000	6,000	1,500,000
8 TB	3,600,000	8,000	2,000,000

Results will vary based on individual factors.

\* Figures represent the average number of photos taken with a 10 megapixel camera with an average file size of 2.2 MB per photo.

† Figures represent the number of movies based on an average file size of 1 GB per movie.


‡ Figures represent the number of MP3 files at an average length of 00:03:25/160 Kbps with an average file size of 4 MB per song.

1 MB = 1,000,000 bytes, 1 GB = 1,000,000,000 bytes, 1 TB = 1,000,000,000,000 bytes. Total accessible capacity varies depending on operating environment.

FLEXIBLE STORAGE AND REDUNDANCY

**RAID 0** offers optimal performance and capacity by evenly storing data across both hard drives with zero redundancy

**RAID 1** automatically creates an exact copy on the second hard drive, protecting your data from hard drive failure



MODELS

HD-WL2TU3R1, HD-WL4TU3R1  
HD-WL6TU3R1, HD-WL8TU3R1

MODELS

DriveStation Duo USB 3.0, Quick-Setup Guide,  
AC Adapter, Warranty Statement

SPECIFICATIONS

INTERNAL HARD DRIVES

Number of Drives	2
Drive Interface	SATA 3 Gbps
Hard Drive Sizes:	1 TB, 2 TB, 3 TB, 4 TB
Total Hard Drives:	2 TB, 4 TB, 6 TB, 8 TB

USB INTERFACE

Standard Compliance	USB 3.0 / 2.0
Number of Ports	1
Data Transfer Rate	Max: 5 Gbps* (USB 3.0) Max. 480 Mbps (USB 2.0)

OTHER

Dimensions (W x H x D in)	3.4 x 5 x 8.1
Weight (lbs)	4.5 Average
Operating Environment	41-95°
Power Supply	AC 100-240V 50/60Hz
Client OS Support	Windows <sup>®</sup> 8 (32-bit/64-bit), Windows <sup>®</sup> 7 (32-bit/64-bit), Windows Vista <sup>®</sup> (32-bit/64-bit), Windows <sup>®</sup> XP, Windows <sup>®</sup> 2000, Windows Server <sup>®</sup> 2003 (32-bit)*, Windows Server <sup>®</sup> 2003 R2 (32-bit)*, Windows Server <sup>®</sup> 2008 (32-bit/64-bit)*, Windows Server <sup>®</sup> 2008 R2 (64-bit)*, Mac OS <sup>®</sup> X 10.5 or later**

\*\* The HDD default format is NTFS; to work with Mac, reformat the HDD using Mac Disk Utility. Only basic external hard drive functionality is supported with this operating system; some included utilities may not work.

\*1 TB = 1,000,000,000,000 bytes; total accessible capacity varies depending on operating environment. Data rate, features and performance may vary based on the configuration of your system and other factors. Buffalo Technology (Buffalo Inc.) shall not be responsible for data loss and shall have no liability arising out of damages from lost data.

**24/7 TECH SUPPORT | 1 YEAR WARRANTY**

(866) 752-6210 | USA & Canada Only