On Line Catalog



BURNDY Catalog Number	GB26TN
UPC Number	781810079294
Description	4-2/0 CU-PLT 1 PC GRD
Status	Active

Web Use
BURNDY Product Line

Dimensional	
Width (in)	1.42
Height (in)	1.74
Size (Hex) or Size (Bolt)	3/8
Thickness	0.25
Size (Hex) or Size (Bolt) - in	0.38
Width (Fraction)	1-3/7
General	
Product Description	Mechanical Grounding Connector, Cable to 1/4" Thick Bar, 4 AWG (Sol.) - 2/0 AWG (Str.), 3/8" Stud, Tin Plated
Conductor(s)	
Bar Thickness (Range)	N/A
Copper Solid Size (Range)	4 AWG-2/0 AWG
Copper Stranded (Range)	4 AWG-2/0 AWG
Physical	
Installation Torque	240
Type of Plating	Tin - Electro Plated
Plated (Yes or No)	Y
Product Material	Copper Alloy
Approvals / Certifications	
Rated for Direct Burial	Y
UL Listed	Y
CSA Certified	Y
ROHS Compatible	Compliant
UL Recognized	N
CULUS	N
Industry Standards	UL467

Documentation

For further technical assistance, please contact us

BURNDY LLC - USA

47, industrial Park Drive
Manchester NH03109

BURNDY Technical Servcies

47, industrial Park Drive
Manchester NH03109

Hours: 8.00 AM - 5.00 PM
Monday - Friday
Phone: 000-346-4175