

170-03010



Article Number: 170-03010

Flame Retardant Expandable Braided Sleeving, 1.25" Dia., Black, 50.0 ft/Standard Reel



Download drawing



Download spec sheet

Base Data

Local Order Number 170-03010

Type BSPFR1140

Color Black (BK)

Features and Benefits

- Treated polyester material contains a combustion inhibitor for use in applications where flame retardancy is required.
- Braided design allows sleeving to expand by 150% to accommodate variations in wire bundle and eases installation.

Product Description A flame retardant woven (threaded) polyester sleeving that is resistant to cuts and abrasion, and contains a combustion inhibitor allowing it to achieve a UL and CSA flame resistance rating of VW-1. Contains white tracer thread for easy identification.

Short Description Flame Retardant Expandable Braided Sleeving, 1.25" Dia., Black, 50.0 ft/Standard Reel

Product Dimensions

Length L (Imperial) 50.0 ft

Length L (Metric) 15.2 m

Reel Length (imperial) 50.0 ft

Bundle Diameter Min. (Imperial) 0.75 "

Bundle Diameter Min. (Metric) 19.1 mm

Bundle Diameter Max. (Imperial) 1.75 "

Bundle Diameter Max. (Metric) 44.5 mm

Nominal Diameter (Imperial) 1-1/4 "

Nominal Diameter (Metric) 31.8 mm

Logistics and Packaging

Quantity Per reel

Package Quantity 50 ft

Package Quantity (Metric) 50.0 ft

Weight (imperial) 0.8 lbs

Weight (Metric) 0.363 kg

Material and Specifications

Material Polyester (PET)

Material Shortcut PET

Flammability FMVSS 302
FAR 25

Mil-202
VW-1

Operating Temperature -94°F to +257°F (-70°C to +125°C)

ROHS Compliant Yes

UL Recognized (US and Canada) Yes