

# 12X12X6 HEATED & COOLED POE ENCLOSURE WITH INTEGRATED 4 ELEMENT RPSMA 4/6 DBI OMNI



The AccelTex Solutions Heated & Cooled PoE enclosure allows an access point to be installed in an outdoor or other temperature-limiting environment. The heater, fan and AP are all powered by a single PoE cable run from the network switch. The enclosure ships ready for an AP installation with our 2.4/5 GHz 4/6 dBi omni antenna integrated onto the bottom of the enclosure.

### Part Number: ATS-12126-S-L-4S-CG-POE-HC-OO-46

## > HEATED & COOLED ENCLOSURE SYSTEM COMPONENTS

- 12x12x6 Poly Enclosure with Solid Door, Latch Lock, Cord Grip and Mounting Feet
- 2.4/5 GHz 4/6 dBi 4 Element RPSMA Omni Mounted to the Bottom of the Enclosure
- 1 Gbps Ethernet Surge Suppression
- 50W Power Injector and PoE Splitter
- 15W Heater and 12V Brushless Fan
- Adjustable Thermostat
- Ethernet Cables (Internal Only, Customer provides Ethernet Cable to Enclosure)
- Ground Bar, Ground Lug and all Internal Components Pre-wired to this Ground
- T-Bar for AP Mounting
- DIN Rail
- 4 RPSMA Lightning Arrestors
- 4 Right Angle RPSMA Jack to RPSMA Plug Adapters

## > POWER INJECTOR SPECIFICATIONS

Protocol: 802.3at GigaBit PoE (supports 802.3af) Input Voltage: AC 90V-264V at 120V/230V Input Frequency: 47-63hz Input Current: 0.75A at 120V AC Inrush Current: 25A Max at 120 VAC Operation Temperature: -13 to 122°F (-25 to 50°C)

## > POE SPLITTER SPECIFICATIONS

Protocol: 802.3at GigaBit PoE (supports 802.3af) Input Voltage: DC 36V-60V Operation Temperature: -13 to 140°F (-25 to 60°C)

## > WARRANTY

1 Year Limited Warranty

The facts and figures herein are carefully compiled to the best of our knowledge and are intended for general informational purposes only. Responsibility for the use and application of AccelTex Solutions materials rests with the end user. All AccelTex Solutions products are sold pursuant to the AccelTex Solutions Terms and Conditions of Sale. © 2015 AccelTex Solutions. All Rights Reserved. AccelTex, AccelTex Solutions, the AccelTex Solutions Logo and other marks are trademarks or registered trademarks of AccelTex Solutions. Other products or service names may be the property of third parties.

1.888.406.8906 SALES@ACCELTEX.COM