



4-1206505-4

Fiber Optic Termination Panel, 1U, 19 in, singlemode, 24 SC/PC, sliding, black

Body Features

Chassis Color	Black
Finish	Powder coated

Configuration Features

Number of Ports	24
Front Connector Type	SC/UPC
Splice Chip Type	Fusion Fusion with sleeve
Configuration	Adapters only
Number of Fibers	24
Number of Splice Organizer Trays	4
Port Style	Duplex
Splice Capacity	24

Dimensions

Height	44.450 mm 1.750 in
Width	482.600 mm 19.000 in

Packaging Features

Includes	Installation Instruction Mounting hardware
Packaging Method	Box/Carton
Packaging Quantity	1

Product Availability

Region	Asia
--------	------

Product Type Features

Product Type	Fiber Termination Panel
System	AMP NETCONNECT
Rack Units	1.0
Optical Mode	Multimode

Regulatory Compliance/Certifications

Agency
RoHS 2011/65/EU

Classification
Compliant