

IGNITION LOCKS

Eagle	Medallion sedan & wagon	All	Coded cylinder without switch and locking bar	C-27-223	Previously available as C-27-221 discontinued when out. If the original switch or locking bolt cannot be reused, additional parts may be available from Chrysler / Jeep-Eagle dealers.		
Eagle	Premier	1988-91	Replacement locks available from Chrysler / Jeep-Eagle dealers only Use tumbler series P-13-101/104 (P-21-111/114)				
Eagle	Summit	1989-92	Coded cylinder automatic transmission	C-22-106	Coded cylinder manual transmission	C-22-105	Use tumbler series P-30-161/164
Eagle	Summit	1993-96	Coded cylinder	C-22-110	Use tumbler series P-33-101/105		
Eagle	Summit Wagon (Colt Vista)	1984-91	Coded cylinder	C-22-102	Use tumbler series P-30-141/144		
Eagle	Summit wagon	1992-93	Coded cylinder	C-22-114	Use tumbler series P-30-161/164		
Eagle	Summit wagon	1994	Coded cylinder automatic transmission	C-22-114	Coded cylinder manual transmission	C-22-113	Use tumbler series P-30-161/164
Eagle	Talon	1990-94	Coded cylinder automatic transmission	C-22-108	Coded cylinder manual transmission	C-22-107	Use tumbler series P-30-161/164
Eagle	Talon	1995-99	Coded cylinder automatic transmission	C-22-117	Coded cylinder manual transmission	C-22-116	Use tumbler series P-30-161/164
Eagle	Vision LH	1993-97	Coded cylinder	LC1355	Uncoded cylinder	LC1355U	Use tumbler series P-44-111/114
Eagle	Vision LH	1998	Coded cylinder	LC6941	Uncoded cylinder	LC6941U	Use tumbler series P-44-131/134
Eagle Truck	Heavy truck	All	See the Heavy Truck section				
Edsel	All	1958-59	Coded cylinder	C-42-400 LC1400	Uncoded cylinder	LC1400U	Use tumbler series P-42-181/185
Edsel	All	1960	Coded cylinder	C-42-401 LC1401	Uncoded cylinder	LC1401U	Use tumbler series P-42-181/185
Fargo	All	All	See Dodge Pickup or Dodge Van				
Ferrari	All	All	See the Exotic Brands section				
Fiat	124	1970-up	Complete lock	C-17-101	Disassembly and rekeying is not recommended.		
Fiat	128	1970-up	Complete lock	C-17-102	Disassembly and rekeying is not recommended.		
Fiat	131 Mirafiori, Brava	1975-81	Complete lock	C-17-106	Disassembly and rekeying is not recommended.		
Fiat	Pininfarina		Complete lock	C-17-101	Disassembly and rekeying is not recommended.		
Fiat	Strada	1979-83	Complete lock	C-17-106	Disassembly and rekeying is not recommended.		
Fiat	X1/9 Bertone		Complete lock	C-17-102	Disassembly and rekeying is not recommended.		
Ford	All cars	1952-59	Coded cylinder	C-42-400 LC1400	Uncoded cylinder	LC1400U	Use tumbler series P-42-181/185
Ford	All cars	1960-64	Coded cylinder	C-42-401 LC1401	Uncoded cylinder	LC1401U	Use tumbler series P-42-181/185
Ford	Aerostar	1986-92	Uncoded cylinder	C-42-117	Coded cylinder	C-42-110	Use tumbler series P-42-191/195
Ford	Aerostar (10-cut locks)	1993-11/95	Uncoded cylinder	C-42-157	Coded cylinder	C-42-150	Use tumbler series P-42-191/195
Ford	Aerostar (8-cut locks)	11/95-97	Uncoded cylinder	C-42-185 LC6177U	Coded cylinder	C-42-184 LC6177	Use tumbler series P-42-191/195 for Hurd production P-42-051/055 for Lockcraft production and most locks originally installed on the car.
Ford	Aspire	1994-99	Coded cylinder	C-40-103	Use tumbler series P-40-101/104		
Ford	Bronco	1966-77	Coded cylinder	C-42-401 LC1401	Uncoded cylinder	LC1401U	Use tumbler series P-42-181/185
Ford	Bronco	1978-79	Coded cylinder	C-42-402 LC1402	Uncoded cylinder	LC1402U	Use tumbler series P-42-131/135
Ford	Bronco	1980-86	Coded cylinder	C-42-406 LC1406	Uncoded cylinder	LC1406U	Use tumbler series P-42-131/135
Ford	Bronco	1987-91	Coded cylinder	C-42-407 LC1407	Uncoded cylinder	LC1407U	Use tumbler series P-42-131/135
Ford	Bronco (10-cut locks)	1992-2/95	Uncoded cylinder	C-42-157	Coded cylinder	C-42-150	Use tumbler series P-42-191/195
Ford	Bronco (8-cut locks)	3/95-97	Uncoded cylinder	C-42-185 LC6177U	Coded cylinder	C-42-184 LC6177	Use tumbler series P-42-191/195 for Hurd production P-42-051/055 for Lockcraft production and most locks originally installed on the car.
Ford	Bronco II	1984	Coded cylinder	C-42-406 LC1406	Uncoded cylinder	LC1406U	Use tumbler series P-42-131/135
Ford	Bronco II	1985-90	Coded cylinder	C-42-407 LC1407	Uncoded cylinder	LC1407U	Use tumbler series P-42-131/135
Ford	Club Wagon, Chateau	All	See Ford Van – Econoline				
Ford	Contour	1995-00	Uncoded cylinder	C-42-167	Coded cylinder	C-42-160	Use tumbler series P-42-191/195
Ford	Cortina	1965-70	Uncoded plug (except with locking steering)	B-14-210	Use tumbler series P-14-211/213		
Ford	Cortina	1971-76	Coded cylinder	C-18-102	Use tumbler series P-18-111/114		
Ford	Crown Victoria	1983-89	Coded cylinder	C-42-407 LC1407	Uncoded cylinder	LC1407U	Use tumbler series P-42-131/135
Ford	Crown Victoria (10-cut locks)	1990-95	Uncoded cylinder	C-42-157	Coded cylinder	C-42-150	Use tumbler series P-42-191/195

Check www.carlocks.com for the most up to date information

IGNITION LOCKS

Ford	Crown Victoria (8-cut locks)	1996-3/05	Uncoded cylinder	C-42-185 LC6177U	Coded cylinder	C-42-184 LC6177	Use tumbler series P-42-191/195 for Hurd production P-42-051/055 for Lockcraft production and most locks originally installed on the car.
Ford	Crown Victoria	4/05-08	Uncoded service pack	C-42-172	Tumblers included in the uncoded service pack		
Ford	Edge	2007-08	Uncoded service pack	C-42-173	Tumblers included in the uncoded service pack NOTE: This is the exact replacement lock of the same design as sold by Ford dealers.		
Ford	Escape	2001-07	Uncoded cylinder (no turn knob)	C-42-188	Coded cylinder (no turn knob)	C-42-189	Use tumbler series P-42-191/195
			Uncoded service pack (with turn knob)	C-42-171	Ignition lock with turn knob, tumblers included in the uncoded service pack.		
Ford	Escape	2008	Uncoded service pack	C-42-173	Tumblers included in the uncoded service pack NOTE: This is the exact replacement lock of the same design as sold by Ford dealers.		
Ford	Escort	1981-87	Coded cylinder chrome	C-42-407 LC1407	Uncoded cylinder	LC1407U	Use tumbler series P-42-131/135
			Coded cylinder black	C-42-409 LC1409	Uncoded cylinder	LC1409U	Use tumbler series P-42-131/135
Ford	Escort	1988-90	Uncoded cylinder	C-42-127	Coded cylinder	C-42-120	Use tumbler series P-42-191/195
Ford	Escort	1991-93	Uncoded cylinder manual transmission	C-42-193	Complete lock & switch manual trans	C-42-291	Use tumbler series P-42-191/195
			Uncoded cylinder automatic transmission	C-42-194	Complete lock & switch automatic trans.	C-42-292	Use tumbler series P-42-191/195
Ford	Escort (10-cut locks)	1994-11/30/95	Uncoded cylinder manual transmission	C-42-193	Complete lock & switch manual trans	C-42-293	Use tumbler series P-42-191/195
			Uncoded cylinder automatic transmission	C-42-194	Complete lock & switch automatic trans.	C-42-294	Use tumbler series P-42-191/195
Ford	Escort (Mazda lockis)	12/1/95 to 1996	Complete lock automatic transmission	C-20-245	Complete lock manual transmission	C-20-244	Discontinued when out Use tumbler series P-33-101/105
Ford	Escort	1997-02	Complete lock & switch automatic transmission	C-20-228	Complete lock & switch manual trans	C-20-227	Use tumbler series P-20-131/155
Ford	Excursion	2000-05	Uncoded cylinder	C-42-185 LC6177U	Coded cylinder	C-42-184 LC6177	Use tumbler series P-42-191/195 for Hurd production P-42-051/055 for Lockcraft production and most locks originally installed on the car.
Ford	EXP	1981-87	see Escort				
Ford	Expedition	1997-02	Uncoded cylinder	C-42-185 LC6177U	Coded cylinder	C-42-184 LC6177	Use tumbler series P-42-191/195 for Hurd production P-42-051/055 for Lockcraft production and most locks originally installed on the car.
Ford	Expedition	2003-08	Replacement locks available from Strattec.				
Ford	Explorer	1991-94	Uncoded cylinder	C-42-117	Coded cylinder	C-42-110	Use tumbler series P-42-191/195
Ford	Explorer (10-cut locks)	1995-96	Uncoded cylinder	C-42-157	Coded cylinder	C-42-150	Use tumbler series P-42-191/195
Ford	Explorer (8-cut locks)	1996-00	Uncoded cylinder	C-42-185 LC6177U	Coded cylinder	C-42-184 LC6177	Use tumbler series P-42-191/195 for Hurd production P-42-051/055 for Lockcraft production and most locks originally installed on the car.
Ford	Explorer 2-door (Explorer Sport)	2001-05	Uncoded cylinder	C-42-185 LC6177U	Coded cylinder	C-42-184 LC6177	Use tumbler series P-42-191/195 for Hurd production P-42-051/055 for Lockcraft production and most locks originally installed on the car.
Ford	Explorer 4-door	2001-08	Replacement locks available from Strattec				
Ford	Explorer Sport Trac (pickup)	2001-06	Uncoded cylinder	C-42-185 LC6177U	Coded cylinder	C-42-184 LC6177	Use tumbler series P-42-191/195 for Hurd production P-42-051/055 for Lockcraft production and most locks originally installed on the car.
Ford	Explorer Sport Trac (pickup)	2007-08	Replacement locks available from Strattec				
Ford	Fairlane	1962-65	Coded cylinder	C-42-401 LC1401	Uncoded cylinder	LC1401U	Use tumbler series P-42-181/185
Ford	Fairlane	1966-70	Coded cylinder	C-42-402 LC1402	Uncoded cylinder	LC1402U	Use tumbler series P-42-131/135
Ford	Fairmont	1978-83	Coded cylinder	C-42-407 LC1407	Uncoded cylinder	LC1407U	Use tumbler series P-42-131/135
Ford	Falcon	1960-65	Coded cylinder	C-42-401 LC1401	Uncoded cylinder	LC1401U	Use tumbler series P-42-181/185
Ford	Falcon	1966-69	Coded cylinder	C-42-402 LC1402	Uncoded cylinder	LC1402U	Use tumbler series P-42-131/135

IGNITION LOCKS

Ford	Pinto	1971 to 5/14/73	Coded cylinder	C-42-404 LC1404	Uncoded cylinder	LC1404U	Use tumbler series P-42-131/135
Ford	Pinto	5/15/73 to 1/76	Coded cylinder	C-42-405 LC1405	Uncoded cylinder	LC1405U	Use tumbler series P-42-131/135
Ford	Pinto	2/76-80	Coded cylinder	C-42-406 LC1406	Uncoded cylinder	LC1406U	Use tumbler series P-42-131/135
Ford	Probe	1989-92	Uncoded plug	C-20-311	Use tumbler series P-20-111/164		
			Complete lock & switch automatic transmission	C-20-215	Complete lock & switch manual transmission	C-20-216	Use tumbler series P-20-111/164
Ford	Probe	1993-97	Complete lock & switch manual trans	C-20-219	Coded cylinder (SEE NOTE)	C-20-109	Use tumbler series P-33-101/105
			Complete lock & switch automatic trans	C-20-220	Uncoded cylinder	C-20-110	Use tumbler series P-33-101/105
			NOTE: C-20-109 cylinder is discontinued when out, now must use complete lock assembly C-20-219.				
Ford	Taurus	1986-89	Uncoded cylinder	C-42-137	Coded cylinder	C-42-130	Use tumbler series P-42-191/195
Ford	Taurus	1990-95	Uncoded cylinder	C-42-147	Coded cylinder	C-42-140	Use tumbler series P-42-191/195
Ford	Taurus	1996-06	Uncoded cylinder	C-42-182 LC6177U	Coded cylinder	C-42-181 LC6177	Use tumbler series P-42-191/195 for Hurd production P-42-051/055 for Lockcraft production and most locks originally installed on the car.
Ford	Taurus	2008	Replacement locks available from Strattec				
Ford	Tempo	1984-87	Coded cylinder chrome	C-42-407 LC1407	Uncoded cylinder	LC1407U	Use tumbler series P-42-131/135
			Coded cylinder black	C-42-409 LC1409	Uncoded cylinder	LC1409U	Use tumbler series P-42-131/135
Ford	Tempo	1988-94	Uncoded cylinder	C-42-127	Coded cylinder	C-42-120	Use tumbler series P-42-191/195
Ford	Thunderbird	1955-59	Coded cylinder	C-42-400 LC1400	Uncoded cylinder	LC1400U	Use tumbler series P-42-181/185
Ford	Thunderbird	1960-64	Coded cylinder	C-42-401 LC1401	Uncoded cylinder	LC1401U	Use tumbler series P-42-181/185
Ford	Thunderbird	1965-69	Coded cylinder	C-42-402 LC1402	Uncoded cylinder	LC1402U	Use tumbler series P-42-131/135
Ford	Thunderbird	1970 to 5/14/73	Coded cylinder	C-42-404 LC1404	Uncoded cylinder	LC1404U	Use tumbler series P-42-131/135
Ford	Thunderbird	5/15/73 to 1/76	Coded cylinder	C-42-405 LC1405	Uncoded cylinder	LC1405U	Use tumbler series P-42-131/135
Ford	Thunderbird	2/76-79	Coded cylinder	C-42-406 LC1406	Uncoded cylinder	LC1406U	Use tumbler series P-42-131/135
Ford	Thunderbird	1980-82	Coded cylinder	C-42-407 LC1407	Uncoded cylinder	LC1407U	Use tumbler series P-42-131/135
Ford	Thunderbird	1983-84	Coded cylinder	C-42-409 LC1409	Uncoded cylinder	LC1409U	Use tumbler series P-42-131/135
Ford	Thunderbird	1984-93	Uncoded cylinder	C-42-127	Coded cylinder	C-42-120	Use tumbler series P-42-191/195
Ford	Thunderbird (10-cut locks)	1994-96	Uncoded cylinder	C-42-147	Coded cylinder	C-42-140	Use tumbler series P-42-191/195
Ford	Thunderbird (8-cut locks)	1996-99	Uncoded cylinder	C-42-185 LC6177U	Coded cylinder	C-42-184 LC6177	Use tumbler series P-42-191/195 for Hurd production P-42-051/055 for Lockcraft production and most locks originally installed on the car.
Ford	Thunderbird	2001-05	Replacement locks available from Strattec Use tumbler series P-42-051/055				
Ford	Torino	1968-69	Coded cylinder	C-42-402 LC1402	Uncoded cylinder	LC1402U	Use tumbler series P-42-131/135
Ford	Torino	1970 to 5/14/73	Coded cylinder	C-42-404 LC1404	Uncoded cylinder	LC1404U	Use tumbler series P-42-131/135
Ford	Torino	5/15/73 to 1/76	Coded cylinder	C-42-405 LC1405	Uncoded cylinder	LC1405U	Use tumbler series P-42-131/135
Ford	Torino	2/76-end of model	Coded cylinder	C-42-406 LC1406	Uncoded cylinder	LC1406U	Use tumbler series P-42-131/135
Ford	Windstar (10-cut locks)	1995-96	Uncoded cylinder	C-42-147	Coded cylinder	C-42-140	Use tumbler series P-42-191/195
Ford	Windstar (8-cut locks)	1996-03	Uncoded cylinder	C-42-185 LC6177U	Coded cylinder	C-42-184 LC6177	Use tumbler series P-42-191/195 for Hurd production P-42-051/055 for Lockcraft production and most locks originally installed on the car.
Ford Pickup	Courier	to 3/73	Complete lock & switch	C-20-100	Discontinued when out by ASP, now available from Ford or Mazda dealers only. Tumblers and service parts are not available.		
Ford Pickup	Courier	3/73-8/75	Complete lock & switch	C-20-103	Discontinued when out by ASP, now available from Ford or Mazda dealers only. Tumblers and service parts are not available.		
Ford Pickup	Courier	3/76-82	Complete lock & switch	C-20-104	Discontinued when out by ASP, now available from Ford or Mazda dealers only. Use tumbler series P-20-111/113		
Ford Pickup	Explorer Sport Trac	2001-06	Uncoded cylinder	C-42-185 LC6177U	Coded cylinder	C-42-184 LC6177	Use tumbler series P-42-191/195 for Hurd production P-42-051/055 for Lockcraft production and most locks originally installed on the car.

ASP PART NUMBERING SYSTEM

The ASP Part Numbering System

Working with the ASP part numbers is easier if you have a basic understanding of the part numbering system, explained here:

The first letter or letters of the part number identify what type of product the part number is:

A	Keying kits and parts assortments
B	Luggage compartment locks
C	Ignition locks
D	Door locks (including complete locks that include the door handle)
DH	Door handles (except complete locks that include the door handle)
DP	Door locks (keyed alike pair)
E	Engine compartment locks
F	Fasteners (including lock retaining clips, shear-head bolts, door panel fasteners, etc.)
G	Glove compartment and stowage locks
KB	Key blanks
P	Lock service parts (including tumblers, face caps, and other parts)
RK	Remote head key blanks
S	Lock sets
T	Fuel tank locks
W	Ignition switches (wiring assembly only without lock cylinder)

The second two digits of the part number tell you the PRIMARY brand of vehicle that the item is used on:

00	Various cars
11	Alfa Romeo
12	Audi
13	BMW
14	British Cars (Austin, Jaguar, Land Rover, MG, Range Rover, Triumph)
15	British Chrysler (Plymouth Cricket, Sunbeam, Hillman)
16	Nissan / Datsun / Infiniti
17	Fiat
18	European Ford (Capri, Fiesta, Merkur)
19	Honda / Acura
20	Mazda
21	Mercedes-Benz
22	Mitsubishi
23	GM Europe (Cadillac Catera, Pontiac Lemans, Opel)

24	Isuzu (including General Motors brands)
25	Peugeot
26	Porsche
27	Renault
28	Saab
29	Subaru
30	Toyota / Lexus / Scion / Hino truck
31	Volkswagen
32	Volvo
33	Suzuki
34	Lada
35	Lancia
36	Hyundai
37	Daihatsu
38	Citroen
39	Yugo
40	Kia
41	General Motors USA (Buick, Cadillac, Chevrolet, GMC, Oldsmobile, Pontiac)
42	Ford / Lincoln / Mercury (USA)
43	American Motors (including some Heavy Trucks and Jeep)
44	Chrysler / Dodge / Jeep / Plymouth
45	Skoda
49	Saturn
50	Daewoo (including Chevrolet Aveo, Saturn Vue, other General Motors brands)
55	Renault truck (including some Mack trucks)
56	Freightliner truck
57	Kenworth truck
93	Harley Davidson Motorcycle
94	Honda Motorcycle
98	Yamaha Motorcycle

For example, if you have part number C-30-107, by understanding the part numbering system you will know that the part is an ignition lock (first letter C), which fits a Toyota (second two digits 30).

There are exceptions to this system created by the same part being used on more than one brand of car. Also some parts are used in more than one place on the car – for example, B-14-210 is numbered as a luggage compartment lock, but also is used as an ignition lock or door lock on some cars.

ASP PART NUMBERING SYSTEM

The same part being used on more than one brand of car is explained by lock families, as follows:

Audi - also found on some Porsche and Volkswagen

Ford USA – also found on some Mazda and Nissan

Honda / Acura - also found on some Isuzu

Mazda – also found on some Chrysler imports, Ford imports, General Motors imports, GEO, Mitsubishi, Suzuki

Nissan - also found on some Subaru and Isuzu truck

Toyota – also found on some Chrysler imports, Daihatsu, General Motors imports, GEO, Hyundai, Isuzu, Kia, Mazda, Mitsubishi, Suzuki.

Volkswagen - also found on some Audi and Porsche (tumblers also used on BMW)

You will also find some parts that are used among the brands of the following groups of cars:

British cars - Aston Martin, Austin, English Ford, Jaguar, Jensen, Land Rover, MG, Morgan, Range Rover, Rover car, Sterling car, Triumph, TVR, Volvo.

French cars - Peugeot, Renault, Citroen

German cars - Audi, BMW, Daewoo, General Motors (Cadillac Catera, Chevrolet Aveo, Pontiac Lemans, others), Mini, Porsche, Mercedes-Benz, Volkswagen

Italian cars - Alfa Romeo, Bertone, Ferrari, Fiat, Iveco, Lada, Lamborghini, Lancia, Maserati, Pininfarina, Yugo

Lockcraft Part Numbers

The first two letters of the part number identify what type of product the part number is:

DL	Door lock
LC	Ignition lock
LS	Lock set
RP	Lock service parts (including tumblers, face caps, and other parts)
SK	Keying kits and parts assortments
TL	Luggage compartment locks

Lockcraft part numbers that end in “U” are uncoded locks.

There have been many changes to the Lockcraft part numbers over the past years, explained as follows:

Most old Lockcraft part numbers had no letter prefix. For example, old part number 1426 was changed to LC1426 to identify the type of product.

Some old Lockcraft part numbers had a letter prefix “A”, which was changed to “RP”. For example, part number A6001 was changed to RP6001. This could be confusing if you have an old Lockcraft or All Lock keying kit or parts assortment which identified the parts inside by the letter prefix “A”. When reordering simply change the “A” to “RP”.

Some old Lockcraft part numbers had a digit “3” at the end of the part number, which designated poly bag packaging. For example, part number LC14263 designated the LC1426 ignition lock in a poly bag. The currently used part numbers now eliminate the “3” at the end and using the example LC14263 is now simply LC1426.

Some old Lockcraft part numbers had a digit “8” at the end of the part number, which designated that it was an uncoded lock. For example, part number LC14268 designated the LC1426 ignition lock in uncoded form. The currently used part numbers now use “U” at the end of the part number instead of the “8”. Using the example LC14268 is now LC1426U.

PART NUMBER LISTING and POPULARITY RATINGS

Part Number Listings and Popularity Ratings

Pages 214-233 contain a complete listing of ASP part numbers, with the 2008 popularity rating for each part number. The popularity ratings are explained as follows:

A = Most popular items (lock cylinders and replacement parts)

B = Second most popular group of lock cylinders

Y = Replacement parts (keying kit refill tumblers, face caps, etc.), popularity equivalent to B-rated lock cylinders

C = Third most popular group of lock cylinders

Z = Replacement parts (keying kit refill tumblers, face caps, etc.), popularity equivalent to C-rated lock cylinders

H = Items not recommended for stock by distributors, these parts are normal stock items for the ASP warehouse and available for drop shipments (HI-SPEED delivery). Orders must be placed through your distributor, and are subject to stock on hand at ASP. Some distributors may have selected H-rated items in stock.

S = Special order items only, may not be in stock at ASP. These items may be subject to minimum order quantities if needed. Some distributors may have selected S-rated items in stock.

DWO = Discontinued when out. Some items may still have limited stock at ASP or at some distributors, but will not be restocked when existing supplies are sold out.

ASP products are sold through the network of locksmith supply distributors located throughout the USA and Canada.

With over 4,000 different part numbers in our range, it is impossible and impractical for distributors to keep every part number in stock. Thus we have assigned each of our part numbers a popularity rating to assist distributors in keeping stock. We have implemented new distributor stocking programs based on these popularity ratings. Please check www.carlocks.com for the most current information about our distributor stocking guidelines. ASP is working closely with our distributors to provide you the fastest delivery possible at the lowest possible cost.

Distributors who make a commitment to keep stock according to our recommendations are listed on www.carlocks.com. This list is subject to change at any time. Distributors who do not keep the stocking commitment will be removed from the list.

Explanation of other notes on the part number listing

a. Some items have (now use ...) to the right of the part number, with a rating of DWO.

For example: A-13-105 (now use A-31-110) – this means that A-13-105 has been superseded by A-31-110.

b. Some items have (substitute ...) to the right of the part number, with a rating of DWO.

For example: B-19-154 (substitute B-19-155) - this means that you can substitute B-19-155 for B-19-154, but there is some difference between the two parts. A complete listing of these part numbers with a brief explanation of the difference between each superseded part and the replacement part is provided on pages 234-237.

c. Some items have (see ...) to the right of the part number, with no popularity rating.

For example: B-16-105 (see B-16-205), with no popularity rating. Then go to B-16-205 and you will see it listed as B-16-205 (B-16-105) with the popularity rating of B. This is a result of our consolidating some similar interchangeable part numbers. In this example, whether you order B-16-105 or B-16-205, you will get the same part at the same price. A complete listing of these part numbers is provided on pages 238-239.