

LOCKNETICS®

Full line catalog and price book

Electromagnetic locks,
electric strikes and accessories

Contents

Electromagnetic locks and electric strikes

WMG Series	4
MG Series	6
CS Series	8
NC Series	10
MDS Series	12
RS Series	14

Access control accessories

Pushbuttons	17
Specialty switches	19
Digital keypads	20
Touch bars	21
Push plates	22
Emergency breaks	23
Door cords	24
Specialty sensor and buzzer switches	25
Power supplies	27
Limited product warranty	28
Weight, case quantity and pricing charts	29

Customer Support

Administrative offices

Allegion Administrative Office
11819 N. Pennsylvania St.
Carmel, IN 46032

allegion.com/us

Allegion Canada Inc.
1076 Lakeshore Road East
Mississauga, ON L5E 1E4

allegion.ca

Placing orders for direct accounts

You can place orders with Allegion via the fax numbers or emails listed below:

US

Fax: 1.800.452.0665

Email: order_entry_schlage_commercial@allegion.com

Canada

Fax: 1.800.209.4734

Email: canada.orders.service@allegion.com

Customer Care

Our Customer Care Representatives are available for questions or assistance for sales order support and technical product support.

US: 1.877.671.7011 Canada: 1.800.900.4734

Technical Product Email Support

US: electronic_lock_techprodsupport@allegion.com

Canada: canada.techservices@allegion.com

Electromagnetic locks and electric strikes



WMG Series

600 and 1200 models



The WMG Series of weather resistant, surface electromagnetic locks are designed for high profile openings that require a tamper-resistant lock with an aesthetically pleasing appearance. A stainless steel housing, fire-rated epoxy seal, optional mounting bracket and an assortment of brackets enable the WMG Series to be used in a variety of applications. Designed for up to 600 lb. or 1200 lb. holding strength.

Features and benefits

- Stainless steel housing
- Sealed with fire-rated epoxy for weather and tamper-resistant applications
- Optional mounting plate for quick, simple installation
- Magnetic bond sensor included
- Built-in voltage spike suppressor
- Field selectable 12/24 VDC
- Suitable for outdoor use

Accessories

- Z bracket kit for in-swing doors
- L bracket for narrow frame, out-swing doors
- 1/2" and 5/8" filler plates


Specifications

- UL10C single door, listed
- UL294, listed
- UL1034, outdoor rating, listed

Electrical


- Dual voltage: 12 VDC @ 0.5A/24 VDC @ 0.25A

Finishes



630/US32D
Satin stainless steel

Brackets




Finishes



628/US28
Aluminum

WMG Series
600 and 1200 models


Lock and armature dimensions



WMG600

Lock: 8" x 1²³/₃₂" x 1⁹/₁₆"
(203mm x 43.5mm x 40mm)

Armature: 7⁵/₁₆" x 1³/₄" x 9⁹/₁₆"
(185mm x 45mm x 14mm)



WMG1200

Lock: 8¹¹/₁₆" x 2¹¹/₁₆" x 1⁵/₈"
(220mm x 68mm x 42mm)

Armature: 7¹/₄" x 1³/₈" x 5⁵/₈"
(185mm x 61mm x 16mm)

WMG Series list prices

Product name	Product description	Finish	Voltage	UPC	List price
WMG600	Weatherproof mag lock - 600lb	630/US32D	12/24 VDC	043156646098	\$370.00
WZBK600	Z-bracket - 600lb	628/US28	N/A	043156646104	\$135.00
WLBK600	L-bracket - 600lb	628/US28	N/A	043156646111	\$58.00
WMG1200	Weatherproof mag lock - 1200lb	630/US32D	12/24 VDC	043156646142	\$470.00
WZBK1200	Z-bracket - 1200lb	628/US28	N/A	043156646159	\$140.00
WLBK1200	L-bracket - 1200lb	628/US28	N/A	043156646166	\$63.00
WFP50	1/2" Filler plate	628/US28	N/A	043156646128	\$25.00
WFP63	5/8" Filler plate	628/US28	N/A	043156646135	\$25.00

MG Series

600 and 1200 models



The MG Series of surface mount electromagnetic locks provides a cost competitive, slim profile and dependable solution for a variety of applications. Designed for up to 600 lb. or 1200 lb. holding strength for both single and double electromagnetic locks.

Features and benefits

- Bi-colored LED sensor provides easy lock status identification
- Adjustable mounting plate for quick, simple installation
- Removable PCB for easy installation
- Built-in voltage spike suppressor
- Field selectable 12/24 VDC

Options (DT models only)

- Timer to provide a 0-90 second delay for locking
- Door status sensor S.P.D.T. switch to determine if door is open or closed

Accessories

- U bracket for glass door
- Z bracket for in-swing doors
- L bracket for narrow frame and out-swing doors
- 1/2" and 5/8" filler plates


Specifications

- UL10C, listed
- UL294, listed
- Indoor use only

Electrical

- Dual voltage: 12 VDC @ 0.5A/24 VDC @ 0.25A

Finishes



630/US32D
Satin stainless steel

Brackets




MLBK600
L bracket

MZBK600
Z bracket



MLBK1200
L bracket

MZBK1200
Z bracket



MUBK
U bracket

Finishes



628/US28
Aluminum


MG Series 600 and 1200 models

Filler plates



MFP50 and MFP63

Finishes



628/US28
Aluminum

Lock and armature dimensions

MG600

Lock: 9 ⁷/₈" x 1 ⁷/₈" x 1 ¹/₁₆"
(250mm x 47.2mm x 26.5mm)

Armature: 7 ⁵/₁₆" x 1 ¹/₂" x 1 ¹/₂"
(185mm x 38mm x 12.5mm)

MG1200

Lock: 10 ¹/₂" x 2 ⁷/₈" x 1 ¹/₂"
(266mm x 73mm x 40mm)

Armature: 7 ¹/₃" x 2 ²/₅" x ³/₅"
(185mm x 61mm x 16mm)

MG600-2

Lock: 19 ³/₄" x 1 ⁷/₈" x 1 ¹/₁₆"
(501.7mm x 47.2mm x 26.5mm)

Armature (each): 7 ⁵/₁₆" x 1 ¹/₂" x 1 ¹/₂"
(185mm x 38mm x 12.5mm)

MG1200-2

Lock: 21" x 2 ⁷/₈" x 1 ¹/₂"
(533.4mm x 73mm x 40mm)

Armature (each): 7 ¹/₃" x 2 ²/₅" x ³/₅"
(185mm x 61mm x 16mm)

MG Series list price

Product name	Product description	Finish	Voltage	UPC	List price
MG600	Mag lock - Standard 600lb	630/US32D	12/24 VDC	043156646173	\$159.00
MG600DT	Mag lock - Monitored 600lb	630/US32D	12/24 VDC	043156646180	\$184.00
MG600-2	Double mag lock - Standard 600lb ¹	630/US32D	12/24 VDC	043156081103	\$295.00
MG600DT-2	Double mag lock - Monitored 600lb ¹	630/US32D	12/24 VDC	043156081110	\$375.00
MLBK600	L-bracket - 600lb ¹	628/US28	N/A	043156646210	\$50.00
MZBK600	Z-bracket - 600lb ¹	628/US28	N/A	043156646197	\$100.00
MG1200	Mag lock - Standard 1200lb	630/US32D	12/24 VDC	043156646241	\$239.00
MG1200DT	Mag lock - Monitored 1200lb	630/US32D	12/24 VDC	043156646258	\$264.00
MG1200-2	Double mag lock - Standard 1200lb ¹	630/US32D	12/24 VDC	043156081127	\$425.00
MG1200DT-2	Double mag lock - Monitored 1200lb ¹	630/US32D	12/24 VDC	043156081134	\$490.00
MLBK1200	L-bracket - 1200lb ¹	628/US28	N/A	043156646289	\$57.00
MZBK1200	Z-bracket - 1200lb ¹	628/US28	N/A	043156646265	\$115.00
MUBK	U-bracket - 600lb/1200lb, adjustable ¹	628/US28	N/A	043156646203	\$65.00
MFP50	¹ / ₂ " Filler plate ¹	628/US28	N/A	043156646234	\$18.00
MFP63	⁵ / ₈ " Filler plate ¹	628/US28	N/A	043156646227	\$23.00

¹. Double Mags require 2 brackets (L, Z, U) and filler plates.

CS Series

450 and 750 models

The low, versatile profile CS Series of electric strikes are designed for use with cylindrical lock sets and select mortise lock sets without deadbolt for both metal and wood door frames.



Features and benefits

- Low profile
- Field selectable fail-safe and fail-secure (fail-secure default), with simple and easy screw reversal
- Included trim piece for installation flexibility and improved appearance
- Mounting tabs included for aluminum frame installation
- Two face plates included: Radius and square edge stainless steel (4 7/8" x 1 1/4")
- Field selectable 12/24 VDC
- Voltage spike suppressor included
- Suitable for rain or dust environment

Options

- CS450 Series accepts latch bolt up to 9/16"
- CS750 Series accepts latch bolt up to 3/4"
- Latch bolt monitoring available

Accessories

- Buzzer rectifier with timer (TBR-100)
- Faceplate kits in 613/US10B finish
- Metal template kit

- 7 15/16 x 1 7/16 radius edge, stainless steel faceplate kits for wood applications
- 6 7/8" x 1 1/4" radius edge, stainless steel faceplate kit for aluminum frames
- 1/2" (12.7mm) lip extension
- 1" (25mm) lip extension
- 2" (50mm) lip extension

Specifications

- UL1034 Burglar-resistant electric locking mechanisms, listed
- UL294 (indoor), listed
- Static strength of 1500 lb. static load, UL certified
- Dynamic strength of 70 ft.-lb. dynamic load, UL certified
- 250,000 cycles endurance, UL certified

Electrical

- Dual voltage: 12VDC @ 0.3A/24VDC @ 0.15A

CS Series 450 and 750 models

Faceplate kit and trim piece



Face plates (each sold separately)




Trim piece

Finish - face plates




613/US10B
Dark bronze




630/US32D
Satin stainless steel

Strike and accessory dimensions



CS450/CS750

3 3/8" x 1 11/16" x 1 3/16"
(85.5mm x 43.5mm x 29.5mm)



CSFP-kit


1 1/4" x 1/8" x 4 7/8"
(31.75mm x 3mm x 124mm)

CCFP-kit

1 1/4" x 1/8" x 6 7/8"
(31.75mm x 3mm x 174.6mm)

CWFP-kit

1 7/16" x 1/8" x 7 15/16"
(36.5mm x 3mm x 201.6mm)



CSLE-.5

1/2" (12.7mm)

CSLE-1

1" (25mm)

CSLE-2

2" (50mm)

CS Series list price

Product name	Product description	Finish	Voltage	UPC	List price
CS450-32D	E-strike - 9/16" deep	630/US32D	12/24 VDC	043156645893	\$170.00
CS450-LBM-32D	E-strike - 9/16" deep with LBM	630/US32D	12/24 VDC	043156645909	\$239.00
CS750-32D	E-strike - 3/4" deep	630/US32D	12/24 VDC	043156645961	\$170.00
CS750-LBM-32D	E-strike - 3/4" deep with LBM	630/US32D	12/24 VDC	043156645978	\$239.00
CSFP-KIT-10B	US10B face plates - Qty 2; Square and radius corner (4 7/8" x 1 1/4")	613/US10B	N/A	043156645916	\$38.00
CCFP-KIT-32D	US32D radius corner faceplate (6 7/8" x 1 1/4")	630/US32D	N/A	043156087365	\$38.00
CCFP-KIT-10B	US10B radius corner faceplate (6 7/8" x 1 1/4")	613/US10B	N/A	043156087358	\$48.00
CWFP-KIT-32D	US32D radius corner faceplate (7 15/16" x 1 7/16") wood applications	630/US32D	N/A	043156645923	\$38.00
CWFP-KIT-10B	US10B radius corner faceplate (7 15/16" x 1 7/16") wood applications	613/US10B	N/A	043156645930	\$48.00
CSLE-.5	1/2" lip extension	N/A	N/A	043156087372	\$50.00
CSLE-1	1" lip extension	N/A	N/A	043156645947	\$50.00
CSLE-2	2" lip extension	N/A	N/A	043156645954	\$50.00
TBR-100	Timer-buzzer rectifier with surge protection for strikes and other access control components	N/A	N/A	043156651740	\$49.00
ESTK-100	E-strike - metal template kit (CS, MDS, RS)	N/A	N/A	043156072842	\$125.00

NC Series

450 model

The no cut electric door strike can be used to convert cylindrical lock sets into an electronic access controlled locking system. No cutting on the frame is required. Simply adjust the vertical alignment feature to the latch bolt centerline and install.



Features and benefits

- No frame cutting is required
- Low profile
- Field selectable fail-safe and fail-secure (fail-secure default) with simple and easy screw reversal
- Two face plates included: Radius and square edge stainless steel (4 7/8" x 1 1/4")
- Field selectable 12/24 VDC
- Voltage spike suppressor included
- Suitable for rain or dust environment

Options

- Accepts latch bolt up to 9/16"
- Latch bolt monitoring available

Accessories

- Buzzer rectifier with timer (TBR-100)
- Face plates kits in 613/US10B finish
- 6 7/8" x 1 1/4" radius edge, stainless steel faceplate kit for aluminum frames
- 7 15/16 x 1 7/16 radius edge, stainless steel faceplate kits for wood applications

Specifications

- UL1034 Burglar-resistant electric locking mechanisms, listed
- UL294 (indoor), listed
- Static strength of 1500 lb. static load, UL certified
- Dynamic strength of 70 ft.-lb. dynamic load, UL certified
- 250,000 cycles endurance, UL certified

Electrical

- Dual voltage: 12VDC @ 0.3A/24VDC @ 0.15A

CS Series
450 and 750 models

Faceplate kit and trim piece



Finish - face plates




613/US10B
Dark bronze




630/US32D
Satin stainless steel

Face plates (each sold separately)


Strike and accessory dimensions




NC450
3 3/8" x 1 1/16" x 1 3/8"
(85mm x 27mm x 35mm)



NCFP-kit
1 1/4" x 1/8" x 4 7/8"
(31.75mm x 3mm x 124mm)



NCCFP-kit
1 1/4" x 1/8" x 6 7/8"
(31.75mm x 3mm x 174.6mm)



NCWFP-kit
1 7/16" x 1/8" x 7 15/16"
(36.5mm x 3mm x 201.6mm)

NC Series list price

Product name	Product description	Finish	Voltage	UPC	List price
NC450	E-strike - no cut - 9/16" deep	630/US32D	12/24 VDC	043156087389	\$215.00
NC450-LBM	E-strike - no cut - 9/16" deep with LBM	630/US32D	12/24 VDC	043156104895	\$284.00
NCFP-KIT-10B	US10B face plates - Qty 1; Radius corner (4 7/8" x 1 1/4")	613/US10B	N/A	043156087396	\$48.00
NCCFP-KIT-32D	US32D radius corner face plate - (6 7/8" x 1 1/4")	630/US32D	N/A	043156087457	\$38.00
NCCFP-KIT-10B	US10B radius corner face plate - (6 7/8" x 1 1/4")	613/US10B	N/A	043156087440	\$48.00
NCWFP-KIT-32D	US32D radius corner face plate (7 15/16" x 1 7/16") wood applications	630/US32D	N/A	043156087419	\$38.00
NCWFP-KIT-10B	US10B radius corner face plate (7 15/16" x 1 7/16") wood applications	613/US10B	N/A	043156087402	\$48.00
NC-RAMPS	US32D removable ramps replacement	630/US32D	N/A	043156087426	\$65.00

MDS Series

100 model

The MDS100 Series electric strike is designed for use with heavy duty mortise lock sets and cylindrical lock sets. Five different face plates included for optional flexibility of installation in wood or metal frames.



Features and benefits

- Heavy duty design with vertical adjustments for flexibility
- Field selectable fail-safe and fail-secure (fail-secure default), with simple and easy screw reversal on non-fire rated models
- Included trim piece for installation flexibility and improved appearance
- Mounting tabs included for aluminum frame installation on non-fire rated doors in non-fire rated applications
- Five stainless steel face plates included for optional flexibility (4 7/8" x 1 1/4" with differing cutouts)
- Field selectable 12/24 VDC
- Built-in voltage spike suppressor included
- Suitable for rain or dust environment

Options

- Fire rating
- Latch bolt monitoring available

Accessories

- Buzzer rectifier with timer (TBR-100)
- Faceplate kit in 613/US10B finish
- Metal template kit


Specifications

- UL1034 burglary-resistant electric locking mechanisms, listed
- UL294 (indoor), listed
- Static strength of 1500 lb. static load, UL certified
- Dynamic strength of 70ft.-lb. dynamic load, UL certified
- UL10C Fire rated, listed - MS100-F models only
- 250,000 cycles endurance, UL certified

Electrical

- Dual-voltage 12 VDC @ .3A/24 VDC @ .15A

Faceplate kit and trim piece




Faceplate kit



Trim piece

Finish - face plates




630/US32D
Satin stainless steel



613/US10B
Dark bronze

Strike and accessory dimensions





MDS100
(excluding faceplate)



3 5/16" x 1 5/8" x 1 13/16"
(84.5mm x 41.5mm x 46.7mm)



Deadbolt latch faceplate



Latch bolt faceplate



MDS Series list prices

Product name	Product description	Finish	Voltage	UPC	List price
MDS100-32D	E-strike - 1" deep; 5 face plates	630/US32D	12/24 VDC	043156645985	\$520.00
MDS100-F-32D	E-strike - 1" deep; 5 face plates (Fire-rated)	630/US32D	12/24 VDC	043156646074	\$585.00
MDS100-LBM-32D	E-strike - 1" deep; 5 face plates with LBM	630/US32D	12/24 VDC	043156645992	\$620.00
MDS100-F-LBM-32D	E-strike - 1" deep; 5 face plates with LBM (Fire-rated)	630/US32D	12/24 VDC	043156646081	\$685.00
MDSFP-KIT-10B	5 piece extra faceplate kit	613/US10B	N/A	043156646005	\$55.00
TBR-100	Timer-buzzer rectifier with surge protection for strikes and other access control components	N/A	N/A	043156651740	\$49.00
ESTK-100	E-strike - metal template kit (CS, MDS, RS)	N/A	N/A	043156072842	\$125.00

RS Series

200 and 300 models

The RS Series of surface mounted electric rim strikes are designed with endurance and flexibility. Available to accommodate rim exit devices with a 1/2" or 3/4" throw pullman latch bolt and multiple spacers are included for superior installation. Four attachment points to the frame provide for extra durability.



Features and benefits

- Surface mounted for easy installation
- Slotted mounting holes for increased adjustment flexibility
- Multiple spacers included for easy installation
- Sleek cover case design
- Field selectable fail-safe and fail-secure (fail-secure default), with simple and easy screw position change, non-fire rated models
- Field selectable 12/24 VDC
- Built-in voltage spike suppressor
- Suitable for rain or dust environments

Options

- RS200 Series accepts 1/2" throw pullman latch bolt
- RS300 Series accepts 3/4" throw pullman latch bolt
- Latch bolt monitoring available
- Offered in both 630/US32D and 613/US10B finishes
- RS300 available in fire rated version

Accessories

- Buzzer rectifier with timer (TBR-100)
- Metal template kit

Specifications

- UL1034 Burglary-resistant electric locking mechanisms, listed
- UL294 (indoor), listed
- UL10C Fire Rated, 90 min. RS300-F models only
- Static strength of 1500 lb. static load, UL certified
- Dynamic strength of 70 ft.-lb. dynamic load, UL certified
- 250,000 cycles endurance, UL certified

Electrical

- Dual-voltage 12 VDC @ .54A / 24 VDC @ .27A

Finishes



630/US32D
Satin stainless steel




613/US10B
Dark bronze


RS Series
200 and 300 models

Spacers

Included with strike and sold separately.



Strike dimensions



RS Series list prices

Product name	Product description	Finish	Voltage	UPC	List price
RS200-32D	Rim strike - 1/2" depth with spacers	630/US32D	12/24 VDC	043156646029	\$475.00
RS200-10B	Rim strike - 1/2" depth with spacers	613/US10B	12/24 VDC	043156646036	\$520.00
RS200-LBM-US32D	Rim strike - 1/2" depth with spacers and LBM	630/US32D	12/24 VDC	043156001484	\$580.00
RS200-LBM-US10B	Rim strike - 1/2" depth with spacers and LBM	613/US10B	12/24 VDC	043156001491	\$625.00
RS300-32D	Rim strike - 3/4" depth with spacers	630/US32D	12/24 VDC	043156646050	\$485.00
RS300-10B	Rim strike - 3/4" depth with spacers	613/US10B	12/24 VDC	043156646067	\$530.00
RS300-LBM-US32D	Rim strike - 3/4" depth with spacers and LBM	630/US32D	12/24 VDC	043156001521	\$590.00
RS300-LBM-US10B	Rim strike - 3/4" depth with spacers and LBM	613/US10B	12/24 VDC	043156001538	\$635.00
RS300-F-32D	Fire rated rim strike - 3/4" depth with spacers	630/US32D	12/24 VDC	043156001552	\$550.00
RS300-F-10B	Fire rated rim strike - 3/4" depth with spacers	613/US10B	12/24 VDC	043156001569	\$595.00
RS300-F-LBM-US32D	Fire rated rim strike - 3/4" depth with spacers and LBM	630/US32D	12/24 VDC	043156001583	\$655.00
RS300-F-LBM-US10B	Fire rated rim strike - 3/4" depth with spacers and LBM	613/US10B	12/24 VDC	043156001590	\$700.00
RS SPACER - US32D	Rim strike spacer - US32D	630/US32D	N/A	043156087433	\$45.00
RS SPACER - US10B	Rim strike spacer - US10B	613/US10B	N/A	043156096336	\$55.00
ESTK-100	E-strike - metal template kit (CS, MDS, RS)	N/A	N/A	043156072842	\$125.00

Access control accessories




Pushbuttons

Illuminated pushbuttons

The push to exit button series combines the most popular buttons in one box.
The IPB Series is packaged with multiple lens options and switches for flexibility.

IPB-100, IPB-100-N



Features and benefits

- LED illuminated push button
- 12/24 VDC, switch contact rated @ 5A /125 VAC
- Includes 3 lenses: Red/Green - "Push to Exit"; Blue - Handicap logo
- 2" square push button on single gang plate; 1 1/2" square push button on narrow stile plate
- Switch mounted on stainless steel single gang or narrow stile plate
- Momentary action switch
- S.P.D.T. and D.P.D.T. switches included

IPB-300, IPB-300-N



Features and benefits

- LED illuminated mushroom-style round push button
- Red and green lenses included
- 12/24 VDC, S.P.D.T. switch contact rated @ 5A/125VAC
- Single gang and narrow stile plate available
- Ideal for request-to-exit applications to release electromagnetic locks
- Fits standard stainless steel single gang surface or recessed electrical boxes (except narrow stile switches)
- Narrow stile model includes narrow black plastic electrical box

Metal pushbuttons

The metal push to exit button provides increased security with a durable and stylish appearance.

MPB-100, MPB-100-N

Features and benefits

- Vandal resistant brass nickel plated push button
- Labeled "PUSH TO EXIT"
- Momentary action switch
- 12/24 VDC, S.P.D.T. switch contact rated @ 5A/125VAC
- Aluminum single gang and narrow stile plate available



Options

Product name	Product description	UPC	List price
IPB-100	LED illuminated 2" button; 3 lenses; S.P.D.T. and D.P.D.T. switches included	043156651351	\$65.00
IPB-100-N	LED illuminated 2" button; 3 lenses; S.P.D.T. and D.P.D.T. switches included; Narrow plate	043156001644	\$65.00
IPB-300	LED illuminated mushroom style round button; 2 lenses; S.P.D.T. switch	043156651375	\$109.00
IPB-300-N	LED illuminated mushroom style round button; 2 lenses; S.P.D.T. switch; Narrow plate	043156651382	\$109.00
MPB-100	Metal button; 'Push to Exit'; S.P.D.T. switch	043156651405	\$109.00
MPB-100-N	Metal button; 'Push to Exit'; S.P.D.T. switch; Narrow plate	043156651399	\$109.00

Specialty switches

Touch switch

The touch **switch** is a cap sense style switch. There is no movable action in the switch, but instead only a touch is required to operate it. The illuminated bi-color LED provides easy status indication.

TS-100, TS-100-N




Features and benefits

- Dual LED (Red/Green) indicates inactive/active status
- 12/24 VDC, S.P.D.T. switch contacts rated @ 2A/30VAC
- Programmable timer output 1-40 sec, adjustable
- Available in stainless steel single gang or narrow stile plate
- Narrow stile model includes narrow black plastic electrical box

Wave switch

The touchless wave **switch** series is ideal for request-to-exit situations where a sanitary environment is desired such as healthcare facilities, restaurants, restrooms or labs.

WS-200, WS-200-MB



Features and benefits

- Infrared sensor technology for no contact switch activation
- Sensor detection range up to approximately 4"
- Dual LED (Red/Green) indicates inactive/active status
- Time delay settable for 0.5, 5, 10 or 20 seconds
- 12/24 VDC, S.P.D.T. switch contacts rated @ 2A/30VAC
- Single gang stainless steel, weather resistant and vandal resistant faceplate
- Operating temperature range is -10° F to +130° F
- Available in flush or surface mount with metal box

TS Series/WS Series list prices

Product name	Product description	UPC	List price
TS-100	Dual LED status indicator with programmable timer; S.P.D.T. switch	043156651498	\$125.00
TS-100-N	Dual LED status indicator with programmable timer; S.P.D.T. switch; Narrow plate	043156651504	\$125.00
WS-200	Touchless infrared sensor switch activation with dual LED and time delay; S.P.D.T. switch	043156651511	\$125.00
WS-200-MB	Touchless infrared sensor switch activation with dual LED and time delay; S.P.D.T. switch; Metal box included	043156651528	\$135.00

Digital keypads

Digital keypads

The DKP Series keypads are designed for simple access control or code control for up to four individual devices. These keypads are a great choice for controlling electric strikes, electromagnetic locks, security systems or other types of openings requiring on/off or momentary control outputs.

DKP-165, DKP-165-S, DKP-165-FM and DKP-NS



Dimensions

DKP-165

4 ³/₄" x 3" x 1 ³/₈"
(120mm x 76mm x 34.9mm)

DKP-165-S

4 ¹⁵/₁₆" x 4 ¹/₈" x 2 ³/₈"
(125mm x 105mm x 60mm)

DKP-165-FM

4 ³/₄" x 3 ¹⁵/₁₆" x 1 ¹/₂"
(120mm x 100mm x 37.4mm)

DKP-NS

1 ¹¹/₁₆" x 5 ⁷/₈" x 1 ¹⁵/₁₆"
(43.2mm x 149.9mm x 24.1mm)

DKP-165 Series features and benefits

- Fully programmable with up to 480 users with 1 to 6 digit user codes
- Keys are back-lit for visibility in dark areas with audible and visual key press feedback
- 12/24 VDC, switch contacts rated @ 2A/30VAC/VDC
- Multi-colored LEDs indicate the state of the keypad
- Timed anti-pass back
- 302 stainless steel gang plate
- Operating temperature range is -10° F to +130° F
- Available in surface mount (DKP-165-S) or flush mount (DKP-165-FM)
- Tamper resistant screws included for faceplate (DKP-165-S only)
- Designed for indoor use (DKP-165)

DKP-NS Series features and benefits

- Designed for outdoor use
- Allows for up to 1010 user codes (zone 1: 1000 users, zone 2: 10 users)
- 12/24 VAC/VDC
- Incorporates a tamper alarm feature as a standard option
- Relock time 0-99 s
- Two-zone feature provides 2 relays and 2 exit button outputs for two-zone applications
- Backlit numbers allow for ease of use in dimly-lit areas (Blue keypad illumination)
- Operating temperature -22°F – 158°F
- IP66 Rating: waterproof, dust proof

DKP Series list prices

Product name	Product description	UPC	List price
DKP-165	Indoor digital keypad; Up to 480 users with timed anti-pass back	043156651634	\$110.00
DKP-165-S	Digital keypad; Surface mount with case; Up to 480 users with timed anti-pass back	043156651641	\$175.00
DKP-165-FM	Digital keypad; Flush mount; Up to 480 users with timed anti-pass back	043156651658	\$150.00
DKP-NS	Outdoor digital keypad; Up to 1,010 users with two zone, re-locking time delay	043156081189	\$209.00

Touch bars

Touch bar

The touch bar is a request to exit device, usually installed as a redundancy to other access control devices for non-fire rated indoor doors.

TB-36, TB-42, TB-48



Features and benefits

- Low operating force, minimal bar travel
- Non-latching
- 12/24 VDC, includes two S.P.D.T. switches for positive redundant operation
- Field reversible and easily installed on all types of doors
- Heavy duty clear anodized satin aluminum construction
- Includes 'Push to Exit' sticker
- Available in three lengths - 36", 42" and 48"
- Available in 628/US28 Aluminum finish

TB Series list prices

Product name	Product description	Finish	UPC	List price
TB-36	Touch bar - 36" door	628/US28	043156651467	\$189.00
TB-42	Touch bar - 42" door	628/US28	043156651474	\$239.00
TB-48	Touch bar - 48" door	628/US28	043156651481	\$239.00

Push plates

Push plates

The PPH Series of push plates are dependable, responsive and easy to install stainless steel switches. These assisted door controls are ideal for a broad range of door automation.

PPH-100-PL, PPH-100-AL,
PPH-200-LED, PPH-50



Features and benefits

- Stainless steel faceplate with engraved text and anodized finish
- Tamper resistant mounting
- Designed for use in high traffic areas
- Mounts on a standard double gang electrical box, except PPH-50
- Red/Blue LED ring available (PPH-200-LED)

PPH-100-PL
D.P.D.T. switch contacts rated 15A @ 125 or 250 VAC
5 1/8" x 5 1/8" x 2 3/4" - Includes box
(130mm x 130mm x 70mm)

PPH-200-LED
S.P.D.T. switch contacts rated
0.5A @ 120 VAC or 1A @ 24 VDC
5 1/8" x 5 1/8" x 1 3/4" - includes box
(133mm x 133mm x 45mm)

PPH-100-AL
D.P.D.T. switch contacts rated
5A @ 125 or 250 VAC
4 1/2" x 4 1/2" x 2 3/4" - includes box
(115mm x 115mm x 69.5mm)

PPH-50
12/24 VDC, S.P.D.T. switch
contacts rated @ 5A/125VAC,
3A/250VAC
4 1/2" x 1 3/4" x 1 3/4"
(114.3mm x 44.4mm x 44.4mm)

PPH Series list prices

Product name	Product description	UPC	List price
PPH-100-PL	Large round push plate w/black box; Stainless steel faceplate with D.P.D.T. switch	043156651412	\$109.00
PPH-100-AL	Large round push plate w/aluminum box; Stainless steel faceplate with D.P.D.T. switch	043156651429	\$129.00
PPH-200-LED	Illuminated dual color large square push plate w/black box; Stainless steel faceplate with S.P.D.T. switch	043156651443	\$149.00
PPH-50	Rectangular narrow push plate w/black box; Stainless steel faceplate with S.P.D.T. switch	043156651450	\$79.00

Emergency breaks

Emergency break


The resettable EGB Series are call points that can be activated without a power supply during emergencies. They are typically located on fire escape doors. The main function is to override an electrical locking device in case of emergency. A provided key allows the unit to be reset to normal mode.

EGB-100-G, EBG-100-R



Features and benefits

- 12/24 VDC, D.P.D.T. switch contacts rated @ 5A/125VAC
- Available in green or red case
- Detachable terminal block for easy installation
- Built-in 80db buzzer
- Blue back light
- Non-glass, durable plastic unit, making it suitable for high traffic areas
- Resettable key included and available to order as a replacement part (EGB-KEY)
- Replacement cover available (EGB-COV)



Detachable terminal block

EGB Series list prices

Product name	Product description	UPC	List price
EGB-100-G	Resettable emergency call point station with green case; Includes blue back light, built-in buzzer and D.P.D.T. switch	043156651597	\$120.00
EGB-100-R	Resettable emergency call point station with red case; Includes blue back light, built-in buzzer and D.P.D.T. switch	043156651603	\$120.00
EGB-KEY	Replacement and resettable key	043156651610	\$10.00
EGB-COV	Replacement clear plastic cover	043156651627	\$10.00

Door cords

Door cords

Door cords offer a protective conduit for running wires from the frame to the door installed with electrical devices such as electrified locks. The cords are available in various lengths and finishes.

DC-HD-16, DC-AL-20,
DC-BR-20, DC-PL-12,
DC-PL-20, DC-HD-16-10B

Features and benefits

- Door loops available in 12", 16" and 20" in length
- Stainless steel cable resists abrasion and damage
- Silver and brown (DC-BR-20 and DC-HD-16-10B) finish available to match doors and frames
- Surface mount
- Mounting hardware included



Heavy duty - DC-HD-16/DC-HD-16-10B with large, durable aluminum boxes for extra protection

Inside loop diameter: $\frac{3}{8}$ "
Outside loop diameter: $\frac{1}{2}$ "



Medium duty - DC-AL-20/DC-BR-20 with aluminum end caps for increased durability

Light duty - DC-PL-12/DC-PL-20 with plastic end caps
Inside loop diameter: $\frac{5}{16}$ "
Outside loop diameter: $\frac{7}{16}$ "

DC Series list prices

Product name	Product description	UPC	List price
DC-HD-16	Heavy duty door cord with aluminum boxes; Stainless steel cable; 16" length	043156651559	\$39.00
DC-HD-16-10B	Heavy duty door cord with aluminum boxes; Stainless steel cable; 16" length; 613/US10B	043156081097	\$49.00
DC-AL-20	Medium duty door cord with aluminum end caps; Stainless steel cable; 20" length	043156651566	\$27.00
DC-BR-20	Medium duty door cord with aluminum end caps; Stainless steel cable; 613/US10B	043156001651	\$32.00
DC-PL-12	Light duty door cord with silver plastic end caps; Stainless steel cable; 12" lengths	043156651573	\$22.00
DC-PL-20	Light duty door cord with silver plastic end caps; Stainless steel cable; 20" lengths	043156651580	\$22.00

Specialty sensor and buzzer switches

Timer-buzzer rectifier

The TBR is a multi-functional device made to serve as an added layer of security or convenience for your access control system. The TBR offers a delay timer, buzzer and AC to DC rectifier all in one package.

TBR-100



Features and benefits

- Built-in surge protection
- Input 12/24 VAC, outputs 1A/12VDC
- Built-in 80db buzzer
- Selectable re-lock time (5, 15, 30 or 60 seconds)
- Red LED output indicator

EMS Series

This versatile sensor can be surface mounted above any door, ceiling or wall for request to exit applications. The EMS Series, Passive Infrared (PIR) Sensor, has the flexibility and low profile design to make it an effective sensor for managing building security and traffic flow.

EMS-100



Features and benefits

- Operating voltage: 12/24 VDC
- Sensing field adjustment masks provide accurate detection zones
- Compact, aesthetically pleasing design
- Includes ceiling and surface mount adapters
- Operating temperature range is -20° F to +130° F

Specialty sensor
and buzzer switches

CSW Series

The CSW Series of switches were designed for a concealed desk application. They are used to release an electric lock or device from a remote location. The CSW Series currently operates via momentary action toggle switches that can be surface mounted.

CSW-100, CSW-200



Features and benefits

- Made from PVC material
- CSW-100 - flush mount
- CSW-200 - surface mount
- S.P.D.T. switch
- Momentary toggle action

Wireless release kit (1 receiver, 2 transmitters)

The 900MHz receiver and transmitters allow wireless activation of electronic **access-controlled** doors. With two outputs, several doors can be controlled at the same time or with slight delay.

WRT-K, WT-2



Features and benefits

- Includes 1 receiver and 2, 1 button standard transmitters
- Colored LEDs indicate transmitter activation, frequency and signal strength
- Receiver will accept up to 75 transmitters
- Frequency hopping allows consistent transmission in areas with other 900 MHz devices
- A battery-powered, hardwired transmitter is ideal for push plate applications
- Extended hold functionality is integrated for various applications needs
- Operating Temperature -22°F to 158°F (-30°C to 70°C)
- Conformance: FCC, IC, HH: IP65/NEMA 4

Options

Product name	Product description	UPC	List price
TBR-100	Timer-buzzer rectifier with surge protection for strikes and other access control components	043156651740	\$49.00
EMS-100	Exit motion sensor with ceiling and surface mount adapters	043156651535	\$160.00
CSW-100	Flush mount concealed desk release; S.P.D.T. switch	043156651542	\$38.00
CSW-200	Surface mount concealed desk release; S.P.D.T. switch; Narrow stile	043156001637	\$38.00
WRT-K	Wireless receiver and transmitter (2) kit	043156081165	\$149.00
WT-2	Wireless transmitter (2) sold separate	043156081172	\$95.00

Power supplies

LP Series

150 and 250 models

The LP Series of power supplies include a 1.5 amp and 2.5 amp option to power various electronic access control devices and most single or double door applications. This line of UL294 certified, Class 2 power supplies have field selectable output voltage, a built-in charger for battery backup and the ability for fire alarm integration. Field replacement is simple with an industry common power supply board footprint and power can be easily managed with the addition of the RDB4 option board.

LP150, LP250



Features and benefits

- Amperage: 1.5 AMPS/2.5 AMPS
- Input voltage: 120 VAC / 60Hz
- Output voltage: Field selectable output voltage 12/24 VDC
- Battery backup circuitry included
- Designed with fire alarm integration, if desired
- Visual LED indicators: AC input status, DC output status, battery back up status
- Protective cover over the AC components

Certifications include:

- UL294, UL603, Class 2, FCC Part 15, CSFM, RoHS and CSA-C22.2 NO.205

Accessories

- RDB4 Option Board is a four output relay distribution board (sold separately)
- LP150B 1.5 AMP board only
- LP250B 2.5 AMP board only

LP Series list prices

Product name	Product description	UPC	List price
LP150	1.5 amp power supply with enclosure	043156085743	\$185.00
LP150B	1.5 amp power supply - board only	043156085781	\$105.00
LP250	2.5 amp power supply with enclosure	043156085750	\$245.00
LP250B	2.5 amp power supply - board only	043156085798	\$175.00
LP250RDB4	2.5 amp power supply and 4 output relay distribution option board with enclosure	043156085767	\$296.00
RDB4	4 output relay distribution option board - board only	043156085774	\$60.00

Warranty information

Limited product warranty

Schlage Lock Company, LLC (the “Company”) extends a limited warranty against defects in material and workmanship to the original user of the Locknetics® branded products manufactured by the Company (the “Products”) beginning from the date of purchase by the original user pursuant to the terms below. Certain Products contain restrictions to this limited warranty, additional warranties, or different warranty periods. Please see below for specific Product limited warranty periods and details. This warranty only applies to Locknetics branded products purchased on or after September 1, 2017.

Product	Warranty period	Product	Warranty period
Locknetics electromagnetic locks	5 years	Locknetics access control accessories	3 years
Locknetics electric strikes	5 years	Locknetics power supplies*	5 years

* This warranty applies to Locknetics branded power supplies purchased on or after July 1, 2019.

What the Company will do: Upon return of the defective Product to the Company or its authorized distributor for inspection, free and clear of all liens and encumbrances and accompanied by the statement of defects and proof of purchase, the company will, at its option, repair or replace the Product (with new or re-manufactured product (as applicable), or refund the purchase price.

Original user: These limited warranties only apply to the original end user of the Products (“Original User”). These warranties are not transferable.

What is not covered: The following costs, expenses and damages are not covered by the provisions of these limited warranties: (i) back charges or labor costs including, but not limited to, such costs as the removal and re-installation of the Product or for normal maintenance; (ii) shipping and freight expenses required to return the Product to Company; (iii) failures, defects, or damage (including, but not limited to, any security failure or loss of data) caused by any third party product, service, or system connected or used in conjunction with the Product; (iv) any other incidental, consequential, indirect, special and/or punitive damages, whether based on contract, warranty, tort (including, but not limited to, strict liability or negligence), patent infringement, or otherwise, even if advised of the possibility of such damages; or (vi) normal wear and tear.

The provisions of these limited warranties do not apply to Products: (i) used for purposes for which they are not designed or intended by the Company; (ii) which have been subjected to alteration, misuse, abuse, negligence, or accident; (iii) which have been improperly stored, installed, maintained, repaired or operated; (iv) which are not the proper size for the application, have been used in violation of written instructions provided by the Company, or have been installed with improper or incorrect parts; (v) which have been subjected to improper temperature, humidity, or other environmental conditions (i.e., corrosion); or (vi) which, based on the Company’s examination, do not disclose to the Company satisfactory non-conformance to these warranties. Additionally, these warranties do not cover scratches, abrasions, or deterioration due to the use of paints, solvents, or other chemicals.

Additional terms: The Company does not authorize any person to create for it any obligation or liability in connection with the Products. No other warranties, express or implied, are made to the Original User with respect to the Products including, but not limited to, any implied warranty of merchantability or fitness for a particular purpose. No agent, representative, dealer, or distributor of Company has the authority to increase or alter the obligations under this limited warranty. No action arising out of a claimed breach of this warranty by Company may be brought by the Original User more than one (1) year after the cause of action has arisen.

How local law applies: This limited warranty gives you specific rights, and you may also have other rights as otherwise permitted by law. If these Products are considered a consumer product, some local laws do not allow limitations on incidental or consequential damages or how long an implied warranty lasts, so the above limitations may not fully apply. Refer to your local laws for your specific rights under this limited warranty.

Claims process: If you have a claim under this limited warranty, please contact Company’s Customer Service for repair, replacement or refund of the original purchase price in exchange for the return of the Product to Company. Contact Company’s Customer Service at US 1-877-671-7011 or Canada 1-800-900-4734.

Weight, case quantity and pricing charts

Electromagnetic locks

WMG Series

Product name	UPC	Master carton quantities	Master carton weight (lb)*	Product weight (lb)*	US list price
WFP50	043156646128	75	14.3	0.19	\$25.00
WFP63	043156646135	50	11.5	0.23	\$25.00
WLBK1200	043156646166	10	7.5	0.75	\$63.00
WLBK600	043156646111	10	4.9	0.49	\$58.00
WMG1200	043156646142	3	16.3	5.43	\$470.00
WMG600	043156646098	5	16.2	3.24	\$370.00
WZBK1200	043156646159	10	15	1.5	\$140.00
WZBK600	043156646104	10	10.5	1.05	\$135.00

MG Series

Product name	UPC	Master carton quantities	Master carton weight (lb)*	Product weight (lb)*	US list price
MG600	043156646173	6	13.3	2.22	\$159.00
MG600DT	043156646180	6	13.5	2.25	\$184.00
MG600-2	043156081103	3	15	5	\$295.00
MG600DT-2	043156081110	3	15	5	\$375.00
MLBK600	043156646210	12	7	0.58	\$50.00
MZBK600	043156646197	15	11.7	0.78	\$100.00
MG1200	043156646241	3	14.9	4.97	\$239.00
MG1200DT	043156646258	3	14.9	4.97	\$264.00
MG1200-2	043156081127	1	11	11	\$425.00
MG1200DT-2	043156081134	1	11	11	\$490.00
MLBK1200	043156646289	20	6	0.3	\$57.00
MZBK1200	043156646265	10	13.8	1.38	\$115.00
MUBK	043156646203	20	14.2	0.71	\$65.00
MFP50	043156646234	80	14.6	0.18	\$18.00
MFP63	043156646227	60	13.6	0.23	\$23.00

Electric strikes

CS Series

Product name	UPC	Master carton quantities	Master carton weight (lb)*	Product weight (lb)*	US list price
CS450-32D	043156645893	14	9	0.64	\$170.00
CS450-LBM-32D	043156645909	14	9.2	0.66	\$239.00
CS750-32D	043156645961	14	9	0.64	\$170.00
CS750-LBM-32D	043156645978	14	9.2	0.66	\$239.00
CSFP-KIT-10B	043156645916	100	14	0.14	\$38.00
CCFP-KIT-32D	043156087365	100	14.5	0.15	\$38.00
CCFP-KIT-10B	043156087358	100	14.5	0.15	\$48.00
CWFP-KIT-32D	043156645923	100	15.5	0.16	\$38.00
CWFP-KIT-10B	043156645930	100	15.5	0.16	\$48.00
CSLE-.5	043156087372	150	6	0.04	\$50.00
CSLE-1	043156645947	100	5.8	0.06	\$50.00
CSLE-2	043156645954	50	5.3	0.11	\$50.00

MDS Series

Product name	UPC	Master carton quantities	Master carton weight (lb)*	Product weight (lb)*	US list price
MDS100-32D	043156645985	14	14	1	\$520.00
MDS100-F-32D	043156646074	14	14	1	\$585.00
MDS100-LBM-32D	043156646081	14	14	1	\$620.00
MDS100-F-LBM-32D	043156645992	14	14	1	\$685.00
MDSFP-KIT-10B	043156646005	50	11.5	0.23	\$55.00

* Weight is approximate and subject to change without notice.

Weight, case quantity and pricing charts (continued)

Electric strikes

NC Series					
Product name	UPC	Master carton quantities	Master carton weight (lb)*	Product weight (lb)*	US list price
NC450	043156087389	14	10	0.71	\$215.00
NC450-LBM	043156104895	14	10.2	0.73	\$284.00
NCFP-KIT-10B	043156087396	100	16	0.16	\$48.00
NCCFP-KIT-32D	043156087457	100	15	0.15	\$38.00
NCCFP-KIT-10B	043156087440	100	15	0.15	\$48.00
NCWFP-KIT-32D	043156087419	100	16	0.16	\$38.00
NCWFP-KIT-10B	043156087402	100	16	0.16	\$48.00
NC-RAMPS	043156087426	100	11.5	0.12	\$65.00

RS Series					
Product name	UPC	Master carton quantities	Master carton weight (lb)*	Product weight (lb)*	US list price
RS200-US32D	043156646029	10	10.3	1.03	\$475.00
RS200-US10B	043156646036	10	10.3	1.03	\$520.00
RS200-LBM-US32D	043156001484	10	12	1.2	\$580.00
RS200-LBM-US10B	043156001491	10	12	1.2	\$625.00
RS300-F-US32D	043156001552	10	12	1.2	\$550.00
RS300-F-US10B	043156001569	10	12	1.2	\$595.00
RS300-F-LBM-US32D	043156001583	10	12.5	1.25	\$655.00
RS300-F-LBM-US10B	043156001590	10	12.5	1.25	\$700.00
RS300-US32D	043156646050	10	12	1.2	\$485.00
RS300-US10B	043156646067	10	12	1.2	\$530.00
RS300-LBM-US32D	043156001521	10	12.5	1.25	\$590.00
RS300-LBM-US10B	043156001538	10	12.5	1.25	\$635.00
RS SPACER-US32D	043156087433	63	15.5	0.25	\$45.00
RS SPACER-US10B	043156096336	63	15.5	0.25	\$55.00

Accessories

Pushbuttons					
Product name	UPC	Master carton quantities	Master carton weight (lb)*	Product weight (lb)*	US list price
IPB-100	043156651351	54	10.8	0.2	\$65.00
IPB-100-N	043156001644	54	10.8	0.2	\$65.00
IPB-300	043156651375	50	10	0.2	\$109.00
IPB-300-N	043156651382	50	8	0.16	\$109.00
MPB-100	043156651405	50	8.2	0.16	\$109.00
MPB-100-N	043156651399	50	9	0.18	\$109.00

Specialty switches					
Product name	UPC	Master carton quantities	Master carton weight (lb)*	Product weight (lb)*	US list price
TS-100	043156651498	50	9	0.18	\$125.00
TS-100-N	043156651504	50	9	0.18	\$125.00
WS-200	043156651511	36	6.35	0.18	\$125.00
WS-200-MB	043156651528	36	11.5	0.32	\$135.00

Digital keypads					
Product name	UPC	Master carton quantities	Master carton weight (lb)*	Product weight (lb)*	US list price
DKP-165	043156651634	50	9	0.18	\$110.00
DKP-165-FM	043156651658	18	7.38	0.41	\$150.00
DKP-165-S	043156651641	18	8.5	0.47	\$175.00
DKP-NS	043156081189	25	3.175	0.13	\$209.00

* Weight is approximate and subject to change without notice.

Weight, case quantity and pricing charts (continued)

Accessories

Touchbars

Product name	UPC	Master carton quantities	Master carton weight (lb)*	Product weight (lb)*	US list price
TB-36	043156651467	4	13	3.25	\$189.00
TB-42	043156651474	4	14.5	3.63	\$239.00
TB-48	043156651481	4	16	4	\$239.00

Pushplates

Product name	UPC	Master carton quantities	Master carton weight (lb)*	Product weight (lb)*	US list price
PPH-100-AL	043156651429	12	10	0.83	\$129.00
PPH-100-PL	043156651412	18	11.3	0.63	\$109.00
PPH-200-LED	043156651443	20	8.6	0.43	\$149.00
PPH-50	043156651450	50	11	0.22	\$79.00

Emergency glass breaks

Product name	UPC	Master carton quantities	Master carton weight (lb)*	Product weight (lb)*	US list price
EGB-100-G	043156651597	40	10.7	0.27	\$120.00
EGB-100-R	043156651603	40	10.7	0.27	\$120.00
EGB-COV	043156651627	100	5.8	0.06	\$10.00
EGB-KEY	043156651610	150	3.9	0.03	\$10.00

Door cords

Product name	UPC	Master carton quantities	Master carton weight (lb)*	Product weight (lb)*	US list price
DC-HD-16	043156651559	30	6.4	0.21	\$39.00
DC-HD-16-10B	043156081097	30	6.4	0.21	\$44.00
DC-AL-20	043156651566	50	5.6	0.11	\$27.00
DC-BR-20	043156001651	50	5.6	0.11	\$32.00
DC-PL-12	043156651573	200	14.8	0.07	\$22.00
DC-PL-20	043156651580	50	5	0.1	\$22.00

Specialty sensor and buzzer switches

Product name	UPC	Master carton quantities	Master carton weight (lb)*	Product weight (lb)*	US list price
TBR-100	043156651740	100	7.9	0.08	\$49.00
EMS-100	043156651535	20	5.23	0.26	\$160.00
CSW-100	043156651542	45	4.7	0.1	\$38.00
CSW-200	043156001637	45	4.2	0.09	\$38.00
WRT-K	043156081165	25	6.5	0.26	\$149.00
WT-2	043156081172	100	13.61	0.14	\$95.00

Power supplies

Product name	UPC	Master carton quantities	Master carton weight (lb)*	Product weight (lb)*	US list price
LP150	043156085743	4	15.43	3.86	\$185.00
LP150B	043156085781	35	11.11	0.32	\$105.00
LP250	043156085750	4	15.43	3.86	\$245.00
LP250B	043156085798	35	12.75	0.36	\$175.00
LP250RDB4	043156085767	4	15.43	3.86	\$296.00
RDB4	043156085774	90	12.25	0.14	\$60.00

* Weight is approximate and subject to change without notice.

About Allegion

Allegion (NYSE: ALLE) is a global pioneer in safety and security, with leading brands like CISA®, Interflex®, LCN®, Schlage®, SimonsVoss® and Von Duprin®. Focusing on security around the door and adjacent areas, Allegion produces a range of solutions for homes, businesses, schools and other institutions. Allegion is a \$2 billion company, with products sold in almost 130 countries.

For more, visit www.allegion.com

KRYPTONITE ■ LCN ■  ■ STEELCRAFT ■ VON DUPRIN