


# WALL PLATES, INSERTS & ENCLOSURES GUIDE

On-Q  
Connectivity



designed to be better.™

 **legrand**®

# SUPERIOR INFRASTRUCTURE SOLUTIONS



CONNECTIVITY



As the industry leader in structured wiring, Legrand provides the proven, practical solutions preferred by installers and major home builders across the country. Our comprehensive product offering — which includes On-Q wall plates, jacks, straps, tools, modules and enclosures — simplifies installations and reduces time on site. We specialize in meeting the right specifications for any project — residential or light commercial — with solutions that exceed your needs. From single-family homes to apartments, townhomes to condominiums, Legrand has the professional answer for any project.

## HDMI

This full line of High-Speed HDMI with Ethernet products — which includes cables, couplers, repeaters and extenders — delivers an unparalleled HD audio and video experience. All of our HDMI cables are CL-3 and in-wall UL-rated.





### WALL PLATES & INSERTS

Our line of Keystone wall plates; Cat 5e, Cat 6, Cat 6a, F Connectors; speaker binding posts; and RCA inserts provides flexible setup options anywhere in the home.

### DECORATOR STRAPS

We offer a series of pre-configured outlet straps for data, phone, video and home theater applications. Add a home theater strap to enable HD audio and video with a few simple connections, or quickly wire a home office using our pre-configured outlet straps that combine phone, data and video into a single decorator opening.


### ENCLOSURES

Our durable enclosures range in size from 12 to 42 inches to suit any installation. Every enclosure is made in the USA and is compatible with all major module mounting schemes. They offer three 2.5 inch top openings for high capacity projects, as well as side lances and tabs for greater flexibility during installation. Available with hinged or screw-on doors, an On-Q enclosure is the easy choice for professional projects.



# HDMI

## AC2MXX-BK High-Speed HDMI Cables with Ethernet



AC2M01-BK

PART NO.	DESCRIPTION
AC2M00-BK	0.7 Meter High-Speed HDMI cable w/Ethernet
AC2M01-BK	1 Meter High-Speed HDMI cable w/Ethernet
AC2M02-BK	2 Meter High-Speed HDMI cable w/Ethernet
AC2M03-BK	3 Meter High-Speed HDMI cable w/Ethernet
AC2M04-BK	4 Meter High-Speed HDMI cable w/Ethernet
AC2M05-BK	5 Meter High-Speed HDMI cable w/Ethernet
AC2M07-BK	7.5 Meter High-Speed HDMI cable w/Ethernet
AC2M10-BK	10 Meter High-Speed HDMI cable w/Ethernet
AC2M15-BK	15 Meter High-Speed HDMI cable w/Ethernet
AC2M20-BK	20 Meter High-Speed HDMI cable w/Ethernet

- DELIVERS UNCOMPRESSED HD VIDEO AND DIGITAL AUDIO IN A SINGLE CABLE
- AUDIO RETURN CHANNEL (ARC) AND HDMI ETHERNET CHANNEL (HEC) CAPABLE
- COMPATIBLE WITH HDTVS, DVD/BLU-RAY PLAYERS, CABLE & SATELLITE SET TOP BOXES, AND GAMING CONSOLES
- GOLD-PLATED CONNECTORS WITH INDIVIDUALLY SHIELDED CONDUCTORS ENSURE MAXIMUM RESOLUTION

## AC3MXX-WH-V1 High-Speed HDMI with Ethernet Slimline Cables



AC3MXX-WH-v1

PART NO.	DESCRIPTION
AC3M01-WH-V1	1 Meter High-Speed HDMI w/ Ethernet Slimline Cable
AC3M02-WH-V1	2 Meter High-Speed HDMI w/ Ethernet Slimline Cable
AC3M04-WH-V1	4 Meter High-Speed HDMI w/ Ethernet Slimline Cable


- 75% THINNER THAN REGULAR HDMI CABLES DELIVERS UNCOMPRESSED HD VIDEO AND DIGITAL AUDIO IN A SINGLE CABLE
- AUDIO RETURN CHANNEL & HDMI ETHERNET CHANNEL (HEC) CAPABLE
- REDUCED WEIGHT ALLOWS FOR A MORE SECURE CONNECTION TO TELEVISIONS AND OTHER COMPONENTS
- REDUCED CABLE PROFILE FOR A PROFESSIONAL UNCLUTTERED LOOK
- UTILIZES REDMERE™ SYNERCHIP FOR HIGH BANDWIDTH SUPPORT OVER DISTANCE

# HDMI

## HDBaseT HDMI Extender

**NEW!**


PART NO.	DESCRIPTION
AC1030	HDBaseT HDMI Extender
	<ul style="list-style-type: none"> <li>THE AC1030 KIT EXTENDS HDMI AND INTERNET SIGNALS UP TO 328 FEET USING CAT 5 OR CAT 6 WIRING. IT SUPPORTS 3D VIDEO AND 1080P RESOLUTION, WHILE DUAL IR TARGETS ALLOW THE SOURCE DEVICE TO RECOGNIZE REMOTE COMMANDS AT A SECONDARY LOCATION.</li> </ul>



## HDMI Accessories

**NEW!**


WP1011-WH



AC2100



AC2101

PART NO.	DESCRIPTION
WP1011-XX	Pre-Configured HDMI 2-Port Strap Colors: BK, LA, WH
AC2100	HDMI Repeater <ul style="list-style-type: none"> <li>CONNECTS TWO HDMI HIGH-SPEED WITH ETHERNET CABLES &amp; EXTENDS ETHERNET SIGNAL UP TO 20 FEET</li> </ul>
AC2101	HDMI Hinged Coupler <ul style="list-style-type: none"> <li>REDUCES CABLE BENDING FOR SUPERIOR ORGANIZATION</li> </ul>



# WALL PLATES & INSERTS

## KEYSTONE WALL PLATES



WP3401-WH\*



WP3402-WH\*



WP3403-WH



WP3404-WH



WP3406-WH



WP3212-WH



WP1194-WH

\*Available in packs of 25

PART NO.	DESCRIPTION
WP3401-XX (KTPD1XX)	1-Gang, 1-Port Wall Plate 25 Count Bulk Pack in WH (W) or LA (WP3401-XX-25)
WP3402-XX (KTPD2XX)	1-Gang, 2-Port Wall Plate 25 Count Bulk Pack in WH (W) or LA (WP3402-XX-25)
WP3403-XX (KTPD3XX)	1-Gang, 3-Port Wall Plate
WP3404-XX (KTPD4XX)	1-Gang, 4-Port Wall Plate
WP3406-XX (KTPD6XX)	1-Gang, 6-Port Wall Plate
WP3212-XX	2-Gang, 12-Port Wall Plate Colors: IV, LA and WH
WP1194-XX	1-Gang, Blank Wall Plate

COLORS: BK, BR, IV (I), LA, WH (W)  
DIMENSIONS: 1-GANG: 2.9375" x 4.6875" 2-GANG: 4.75" x 4.6875"

## KEYSTONE LABELED Wall Plates

PART NO.	DESCRIPTION
KTPDL1XX	1-Port Keystone Labeled Wall Plate
KTPDL2XX	2-Port Keystone Labeled Wall Plate
KTPDL3XX	3-Port Keystone Labeled Wall Plate
KTPDL4XX	4-Port Keystone Labeled Wall Plate
KTPDL6XX	6-Port Keystone Labeled Wall Plate

COLORS: I, LA, W

DIMENSIONS: 1-GANG: 2.9375" x 4.6875" 2-GANG: 4.75" x 4.6875"

## OVERSIZED WALL PLATES



WP3301-WH



WP3302-WH



WP3303-WH



WP3304-WH



WP3306-WH



WP3300-WH

PART NO.	DESCRIPTION
WP3301-XX	1-Gang, 1-Port Oversized Wall Plate
WP3302-XX	1-Gang, 2-Port Oversized Wall Plate
WP3303-XX	1-Gang, 3-Port Oversized Wall Plate
WP3304-XX	1-Gang, 4-Port Oversized Wall Plate
WP3306-XX	1-Gang, 6-Port Oversized Wall Plate
WP3300-XX	1-Gang, Blank Oversized Wall Plate

COLORS: WH, LA  
DIMENSIONS: 1-GANG: 3.3125" x 5.0625" 2-GANG: 5.125" x 5.0625"  
3-GANG: 6.9375" x 5.0625" 4-GANG: 8.75" x 5.0625"

### COLOR OPTIONS



BK BR IV (I) LA WH (W)

# WALL PLATES & INSERTS

## DECORATOR WALL PLATES



TP13W



TP26W



TP262W



TP263W



TP264W

PART NO.	DESCRIPTION
TP13XX <sup>†</sup> (WP1194-XX)	1-Gang Blank Wall Plate
TP26XX <sup>†</sup> (WP1205-XX)	1-Gang Decorator Wall Plate
TP262XX <sup>†</sup> (WP1207-XX)	2-Gang Decorator Wall Plate
TP263XX <sup>†</sup> (WP1208-XX)	3-Gang Decorator Wall Plate
TP264XX <sup>†</sup>	4-Gang Decorator Wall Plate

COLORS:

BK, BR, IV (I), LA, WH (W)

DIMENSIONS:

1-GANG: 2.9375" x 4.6875" 2-GANG: 4.75" x 4.6875"

## JUMBO DECORATOR Wall Plates

PART NO.	DESCRIPTION
TPJ13XX	Jumbo 1-Gang Blank Wall Plate
TPJ26XX	Jumbo 1-Gang Wall Plate
TPJ262XX	Jumbo 2-Gang Wall Plate
TPJ263XX	Jumbo 3-Gang Wall Plate

COLORS:

BK, I, LA, W

DIMENSIONS:

1-GANG: 3.3125" X 5.0625", 2-GANG: 5.125" X 5.0625", 3-GANG: 6.9375" X 5.0625"

## LOW VOLTAGE BRACKETS



AC1009-01



AC1009-02



AC1009-11



AC1010-01



AC1010-02



AC1010-03

PART NO.	DESCRIPTION
AC1009-01	1-Gang, LV Bracket w/Nail, New Construction
AC1009-02	2-Gang, LV Bracket, Face Mount, New
AC1009-11	1-Gang, LV Bracket, Face Mount, New
AC1010-01	1-Gang, LV Bracket, Retrofit
AC1010-02	2-Gang, LV Bracket, Retrofit
AC1010-03	3-Gang, LV Bracket, Retrofit

CRAFTED WITH DURABLE HEAVY-DUTY PLASTIC, ON-Q LV BRACKETS FEATURE AN OPEN BACK AND AN INTEGRATED CABLE MANAGEMENT SYSTEM FOR CLEAN CONNECTIONS AND EASY INSTALLATION

### COLOR OPTIONS



BK

BR

IV (I)

LA

WH (W)

# WALL PLATES & INSERTS

## TELEPHONE AND DATA Keystone Inserts



WP3475-WH\*



WP3476-WH



WP346A-WH



WP3450-WH\*



WP3460-WH



WP3458-WH



WP3451-WH



WP3425-WH



WP3550-WH



WP3560-WH

\* Available in white, light almond, and blue in packs of 50

PART NO.	DESCRIPTION
WP3475-XX	Cat 5e Quick Connect RJ45 Keystone Connector Colors: BE, BK, BR, GY, GN, IV, LA, OR, RE, WH, YE
WP3476-XX	Cat 6 Quick Connect RJ45 Keystone Connector Colors: BE, BK, BR, GY, IV, LA, OR, RE, WH
WP346A-XX	Cat 6a Quick Connect RJ45 Keystone Connector Colors: BE, BK, BR, GY, GN, IV, LA, OR, RE, WH, YE <b>... TERMINATE ALL WIRES AT ONCE USING THE AC3400 PUNCH &amp; GO TOOL WITH ANY QUICK CONNECT INSERT</b>
WP3450-XX (KS58ABXX)†	Cat 5e RJ45 Keystone Connector Colors: BE (BL), BK, BR, GY (GRY), IV (I), LA, OR, RE (RED), WH (WH)
WP3460-XX (KS68ABXX)†	Cat 6 RJ45 Keystone Connector Colors: BE (BL), BK, BR, GY (GRY), IV (I), LA, OR, RE (RED), WH (WH)
WP3458-XX	Cat 5e Keyed RJ45 Keystone Connector Colors: BK, BR, IV, LA, WH
WP3451-XX (KS888XX)	Cat 5e RJ45 Keystone Coupler Colors: BK, WH (W)
WP3425-XX (KS6UXX)†	RJ25 6P6C Keystone Connector Colors: BK, BR, IV (I), LA, WH (W)
WP3550-XX	Snap & Go Cat 5e Keystone Connector Colors: BE, BK, BR, GY, IV, LA, OR, RE, WH
WP3560-XX	Snap & Go Cat 6 Keystone Connector Colors: BE, BK, BR, GY, IV, LA, OR, RE, WH

## VIDEO INSERTS




WP3479-WH\*



WP3480-WH



WP3481-WH\*



WP3482-WH



WP1234-WH



WP3455-WH



KSBNCW



KSSVW

\*Available in packs of 50.

PART NO.	DESCRIPTION
WP3479-XX	Non-Recessed Coax Keystone F Connector (1 GHz) 50 Count Bulk Pack in WH or LA (WP3479-XX-50)
WP3480-XX	Recessed Gold F Connector (3GHz)
WP3481-XX (KSFFXX)	Recessed Nickle F Connector (3GHz) 50 Count Bulk Pack in WH (WP3481-WH-50)
WP3482-XX (KSFFSTXX)	Recessed Self-Terminating Keystone F Connector (1 GHz)
WP1234-XX	HDMI Keystone Insert/Coupler
WP3455-XX (KSBL10XX)†	Blank Keystone Insert Colors: BK, BR, IV (I), LA, WH (W)
KSBNCXX	Keystone BNC-to-BNC Connector
KSSVXX	Keystone S-Video-to-110 Termination Colors: I, LA, W

### COLOR OPTIONS





# WALL PLATES & INSERTS

## RCA TO F CONNECTORS



WP3461-WH



WP3462-WH



WP3463-WH



WP3464-WH



WP3465-WH



WP3466-WH

PART NO.	DESCRIPTION
WP3461-XX	White Keystone RCA to F Connector Connector Application: Left/Mono
WP3462-XX (KSRCAFX) <sup>†</sup>	Red Keystone RCA to F Connector Connector Application: Right
WP3463-XX	Green Keystone RCA to F Connector Connector Application: Center
WP3464-XX	Blue Keystone RCA to F Connector Connector Application: Left Surround
WP3465-XX	Yellow Keystone RCA to F Connector Connector Application: Composite Video
WP3466-XX	Purple Keystone RCA to F Connector Connector Application: Subwoofer

COLORS:

BK, BR, IV (I), LA, WH (W)

## MULTIMEDIA INSERTS



KSSCW



KSSTW



WP3457-WH



WP3456-WH

PART NO.	DESCRIPTION
KSSCXX	Keystone SC Multimode, Phosphor Bronze Sleeve Colors: I, LA, W
KSSTXX	Keystone ST Multimode, Phosphor Bronze Sleeve Colors: I, LA, W
WP3457-XX (KS2BPXX) <sup>†</sup>	Audio Keystone Binding Post - Pair Colors: BK, BR, IV (I), LA, WH (W)
WP3456-XX	Speaker Pair Insert Colors: BK, BR, IV, LA, WH

## RCA TO RCA INSERTS



KSRCAYW



KSRCARW



KSRCABW



KSRCABEW



KSRCAGNW

PART NO.	DESCRIPTION
KSRCAYXX	Keystone RCA to RCA (Yellow Insulator) Colors: I, LA, W
KSRCARXX	Keystone RCA to RCA (Red Insulator) Colors: I, LA, W
KSRCABXX	Keystone RCA to RCA (Black Insulator) Colors: I, LA, W
KSRCABEXX	Keystone RCA to RCA (Blue Insulator) Colors: I, LA, W
KSRCAGNXX	Keystone RCA to RCA (Green Insulator) Colors: I, LA, W

### COLOR OPTIONS




BK BR IV (I) LA WH (W)

<sup>†</sup>Number in parentheses indicates former part no. and color code  
<sup>†</sup>Omit color code to order brown device

# WALL PLATES & INSERTS

## CAT 5e PATCH CABLES




363201-2X-V1  
AC35XX-WH-V1

PART NO.	DESCRIPTION
363201-26-V1	1 Foot Cat 5e Patch Cable
363201-25-V1	2 Foot Cat 5e Patch Cable
AC3503-WH-V1	3 Foot Cat 5e Patch Cable
AC3507-WH-V1	7 Foot Cat 5e Patch Cable
AC3514-WH-V1	14 Foot Cat 5e Patch Cable
AC3525-WH-V1	25 Foot Cat 5e Patch Cable
AC3550-WH-V1	50 Foot Cat 5e Patch Cable

- 100MHZ RATED PATCH CABLE
- UL VERIFIED TO SUPPORT THE CAT 5e PERFORMANCE PATCH CABLE SPECIFICATION
- SNAGLESS OVERMOLD PREVENTS INSERTION TAB FROM CATCHING ON OTHER CABLES
- 24 AWG STRANDED PATCH CABLE
- AVAILABLE IN WHITE

## CAT 6 PATCH CABLES




AC36XX-BE-V1

PART NO.	DESCRIPTION	NEW!
AC3607-BE-V1	7 Foot Cat 6 Patch Cable	
AC3614-BE-V1	14 Foot Cat 6 Patch Cable	
AC3625-BE-V1	25 Foot Cat 6 Patch Cable	
AC3650-BE-V1	50 Foot Cat 6 Patch Cable	

- 250MHZ RATED PATCH CABLE
- UL VERIFIED TO SUPPORT THE CAT 6 PERFORMANCE PATCH CABLE SPECIFICATION
- SNAGLESS OVERMOLD PREVENTS INSERTION TAB FROM CATCHING ON OTHER CABLES
- 22 AWG STRANDED PATCH CABLE
- AVAILABLE IN BLUE

## CAT 6a PATCH CABLES



AC6AXX-GY-V1

PART NO.	DESCRIPTION	NEW!
AC6A07-GY-V1	7 Foot Cat 6a Patch Cable	
AC6A14-GY-V1	14 Foot Cat 6a Patch Cable	
AC6A25-GY-V1	25 Foot Cat 6a Patch Cable	
AC6A50-GY-V1	50 Foot Cat 6a Patch Cable	

- 500MHZ RATED PATCH CABLE
- UL VERIFIED TO SUPPORT THE CAT 6a PERFORMANCE PATCH CABLE SPECIFICATION
- SNAGLESS OVERMOLD PREVENTS INSERTION TAB FROM CATCHING ON OTHER CABLES
- 22 AWG STRANDED PATCH CABLE
- AVAILABLE IN GRAY

**CAT 3**

Best application: 10BaseT Ethernet at 10Mbps  
Bandwidth: 16MHz

**CAT 5**

Best application: 100BaseT Ethernet at 100Mbps  
Bandwidth: 100MHz

**CAT 5e**

Best application: 1000BaseT Ethernet at 250Mbps  
Bandwidth: 100MHz

**CAT 6**

Best application: 1000BaseT at 1000Mbps (1Gbps)  
Bandwidth: 250MHz

**CAT 6a**

Best application: 10GBaseT at 10Gbps  
Bandwidth: 500MHz



## NETWORKING CABLE REFERENCE GUIDE

**CAT 3** was a popular cabling format for computer network administrators in the early 1990s. It was superseded when Cat 5 became standardized because of its higher performance. It is used only in two-line phone systems.

**CAT 5** was developed to support faster 100BaseT Ethernet standards. When Gigabit Ethernet (1000BaseT) standards were introduced, the Cat 5 cable became vulnerable to crosstalk, which caused interference and signal loss within the transmission.

**CAT 5e** superseded Cat 5 in 1999. It was designed to reduce crosstalk when transmitting 1000BaseT Ethernet. The "e" in Cat 5e stands for "enhanced". It is the most widely used cable in residential installations today.

**CAT 6** was designed to transmit 1000BaseT at Gigabit speeds. Cat 6 is a wider cable than Cat 5e with more twists within its pairs to reduce crosstalk. Cat 6 can also be used in shorter runs for 10GBaseT Ethernet, but is vulnerable to alien crosstalk in a crowded cable environment.

**CAT 6a** was designed to transmit 10GBaseT, even in commercial environments. Cat 6a defends against alien crosstalk, which is crosstalk between cables in a crowded installation. The "a" in Cat 6a stands for "augmented".

### WHAT'S THE DIFFERENCE BETWEEN BITS AND BYTES?

Network speeds are typically calculated in Bits, while files are calculated in Bytes. A Byte is 8 Bits.

### WHY ARE NETWORKING CABLES TWISTED?

The twists in a cable are meant to defend against crosstalk on the line. The physics of this phenomenon are complex, but the twists prevent the signal running on one twisted pair in the cable from jumping to another twisted pair, causing interference.

# WALL PLATES & INSERTS

## STUDIO WALL PLATES 1, 2, 3 and 4-Gang



WP5001-XX



WP5003-XX



WP5002-XX



WP5004-XX

PART NO.	DESCRIPTION
WP5001-XX	1-Gang Studio Wall Plate
WP5002-XX	2-Gang Studio Wall Plate
WP5003-XX	3-Gang Studio Wall Plate
WP5004-XX	4-Gang Studio Wall Plate
<p>... SCREWLESS STUDIO WALL PLATES ARE COMPATIBLE WITH ANY DECORATOR-STYLE STRAP, OUTLET OR SWITCH</p>	



## COLOR OPTIONS



Gloss Black (GB)



Cement (CM)



Titanium (TI)



Khaki (KK)



Light Almond (LA)



White (WH)



Bordeaux (BD)



Cameo Pink (CP)



Spanish Red (SP)



Sand (SD)



Citrus (CR)



Taupe (TP)



Aloe (AE)



Moss (MS)



Cozumel (CZ)



Cyan (CY)



Nirvana (NV)

# WALL PLATES & INSERTS

## PRE-CONFIGURED WALLPLATES



PART NO.	DESCRIPTION
TPTE1XX <sup>†</sup>	2-Line Telephone Jack Wall Plate (4 Conductor Configuration) Colors: BK, BR, I, LA, W
TPTE2XX <sup>†</sup>	Dual 2-Line Telephone Jack Wall Plate (4 Conductor Configuration) Colors: BK, BR, I, LA, W
26TE14XX	Decorator 2-Line Telephone Jack (4 Conductor Configuration) Colors: I, LA, W
26TE16XX	Decorator 3-Line Telephone Jack (6 Conductor Configuration) Colors: I, W
WMTE14XX	2-Line Wall Mount Telephone Jack for Hanging Phones (4 Conductor Configuration) Colors: I, LA, W
SMTE14I	Surface Mount Modular 2-Line Telephone Jack (4 Conductor Configuration) Colors: I
TPCATVXX <sup>†</sup>	1 GHz Coaxial Connector & Wall Plate Colors: I, LA, W, BR, BK
TPCATV2XX <sup>†</sup>	Dual 1GHz Coaxial Connector Wall Plate Colors: I, LA, W, BR, BK
26CATVXX	Decorator 1 GHz Coaxial Connector Colors: I, LA, W
TPTELTVXX <sup>†</sup>	1 GHz Coaxial Connector & 2-Line Phone Jack Wall Plate Colors: I, LA, W, BR, BK
26TELTVXX	1 GHz Coaxial Connector & 2-Line Phone Jack with One-Piece Molded Decorator Plate Colors: I, LA, W
WP3409-WH	Single Gang Surface Mount Box Colors: WH
WP3501-WH	Surface Mount Box 1-Port Colors: WH
WP3502-WH	Surface Mount Box 2-Port Colors: WH
WP3467-XX	Keystone Wall Phone Plate Colors: WH, SS (Stainless Steel)
WP2001-WH-10	Pre-Configured 1-Gang Gold F Connector (10 Pack in WH)
WP2002-WH	1-Gang 6P6C RJ25 Terminating Wall Phone Plate Colors: WH
WP2008-XX-V1	Basic 3GHz Coax Wallplate Colors: LA, WH
WP2009-XX-V1	Basic 3GHz Dual Coax Wallplate Colors: LA, WH

### COLOR OPTIONS



<sup>†</sup>Number in parentheses indicates former part no. and color code  
<sup>†</sup>Omit color code to order brown device

# WALL PLATES & INSERTS

## HOME THEATER Straps and Wallplates



F9004-WH




F9005-WH



F9006-WH



F9008-WH-V1



WP9009-WH-V1



WP1010-WH



WP1014-WH



WP9001-WH



WP9002-WH

PART NO.	DESCRIPTION
F9004-XX	5.1 Home Theater Outlet Strap <b>TOP SELLER!</b> Colors: BK, BR, IV, LA, WH
F9005-XX	Universal Dual Speaker Strap Colors: BK, BR, IV, LA, WH
F9006-XX	Single Speaker Connection Strap Colors: BK, BR, IV, LA, WH
F9008-XX-V1	5.1 Home Theater Outlet Strap with Wall Plate Colors: DM, LA, WH
WP9009-XX-V1	7.1 Home Theater Connection Kit Colors: BK, BR, IV, LA, WH
WP1010-XX	Component Video/Digital Audio Balun Colors: BK, LA, WH <b>CONVERTS 5.1 DIGITAL AUDIO AND COMPOSITE VIDEO TO CAT 5/CAT 6 CABLE (TWO STRAPS REQUIRED FOR INSTALLATION)</b>
WP1014-WH	Cable Access Strap <b>TOP SELLER!</b>
WP9001-XX	Single Gang Hinged Bullnose Wall Plate Colors: BK, WH
WP9002-XX	Double Gang Hinged Bullnose Wall Plate Colors: BK, WH

## HOME THEATER Connection Kits



HT2102-WH-V1



HT2103-WH-V1



HT2000-WH-V1



HT2001-WH-V1



HT2202-WH-V1

PART NO.	DESCRIPTION
HT2102-WH-V1	Flat Panel TV Connection Kit
HT2103-WH-V1	Home Theater Connection Kit
HT2000-WH-V1	HDMI In-Wall Connection Kit Contents: • 1 9-Foot High-Speed HDMI Cable w/Ethernet • 2 Cable Access Straps with Wall Plates
HT2001-WH-V1	HDMI Premium In-Wall Connection Kit Contents: • 1 9-Foot High-Speed HDMI Cable w/Ethernet • 1 Cable Access Strap w/Wall Plate • 1 3-Port HDMI Strap w/ Wall Plate
HT2202-WH-V1	In-Wall TV Power Kit <b>EASILY HIDE POWER AND AV CABLES INSIDE THE WALL WITHOUT MODIFYING THE HOMES ELECTRICAL WIRING.</b>

# DECORATOR STRAPS

## DECORATOR STRAPS



WP3411-WH



WP3412-WH



WP3413-WH



WP3414-WH



WP3416-WH



WP3410-WH

PART NO.	DESCRIPTION
WP3411-XX	1-Port Decorator Outlet Strap
WP3412-XX [KS226XX]*	2-Port Decorator Outlet Strap
WP3413-XX [KS326XX]*	3-Port Decorator Outlet Strap
WP3414-XX [KS426XX]*	4-Port Decorator Outlet Strap
WP3416-XX	6-Port Decorator Outlet Strap
WP3410-XX	Blank Decorator Outlet Strap

COLORS: BK, BR, IV (I), LA, WH (W)

## PRE-CONFIGURED Decorator Straps



WP3210-WH



WP3211-WH



WP3220-WH



WP3422-WH



WP1000-WH



CO1000\*

PART NO.	DESCRIPTION
WP3210-XX	1-Port Strap, 1RJ45 Colors: BK, LA, WH
WP3211-XX	2-Port Strap Phone/TV Colors: BK, LA, WH
WP3220-XX	2-Port Strap Phone/Data Colors: BK, LA, WH
WP3422-XX	4-Port Strap Phone/Data, TV/AUX <b>WITH THIS PRE-CONFIGURED 4-PORT STRAP YOU CAN OFFER PHONE, DATA, TV AND AN AUXILIARY LINE IN ONE DECORATOR OPENING. PERFECT FOR HOME OFFICES, MDU AND ENTERTAINMENT CENTERS. PRE-LABELED FOR EASY ORGANIZATION.</b> Colors: BK, LA, WH
WP1000-WH	Phone/Data Wall Outlet Strap* Colors: IV, LA, WH
CO1000	Phone/Data Module *WP1000 phone/data strap required

### COLOR OPTIONS



# ENCLOSURES


## SCREW-ON COVER ENCLOSURES



PART NO.	DESCRIPTION
EN1200	12 Inch Enclosure with Screw-On Cover 12.13" H x 12" W x 3.7" D
EN1400	14 Inch Enclosure with Screw-On Cover 14" H x 14.25" W x 3.6" D
EN2000	20 Inch Enclosure with Screw-On Cover 20" H x 14.25" W x 3.6" D
EN2800	28 Inch Enclosure with Screw-On Cover 28" H x 14.25" W x 3.6" D
EN4200	42 Inch Enclosure with Screw-On Cover 42" H x 14.25" W x 3.6" D

OUR AMERICAN-MADE ENCLOSURES ARE COMPATIBLE WITH ALL MAJOR MODULE MOUNTING SCHEMES AND OFFER THREE 2.5 INCH OPENINGS FOR HIGH CAPACITY WIRING, SIDE LANCES, A GROUNDING SCREW, AND SIDE TABS FOR MORE FLEXIBLE INSTALLATION OPTIONS. UL CERTIFIED FOR FIRE AND BURGLARY.

## ENCLOSURE EXTENDERS



PART NO.	DESCRIPTION
364450-03	28 Inch Enclosure Extender 29.0" L x 15.4" W x 2.5" H
364450-04	42 Inch Enclosure Extender 43.0" L x 15.4" W x 2.5" H

ADDS 2.5 INCHES OF ADDITIONAL DEPTH TO THE ENCLOSURE TO ACCOMMODATE ROUTERS, SWITCHES AND POWER SUPPLIES.



# ENCLOSURES

## HINGED DOOR ENCLOSURES



EN1450



EN2050



EN2850



EN4250

PART NO.	DESCRIPTION
EN1450	14 Inch Enclosure with Hinged Door 14" H x 14.25" W x 3.6" D
EN2050	20 Inch Enclosure with Hinged Door 20" H x 14.25" W x 3.6" D
EN2850	28 Inch Enclosure with Hinged Door 28" H x 14.25" W x 3.6" D
EN4250	42 Inch Enclosure with Hinged Door 42" H x 14.25" W x 3.6" D
	HINGED DOORS KEEP MODULES SECURE AND PROTECT PRODUCTS FROM WEAR AND TEAR. SHIPS STANDARD WITH STURDY FULL LENGTH PIANO HINGES ALONG WITH LOCK CHAMBERS AND KEYS FOR QUICK AND EASY ACCESS.



# PATCH PANELS

## CAT 5e & CAT 6 Rack Mount Patch Panels



24845C5E



48845CC6

PART NO.	DESCRIPTION
24845C5E	Cat 5e 24-Port Rack Mount Patch Panel
48845C5E	Cat 5e 48-Port Rack Mount Patch Panel
24845CC6	Cat 6 24-Port Rack Mount Patch Panel
48845CC6	Cat 6 48-Port Rack Mount Patch Panel

- 24 PORT PATCH PANEL USES 1 RACK MOUNT SPACE
- 48 PORT PATCH PANEL USES 2 RACK MOUNT SPACES
- 110 PUNCHDOWN REAR TERMINATION
- T568A/B UNIVERSAL WIRING

## CAT 5e FRONT TERMINATE Wall-Mount Jack Panels with Stand-Off Legs



JP12845C5E



JP24845C5E



JP36845C5E

PART NO.	DESCRIPTION
JP12845C5E	12-Port Cat 5e Front Terminate Wall-Mount Jack Panels with Stand-Off Legs
JP24845C5E	24-Port Cat 5e Front Terminate Wall-Mount Jack Panels with Stand-Off Legs
JP36845C5E	36-Port Cat 5e Front Terminate Wall-Mount Jack Panels with Stand-Off Legs

- T568A UNIVERSAL WIRING

## CAT 5e Wall-Mount Patch Panel with 89D Bracket



12845C5E89

PART NO.	DESCRIPTION
12845C5E89	12-Port Cat 5e Wall-Mount Patch Panel with 89D Bracket

- T568A/B UNIVERSAL WIRING

## 66 BLOCK & BRACKET



PS665089V



PS11050KIT4V

PART NO.	DESCRIPTION
PS665089V	50-Pair 66 Block, Unwired & Mounting Bracket
PS11050KIT4V	50-Pair 110 Kit with Legs

# ACCESSORIES & TOOLS

## ACCESSORIES



364554-01



AC2006



AC3460-V0



WP3483-01



364405-01



364774-01



364597-01



364246-01

PART NO.	DESCRIPTION	
364554-01	EZ-RJ45 Modular Cat 5e Plug	<b>LABOR SAVER!</b>
AC2006	EZ-RJ45 Modular Cat 6 Plug	<b>LABOR SAVER!</b>
	⚡ PATENTED DESIGN PROVIDES A QUICK AND HASSLE-FREE CONNECTION FOR CAT 5E (364554-01) OR CAT 6 (AC2006) CABLE. ALLOWS EASY INSPECTION OF WIRE ORDER BEFORE TERMINATION. DESIGNED FOR USE WITH THE EZ-RJ45 MODULAR PLUG HAND TOOL (364555-01).	
AC3460-V0	High Performance Cat 6 RJ45 Modular Plug	10 pack
WP3483-01	Gold Banana Plugs	
364405-01	High Performance RJ45 Modular Plugs	25 pack
364774-01	F to Twin Lead Adapter	⚡ USED TO QUICKLY CONNECT LYRIQ VOLUME CONTROLS TO SUBWOOFER VIA COAX
364597-01	Mini Coax Jumper Assembly, 12"	
364246-01	360 Conical Coax F Plug	

## TOOLS



362721-02



364555-01



363292-01



AC3400



AC3401



AC1018



363293-01



364346-01



364347-01



364406-01



363291-01

PART NO.	DESCRIPTION	
362721-02	RG6 Coax Stripper	<b>LABOR SAVER!</b>
364555-01	EZ-RJ45 Modular Plug Hand Tool	<b>LABOR SAVER!</b>
363292-01	Cat 5 Strip and Fit Tool	<b>LABOR SAVER!</b>
AC3400	Punch & Go Tool	<b>LABOR SAVER!</b>
	⚡ IMPROVES TERMINATION SPEEDS, REDUCES COMPROMISED CONNECTIONS AND INCREASES PRODUCTIVITY OF ANY QUICK CONNECT DATA INSERT	
AC3401	Punch & Go Tool Replacement Blade	
AC1018	Radial Taper Compression Tool (use with 364246-01 Coax F Plug)	
363293-01	110 Punch Down Tool, Impact	
364346-01	Coax Flaring and Insertion Tool	
364347-01	Extended Coax Connector Wrench	
364406-01	High Performance RJ45 Modular Plug Hand Tool	
363291-01	Coax Hex Crimp Tool (use with 363140-03 Coax F Plug)	



# RESOURCES - LINKS & AVAILABLE TOOLS

## TECH SUPPORT

800.321.2343  
tech.support-hs@legrand.us

Our toll-free support line is available from **7:30 a.m. to 6:30 p.m. EST**, Monday through Friday (excluding holidays)

## CUSTOMER SERVICE

800.321.2343  
customer.support-hs@legrand.us

Our toll-free customer service line is available from **8:00 a.m. to 6:30 p.m. EST**, Monday through Friday (excluding holidays)

## TRAINING

legrand.us/education  
training-hs@legrand.us

Legrand offers award-winning in-person and online training. Our innovative sales and installation curriculum is designed to exceed the needs of professional installers.

**Online Training:** Comprehensive online training classes you can take anytime from your home or office.

**Webinars:** These bi-monthly sessions highlight new product offerings, tackle frequently asked questions, and give you a overview of how to efficiently configure and install On-Q solutions.

**Live Product Installation Training:** Our comprehensive courses — taught by certified professional trainers — cover category overviews, installation best practices, troubleshooting tips and much more.

## LITERATURE


### 2013/2014 PRODUCT CATALOG

Part No.1308222  
Showcases the complete On-Q product line along with all the innovative solutions available to homeowners



### HOME SYSTEMS FOLDER

Part No.1308074  
Consumer-friendly brochure with inserts, each one focusing on the benefits of a specific home system such as intercom, audio, camera, networking and more.



©2013 by Legrand. All Rights Reserved. Part# 1308205\_B 8m-LF/TK-10/13

designed to be better™



### Home Systems

301 Fulling Mill Road, Suite G  
Middletown, PA 17057  
(800) 321-2343  
www.legrand.us/onq

570 Applewood Crescent  
Vaughan, Ontario L4K 4B4  
905.738.9195  
www.legrand.ca

Follow Us

