

DOOR LOCKS

Buick	Electra	1977-88	Uncoded service pack no alarm, non lighted chrome	DL1580U	Coded pair	DL1580	Use face cap RP6036 (P-41-201) Use tumbler series P-41-101/105
			Uncoded service pack no alarm, non lighted black	DL1525U	Coded pair	DL1525	Use face cap RP6520 (P-41-202) Use tumbler series P-41-101/105
			Coded pair with factory alarm no lighted keyhole	DP-41-115	Use face cap RP6036 (P-41-201) Use tumbler series P-41-101/105		
			With lighted keyhole – replacement locks available from Strattec				
Buick	Enclave	2008	Uncoded service pack	D-41-003	Use tumbler series P-41-011/015 for D-41-003 sold by ASP. Different tumblers may be used for locks not sold by ASP including some locks sold by GM dealers or originally installed on the car when it was new.		
Buick	Estate Wagon	All	see Le Sabre				
Buick	Le Sabre	1968-70	Uncoded service pack	DL1580U	Coded pair	DL1580	Use face cap RP6036 (P-41-201) Use tumbler series P-41-101/105
Buick	Le Sabre 2-door	1971	Uncoded service pack	DL1580U	Coded pair	DL1580	Use face cap RP6036 (P-41-201) Use tumbler series P-41-101/105
Buick	Le Sabre 4-door	1971	Uncoded service pack	DL1582U	Coded pair	DL1582	Use face cap RP6036 (P-41-201) Use tumbler series P-41-101/105
Buick	Le Sabre	1972-76	Uncoded service pack	DL1582U	Coded pair	DL1582	Use face cap RP6036 (P-41-201) Use tumbler series P-41-101/105
Buick	Le Sabre	1977-99	Uncoded service pack no alarm, non lighted	DL1580U	Coded pair	DL1580	Use face cap RP6036 (P-41-201) Use tumbler series P-41-101/105
			Coded pair with factory alarm no lighted keyhole	DP-41-115	Use face cap RP6036 (P-41-201) Use tumbler series P-41-101/105		
			Uncoded service pack with factory alarm no lighted keyhole	D-41-215	NOTE: D-41-215 uses H keyway used on 1977, 1981, and 1991-99 models only. Uncoded service package not available with other keyways as used 1978-80 and 1982-90. Use face cap RP6036 (P-41-201) Use tumbler series P-41-101/105		
			With lighted keyhole – replacement locks available from Strattec				
Buick	Le Sabre	2000-05	Uncoded service pack	D-41-001	Use face cap P-41-205 Use tumbler series P-41-121/124 for D-41-001 sold by ASP. Different tumblers may be used for locks not sold by ASP including some locks sold by GM dealers.		
Buick	Lucerne	2006-07	Replacement locks available from Strattec				
Buick	Opel (Japan)	1976-79	Uncoded service pack	D-24-201	Use face cap P-24-203 (chrome) or P-24-204 (black) Use tumbler series P-30-141/144		
Buick	Park Avenue	1989-96	Uncoded service pack no alarm, non lighted	DL1580U	Coded pair	DL1580	Use face cap RP6036 (P-41-201) Use tumbler series P-41-101/105
			Coded pair with factory alarm no lighted keyhole	DP-41-115	Use face cap RP6036 (P-41-201) Use tumbler series P-41-101/105		
			Uncoded service pack with factory alarm no lighted keyhole	D-41-215	NOTE: D-41-215 uses H keyway used on 1991-96 models only. Uncoded service package not available with other keyways as used 1989-90 Use face cap RP6036 (P-41-201) Use tumbler series P-41-101/105		
			With lighted keyhole – replacement locks available from Strattec				
Buick	Park Avenue	1997-05	Replacement locks available from Buick / GM dealers only. Parts to service original locks are available as follows: Face cap: P-41-203, Dust cover assembly: P-41-233 Plastic pawls (1997-99 only): P-41-301 for right side, P-41-302 for left side Use tumbler series P-41-111/114				
Buick	Reatta	1988-92	Uncoded service pack no alarm, non lighted	DL1580U	Coded pair	DL1580	Use face cap RP6036 (P-41-201) Use tumbler series P-41-101/105
			Coded pair with factory alarm no lighted keyhole	DP-41-115	Use face cap RP6036 (P-41-201) Use tumbler series P-41-101/105		
			Uncoded service pack with factory alarm no lighted keyhole	D-41-215	NOTE: D-41-215 uses H keyway used on 1991-92 models only. Uncoded service package not available with other keyways as used 1988-90 Use face cap RP6036 (P-41-201) Use tumbler series P-41-101/105		
			With lighted keyhole – replacement locks available from Strattec				
Buick	Regal	1973-78	Uncoded service pack	DL1580U	Coded pair	DL1580	Use face cap RP6036 (P-41-201) Use tumbler series P-41-101/105
Buick	Regal 2-door	1979-87	Uncoded service pack (chrome)	DL1582U	Coded pair (chrome)	DL1582	Use face cap RP6036 (P-41-201) Use tumbler series P-41-101/105
			Uncoded service pack (black)	DL1527U	Coded pair (black)	DL1527	Use face cap RP6520 (P-41-202) Use tumbler series P-41-101/105
Buick	Regal 2-door	1988-97	Uncoded service pack	DL1508U	Coded pair	DL1508	Use tumbler series P-41-101/105
Buick	Regal 4-door	1973-87	Uncoded service pack	DL1580U	Coded pair	DL1580	Use face cap RP6036 (P-41-201) Use tumbler series P-41-101/105
Buick	Regal 4-door	1988-97	Uncoded service pack chrome	DL1580U	Coded pair chrome	DL1580	Use face cap RP6036 (P-41-201) Use tumbler series P-41-101/105
			Uncoded service pack black	DL1525U	Coded pair black	DL1525	Use face cap RP6520 (P-41-202) Use tumbler series P-41-101/105

Check www.carlocks.com for the most up to date information

DOOR LOCKS

Buick	Regal	1997-04	Replacement locks available from Strattec Use tumbler series P-41-161/164				
Buick	Rendezvous	2002-07	Replacement locks available from Buick / GM dealers only. Face cap must be removed to service original lock on the car, replacement caps not currently available Use tumbler series P-41-111/114				
Buick	Riviera	1968-70	Uncoded service pack	DL1581U	Coded pair	DL1581	Use face cap RP6036 (P-41-201) Use tumbler series P-41-101/105
Buick	Riviera	1971-74	Uncoded service pack	DL1580U	Coded pair	DL1580	Use face cap RP6036 (P-41-201) Use tumbler series P-41-101/105
Buick	Riviera	1975-76	Uncoded service pack	DL1582U	Coded pair	DL1582	Use face cap RP6036 (P-41-201) Use tumbler series P-41-101/105
Buick	Riviera	1977-80	Uncoded service pack	DL1580U	Coded pair	DL1580	Use face cap RP6036 (P-41-201) Use tumbler series P-41-101/105
Buick	Riviera	1981-85	Uncoded service pack no alarm, non lighted	DL1582U	Coded pair	DL1582	Use face cap RP6036 (P-41-201) Use tumbler series P-41-101/105
			Coded pair with factory alarm no lighted keyhole	DP-41-115	Use face cap RP6036 (P-41-201) Use tumbler series P-41-101/105		
			With lighted keyhole – replacement locks available from Strattec				
Buick	Riviera	1986-93	Uncoded service pack no alarm, non lighted, chrome	DL1580U	Coded pair	DL1580	Use face cap RP6036 (P-41-201) Use tumbler series P-41-101/105
			Uncoded service pack no alarm, non lighted black	DL1525U	Coded pair	DL1525	Use face cap RP6520 (P-41-202) Use tumbler series P-41-101/105
			Coded pair with factory alarm no lighted keyhole chrome	DP-41-115	Use face cap RP6036 (P-41-201) Use tumbler series P-41-101/105		
			Uncoded service pack with factory alarm no lighted keyhole chrome	D-41-215	NOTE: D-41-215 uses H keyway used on 1991-93 models only. Uncoded service package not available with other keyways as used 1986-90 Use face cap RP6036 (P-41-201) Use tumbler series P-41-101/105		
			Uncoded service pack with factory alarm no lighted keyhole black	D-41-242	NOTE: D-41-242 uses H keyway used on 1991-93 models only. Uncoded service package not available with other keyways as used 1986-90 Use face cap RP6520 (P-41-202) Use tumbler series P-41-101/105		
			With lighted keyhole – replacement locks available from Strattec				
Buick	Riviera	1995-99	Replacement locks available from Strattec Use tumbler series P-41-161/164				
Buick	Roadmaster	1992-96	Uncoded service pack	DL1580U	Coded pair	DL1580	Use face cap RP6036 (P-41-201) Use tumbler series P-41-101/105
Buick	Skyhawk	1975-91	Uncoded service pack	DL1580U	Coded pair	DL1580	Use face cap RP6036 (P-41-201) Use tumbler series P-41-101/105
Buick	Skylark	1967-91	Uncoded service pack	DL1580U	Coded pair	DL1580	Use face cap RP6036 (P-41-201) Use tumbler series P-41-101/105
Buick	Skylark	1992-94	Uncoded service pack RH no alarm	D-41-243	Uncoded service pack LH no alarm	D-41-244	Use tumbler series P-41-101/105
Buick	Skylark	1995-99	Replacement locks available from Strattec Use tumbler series P-41-161/164				
Buick	Somerset	All	see Skylark				
Buick	Terraza	2005-07	Locks using B106 keys, replacement locks available from Buick / GM dealers only. Use tumbler series P-41-011/015				
			Locks using B86 keys, available from Strattec Use tumbler series P-41-161/164				
Buick	Wildcat	1968-70	Uncoded service pack	DL1580U	Coded pair	DL1580	Use face cap RP6036 (P-41-201) Use tumbler series P-41-101/105
Cadillac	Allante	1986-93	Replacement locks available from Cadillac / GM dealers only, other service parts not available from ASP.				
Cadillac	Calais	All	see Deville				
Cadillac	Cimarron	1982-88	Uncoded service pack	DL1580U	Coded pair	DL1580	Use face cap RP6036 (P-41-201) Use tumbler series P-41-101/105
Cadillac	Catera	1997-02	Uncoded plug	D-23-311	Use tumbler series P-13-101/104 (P-21-111/114)		
Cadillac	CTS	2003-07	Uncoded service pack	D-41-001	Use tumbler series P-41-121/124 for D-41-001 sold by ASP. Different tumblers may be used for locks not sold by ASP including some locks sold by GM dealers or originally installed on the car when it was new. Use face cap P-41-205		
Cadillac	CTS	2008	Uncoded service pack	D-41-003	Use tumbler series P-41-011/015 for D-41-003 sold by ASP. Different tumblers may be used for locks not sold by ASP including some locks sold by GM dealers or originally installed on the car when it was new.		
Cadillac	Deville 2- door coupe & convertible	1967-68	Uncoded service pack	DL1581U	Coded pair	DL1581	Use face cap RP6036 (P-41-201) Use tumbler series P-41-101/105
Cadillac	Deville 4-door	1967-68	Uncoded service pack	DL1580U	Coded pair	DL1580	Use face cap RP6036 (P-41-201) Use tumbler series P-41-101/105
Cadillac	Deville	1969-70	Uncoded service pack	DL1581U	Coded pair	DL1581	Use face cap RP6036 (P-41-201) Use tumbler series P-41-101/105

DOOR LOCKS

Suzuki	XL-7	2007-08	Uncoded service pack	D-41-003	Use tumbler series P-41-011/015 for D-41-003 sold by ASP. Different tumblers may be used for locks not sold by ASP including some locks sold by GM dealers or originally installed on the car when it was new.		
Toyota	Avalon	1995-99	Complete lock RH	D-30-129	Complete lock LH (no lighted keyhole)	D-30-130	Use tumbler series P-30-181/188
			Lighted keyhole on left side only		Complete lock LH (lighted keyhole)	D-30-131	Use tumbler series P-30-181/188
Toyota	Avalon	2000-04	Complete lock RH	D-30-517	Complete lock LH	D-30-518	Use tumbler series P-30-181/188
Toyota	Avalon	2005-07	no lock cylinder on RH side		Complete lock LH cars with SmartKey	D-30-546	Use tumbler series P-30-121/123
					For cars without SmartKey replacement locks available from Toyota dealers only. Use tumbler series P-30-131/134		
Toyota	Camry	1983-91	Lock service package	D-30-207 (D-30-107)	Door lock pair including pawls	DP-30-107	If original pawl cannot be reused, use P-30-312 (RH) or P-30-313 (LH) Use face cap P-30-211 Use tumbler series P-30-141/144
			Lighted keyhole on left side only		Complete lock LH with lighted keyhole	D-30-120	Use face cap P-30-205 Use tumbler series P-30-141/144
Toyota	Camry	1992-96	Complete lock RH	D-30-109	Complete lock LH (no lighted keyhole)	D-30-110	Use face cap P-30-219 Use tumbler series P-30-181/188
			Lighted keyhole on left side only		Complete lock LH with lighted keyhole	D-30-128	Use face cap P-30-219 Use tumbler series P-30-181/188
Toyota	Camry	1997-01	Complete lock RH	D-30-152	Complete lock LH	D-30-153	Use face cap P-30-265 Use tumbler series P-30-181/188
Toyota	Camry	2002-06	Complete lock RH	D-30-529	Complete lock LH	D-30-530	Use face cap P-30-268 Use tumbler series P-30-131/134
Toyota	Camry	2007-08	Complete lock RH except Hybrid and cars with Smartkey	D-30-541	Complete lock LH except Hybrid and cars with Smartkey	D-30-542	Use face cap P-30-268 Use tumbler series P-30-131/134
			Hybrid and cars with Smartkey no lock cylinder on RH side		Complete lock LH Hybrid and cars with Smartkey only	D-30-556	Use face cap P-30-268 Use tumbler series P-30-121/123
Toyota	Camry Solara	All	see Solara				
Toyota	Carina	1972-73	Complete lock with reversible pawl R/L	D-30-101	Door lock pair	DP-30-101	Use face cap P-30-201 Use tumbler series P-30-141/144
Toyota	Celica	1970-77	Complete lock with reversible pawl R/L	D-30-101	Door lock pair	DP-30-101	Use face cap P-30-201 Use tumbler series P-30-141/144
Toyota	Celica	1978-81	Complete lock with reversible pawl R/L	D-30-104	Door lock pair	DP-30-104	Use face cap P-30-201 Use tumbler series P-30-141/144
Toyota	Celica	1982-83	Complete lock RH	D-30-121	Complete lock LH	D-30-122	Use face cap P-30-212 (RH) Use face cap P-30-213 (LH) Use tumbler series P-30-141/144
Toyota	Celica	1984-85	Complete lock RH	D-30-116	Complete lock LH	D-30-117	Use face cap P-30-261 Use tumbler series P-30-141/144
Toyota	Celica coupe	1986-89	Complete lock RH	D-30-142	Complete lock LH	D-30-143	Use tumbler series P-30-141/144
Toyota	Celica liftback	1986-89	Uncoded plug	D-30-339	Complete locks previously sold as D-30-160 (RH) and D-30-161 (LH), discontinued when out. Use tumbler series P-30-151/157		
Toyota	Celica coupe	1990-93	Lock service pack	D-30-111	The original pawl must be reused. Use tumbler series P-30-161/164		
Toyota	Celica liftback	1990-93	Complete lock RH	D-30-164	Complete lock LH	D-30-165	Use tumbler series P-30-151/157
Toyota	Celica	1994-99	Complete lock (includes pawl for left side)	D-30-127	NOTE: D-30-127 includes left side pawl. For right side the original pawl must be reused. Use tumbler series P-30-181/188		
Toyota	Celica	2000-05	Complete lock RH	D-30-519	Complete lock LH	D-30-520	Use tumbler series P-30-181/188
Toyota	Corolla except station wagon	1970-79	Complete lock with reversible pawl R/L	D-30-101	Door lock pair	DP-30-101	Use face cap P-30-201 Use tumbler series P-30-141/144
Toyota	Corolla station wagon	1970-79	Complete lock with reversible pawl R/L	D-30-166	Use face cap P-30-201 Use tumbler series P-30-171/174		
Toyota	Corolla except station wagon	1980-83	Complete lock with reversible pawl R/L	D-30-104	Door lock pair	DP-30-104	Use face cap P-30-201 Use tumbler series P-30-141/144
Toyota	Corolla station wagon	1980-83	Complete lock with reversible pawl R/L	D-30-113	Use face cap P-30-201 Use tumbler series P-30-171/174		
Toyota	Corolla	1984-87	Lock service package	D-30-206 (D-30-106)	Coded pair includes pawls	DP-30-106	If original pawl cannot be reused, use P-30-312 (RH) or P-30-313 (LH) Use face cap P-30-211 Use tumbler series P-30-141/144
Toyota	Corolla FX	1987-88	Lock service package	D-30-206 (D-30-106)	Coded pair includes pawls	DP-30-106	If original pawl cannot be reused, use P-30-312 (RH) or P-30-313 (LH) Use face cap P-30-211 Use tumbler series P-30-141/144
Toyota	Corolla	1988-92	Complete lock with reversible pawl R/L	D-30-108	Door lock pair	DP-30-108	Use tumbler series P-30-161/164
Toyota	Corolla wagon 2-wheel drive	1988-92	Complete lock with reversible pawl R/L	D-30-507	Use tumbler series P-30-151/157		

Check www.carlocks.com for the most up to date information

ASP PART NUMBERING SYSTEM

The ASP Part Numbering System

Working with the ASP part numbers is easier if you have a basic understanding of the part numbering system, explained here:

The first letter or letters of the part number identify what type of product the part number is:

A	Keying kits and parts assortments
B	Luggage compartment locks
C	Ignition locks
D	Door locks (including complete locks that include the door handle)
DH	Door handles (except complete locks that include the door handle)
DP	Door locks (keyed alike pair)
E	Engine compartment locks
F	Fasteners (including lock retaining clips, shear-head bolts, door panel fasteners, etc.)
G	Glove compartment and stowage locks
KB	Key blanks
P	Lock service parts (including tumblers, face caps, and other parts)
RK	Remote head key blanks
S	Lock sets
T	Fuel tank locks
W	Ignition switches (wiring assembly only without lock cylinder)

The second two digits of the part number tell you the PRIMARY brand of vehicle that the item is used on:

00	Various cars
11	Alfa Romeo
12	Audi
13	BMW
14	British Cars (Austin, Jaguar, Land Rover, MG, Range Rover, Triumph)
15	British Chrysler (Plymouth Cricket, Sunbeam, Hillman)
16	Nissan / Datsun / Infiniti
17	Fiat
18	European Ford (Capri, Fiesta, Merkur)
19	Honda / Acura
20	Mazda
21	Mercedes-Benz
22	Mitsubishi
23	GM Europe (Cadillac Catera, Pontiac Lemans, Opel)

24	Isuzu (including General Motors brands)
25	Peugeot
26	Porsche
27	Renault
28	Saab
29	Subaru
30	Toyota / Lexus / Scion / Hino truck
31	Volkswagen
32	Volvo
33	Suzuki
34	Lada
35	Lancia
36	Hyundai
37	Daihatsu
38	Citroen
39	Yugo
40	Kia
41	General Motors USA (Buick, Cadillac, Chevrolet, GMC, Oldsmobile, Pontiac)
42	Ford / Lincoln / Mercury (USA)
43	American Motors (including some Heavy Trucks and Jeep)
44	Chrysler / Dodge / Jeep / Plymouth
45	Skoda
49	Saturn
50	Daewoo (including Chevrolet Aveo, Saturn Vue, other General Motors brands)
55	Renault truck (including some Mack trucks)
56	Freightliner truck
57	Kenworth truck
93	Harley Davidson Motorcycle
94	Honda Motorcycle
98	Yamaha Motorcycle

For example, if you have part number C-30-107, by understanding the part numbering system you will know that the part is an ignition lock (first letter C), which fits a Toyota (second two digits 30).

There are exceptions to this system created by the same part being used on more than one brand of car. Also some parts are used in more than one place on the car – for example, B-14-210 is numbered as a luggage compartment lock, but also is used as an ignition lock or door lock on some cars.

ASP PART NUMBERING SYSTEM

The same part being used on more than one brand of car is explained by lock families, as follows:

Audi - also found on some Porsche and Volkswagen

Ford USA – also found on some Mazda and Nissan

Honda / Acura - also found on some Isuzu

Mazda – also found on some Chrysler imports, Ford imports, General Motors imports, GEO, Mitsubishi, Suzuki

Nissan - also found on some Subaru and Isuzu truck

Toyota – also found on some Chrysler imports, Daihatsu, General Motors imports, GEO, Hyundai, Isuzu, Kia, Mazda, Mitsubishi, Suzuki.

Volkswagen - also found on some Audi and Porsche (tumblers also used on BMW)

You will also find some parts that are used among the brands of the following groups of cars:

British cars - Aston Martin, Austin, English Ford, Jaguar, Jensen, Land Rover, MG, Morgan, Range Rover, Rover car, Sterling car, Triumph, TVR, Volvo.

French cars - Peugeot, Renault, Citroen

German cars - Audi, BMW, Daewoo, General Motors (Cadillac Catera, Chevrolet Aveo, Pontiac Lemans, others), Mini, Porsche, Mercedes-Benz, Volkswagen

Italian cars - Alfa Romeo, Bertone, Ferrari, Fiat, Iveco, Lada, Lamborghini, Lancia, Maserati, Pininfarina, Yugo

Lockcraft Part Numbers

The first two letters of the part number identify what type of product the part number is:

DL	Door lock
LC	Ignition lock
LS	Lock set
RP	Lock service parts (including tumblers, face caps, and other parts)
SK	Keying kits and parts assortments
TL	Luggage compartment locks

Lockcraft part numbers that end in “U” are uncoded locks.

There have been many changes to the Lockcraft part numbers over the past years, explained as follows:

Most old Lockcraft part numbers had no letter prefix. For example, old part number 1426 was changed to LC1426 to identify the type of product.

Some old Lockcraft part numbers had a letter prefix “A”, which was changed to “RP”. For example, part number A6001 was changed to RP6001. This could be confusing if you have an old Lockcraft or All Lock keying kit or parts assortment which identified the parts inside by the letter prefix “A”. When reordering simply change the “A” to “RP”.

Some old Lockcraft part numbers had a digit “3” at the end of the part number, which designated poly bag packaging. For example, part number LC14263 designated the LC1426 ignition lock in a poly bag. The currently used part numbers now eliminate the “3” at the end and using the example LC14263 is now simply LC1426.

Some old Lockcraft part numbers had a digit “8” at the end of the part number, which designated that it was an uncoded lock. For example, part number LC14268 designated the LC1426 ignition lock in uncoded form. The currently used part numbers now use “U” at the end of the part number instead of the “8”. Using the example LC14268 is now LC1426U.

PART NUMBER LISTING and POPULARITY RATINGS

Part Number Listings and Popularity Ratings

Pages 214-233 contain a complete listing of ASP part numbers, with the 2008 popularity rating for each part number. The popularity ratings are explained as follows:

A = Most popular items (lock cylinders and replacement parts)

B = Second most popular group of lock cylinders

Y = Replacement parts (keying kit refill tumblers, face caps, etc.), popularity equivalent to B-rated lock cylinders

C = Third most popular group of lock cylinders

Z = Replacement parts (keying kit refill tumblers, face caps, etc.), popularity equivalent to C-rated lock cylinders

H = Items not recommended for stock by distributors, these parts are normal stock items for the ASP warehouse and available for drop shipments (HI-SPEED delivery). Orders must be placed through your distributor, and are subject to stock on hand at ASP. Some distributors may have selected H-rated items in stock.

S = Special order items only, may not be in stock at ASP. These items may be subject to minimum order quantities if needed. Some distributors may have selected S-rated items in stock.

DWO = Discontinued when out. Some items may still have limited stock at ASP or at some distributors, but will not be restocked when existing supplies are sold out.

ASP products are sold through the network of locksmith supply distributors located throughout the USA and Canada.

With over 4,000 different part numbers in our range, it is impossible and impractical for distributors to keep every part number in stock. Thus we have assigned each of our part numbers a popularity rating to assist distributors in keeping stock. We have implemented new distributor stocking programs based on these popularity ratings. Please check www.carlocks.com for the most current information about our distributor stocking guidelines. ASP is working closely with our distributors to provide you the fastest delivery possible at the lowest possible cost.

Distributors who make a commitment to keep stock according to our recommendations are listed on www.carlocks.com. This list is subject to change at any time. Distributors who do not keep the stocking commitment will be removed from the list.

Explanation of other notes on the part number listing

a. Some items have (now use ...) to the right of the part number, with a rating of DWO.

For example: A-13-105 (now use A-31-110) – this means that A-13-105 has been superseded by A-31-110.

b. Some items have (substitute ...) to the right of the part number, with a rating of DWO.

For example: B-19-154 (substitute B-19-155) - this means that you can substitute B-19-155 for B-19-154, but there is some difference between the two parts. A complete listing of these part numbers with a brief explanation of the difference between each superseded part and the replacement part is provided on pages 234-237.

c. Some items have (see ...) to the right of the part number, with no popularity rating.

For example: B-16-105 (see B-16-205), with no popularity rating. Then go to B-16-205 and you will see it listed as B-16-205 (B-16-105) with the popularity rating of B. This is a result of our consolidating some similar interchangeable part numbers. In this example, whether you order B-16-105 or B-16-205, you will get the same part at the same price. A complete listing of these part numbers is provided on pages 238-239.