

DOOR LOCKS

Cadillac	Seville	1986-91	Uncoded service pack no alarm, non lighted	DL1580U	Coded pair	DL1580	Use face cap RP6036 (P-41-201) Use tumbler series P-41-101/105	
			Coded pair with factory alarm no lighted keyhole	DP-41-115	Use face cap RP6036 (P-41-201) Use tumbler series P-41-101/105			
			Uncoded service pack with factory alarm no lighted keyhole	D-41-215	NOTE: D-41-215 uses H keyway used on 1991-95 models only. Uncoded service package not available with other keyways as used 1986-90 Use face cap RP6036 (P-41-201) Use tumbler series P-41-101/105			
			With lighted keyhole – replacement locks available from Strattec					
Cadillac	Seville SLS, STS	1992-00	Uncoded service pack RH no alarm	D-41-243	Uncoded service pack LH no alarm	D-41-244	Use tumbler series P-41-101/105	
			Uncoded service pack RH with alarm	D-41-245	Uncoded service pack LH with alarm	D-41-246	Use tumbler series P-41-101/105	
Cadillac	Seville SLS, STS	1998-02	Replacement locks available from Cadillac / GM dealers only. Parts to service original locks are available as follows: Face cap: P-41-203, Dust cover assembly: P-41-233 Use tumbler series P-41-111/114					
Cadillac	SRX	2004-08	Uncoded service pack	D-41-003	Use tumbler series P-41-011/015 for D-41-003 sold by ASP. Different tumblers may be used for locks not sold by ASP including some locks sold by GM dealers or originally installed on the car when it was new.			
Cadillac	STS	2005-08	Uncoded service pack	D-41-003	Use tumbler series P-41-011/015 for D-41-003 sold by ASP. Different tumblers may be used for locks not sold by ASP including some locks sold by GM dealers or originally installed on the car when it was new.			
Cadillac	XLR	2004-08	Remote access only, no lock cylinders					
Checker	All	1978-81	Uncoded service pack	DL1580U	Coded pair	DL1580	Use face cap RP6036 (P-41-201) Use tumbler series P-41-101/105	
Chevrolet	Aveo hatchback	2004-08	Complete lock RH	D-50-115	Complete lock LH	D-50-116	Use tumbler series P-13-101/104 (P- 21-111/114)	
Chevrolet	Aveo sedan	2004-06	Complete lock RH	D-50-115	Complete lock LH	D-50-116	Use tumbler series P-13-101/104 (P- 21-111/114)	
Chevrolet	Aveo sedan	2007-08	Complete lock RH	D-50-117	Complete lock LH	D-50-118	Use tumbler series P-13-101/104 (P- 21-111/114)	
Chevrolet	Bel Air	1967-up	see Caprice					
Chevrolet	Biscayne	1967-up	see Caprice					
Chevrolet	Blazer C/5, K/5	1967-91	Uncoded service pack (chrome)	DL1580U	Coded pair (chrome)	DL1580	Use face cap RP6036 (P-41-201) Use tumbler series P-41-101/105	
			Uncoded service pack (black)	DL1525U	Coded pair (black)	DL1525	Use face cap RP6520 (P-41-202) Use tumbler series P-41-101/105	
Chevrolet	Blazer C/5, K/5	1992-94	Coded pair	DL1539	Coded 3-piece set 2 front doors + tailgate	DL1518		
			Uncoded service pack	DL1539U	Use tumbler series P-41-101/105			
Chevrolet	Blazer C/5, K/5	1995-02	Replacement locks available from Strattec Use tumbler series P-41-161/164					
Chevrolet	Blazer S10	1982-94	Uncoded service pack (chrome)	DL1580U	Coded pair (chrome)	DL1580	Use face cap RP6036 (P-41-201) Use tumbler series P-41-101/105	
			Uncoded service pack (black)	DL1525U	Coded pair (black)	DL1525	Use face cap RP6520 (P-41-202) Use tumbler series P-41-101/105	
Chevrolet	Blazer S10	1995-05	Replacement locks available from Strattec Use tumbler series P-41-161/164					
Chevrolet	Beretta	1987-96	Replacement locks available from Strattec Use tumbler series P-41-101/105					
Chevrolet	Camaro	1967-12/69	Uncoded service pack	DL1580U	Coded pair	DL1580	Use face cap RP6036 (P-41-201) Use tumbler series P-41-101/105	
Chevrolet	Camaro	1/70-78	Uncoded service pack	DL1581U	Coded pair	DL1581	Use face cap RP6036 (P-41-201) Use tumbler series P-41-101/105	
Chevrolet	Camaro	1979-81	Uncoded service pack	DL1582U	Coded pair	DL1582	Use face cap RP6036 (P-41-201) Use tumbler series P-41-101/105	
Chevrolet	Camaro	1982-92	Uncoded service pack (chrome)	DL1580U	Coded pair (chrome)	DL1580	Use face cap RP6036 (P-41-201) Use tumbler series P-41-101/105	
			Uncoded service pack (black)	DL1525U	Coded pair (black)	DL1525	Use face cap RP6520 (P-41-202) Use tumbler series P-41-101/105	
Chevrolet	Camaro	1993-02	Uncoded service pack (chrome)	DL6553U	Coded pair (chrome)	DL6553	Use face cap RP6036 (P-41-201) Use tumbler series P-41-101/105	
			Uncoded service pack (black)	DL6943U	Coded pair (black)	DL6943	Use face cap RP6520 (P-41-202) Use tumbler series P-41-101/105	
Chevrolet	Caprice	1967-70	Uncoded service pack	DL1580U	Coded pair	DL1580	Use face cap RP6036 (P-41-201) Use tumbler series P-41-101/105	
Chevrolet	Caprice	1971-76	Uncoded service pack	DL1582U	Coded pair	DL1582	Use face cap RP6036 (P-41-201) Use tumbler series P-41-101/105	
Chevrolet	Caprice (also Impala)	1977-96	Uncoded service pack chrome	DL1580U	Coded pair chrome	DL1580	Use face cap RP6036 (P-41-201) Use tumbler series P-41-101/105	
			Uncoded service pack black	DL1525U	Coded pair black	DL1525	Use face cap RP6520 (P-41-202) Use tumbler series P-41-101/105	
Chevrolet	Cavalier	1982-94	Uncoded service pack	DL1580U	Coded pair	DL1580	Use face cap RP6036 (P-41-201) Use tumbler series P-41-101/105	
Chevrolet	Cavalier	1995-05	Replacement locks available from Strattec Use tumbler series P-41-161/164					

DOOR LOCKS

Pontiac	Safari wagon	1968-91	see Bonneville				
Pontiac	Solstice	2006-07	Replacement locks available from Pontiac / GM dealers only				
Pontiac	Solstice	2008	Replacement locks available from Strattec				
Pontiac	Sunbird	1979-94	Uncoded service pack	DL1580U	Coded pair	DL1580	Use face cap RP6036 (P-41-201) Use tumbler series P-41-101/105
Pontiac	Sunburst	1985-91	Uncoded service pack without pawl	D-24-202	Use pawl P-30-330 (reversible for RH & LH) Use face cap P-30-211 (chrome) or P-30-215 (black) Use tumbler series P-24-101/104		
Pontiac	Sunfire	1995-05	Replacement locks available from Strattec Use face cap RP6036 (P-41-201) chrome, or RP6520 (P-41-202) black Use tumbler series P-41-161/164				
Pontiac	Sunrunner	1989-98	Coded lock without pawl	D-33-203	If original pawl cannot be reused use P-30-322 (RH) or P-30-323 (LH) Use face cap P-33-201 Use tumbler series P-33-101/105		
Pontiac	T-37 & GT-37	1971	see Lemans 1971				
Pontiac	T1000	1982-87	Uncoded service pack (chrome)	DL1580U	Coded pair (chrome)	DL1580	Use face cap RP6036 (P-41-201) Use tumbler series P-41-101/105
			Uncoded service pack (black)	DL1525U	Coded pair (black)	DL1525	Use face cap RP6520 (P-41-202) Use tumbler series P-41-101/105
Pontiac	Tempest	All	see Lemans				
Pontiac	Torrent	2006-08	Uncoded service pack	D-41-003	Use tumbler series P-41-011/015 for D-41-003 sold by ASP. Different tumblers may be used for locks not sold by ASP including some locks sold by GM dealers or originally installed on the car when it was new.		
Pontiac	Trans Am	All	see Firebird				
Pontiac	Trans Sport	1990-96	Uncoded service pack without factory alarm or automatic locking 1990-96	D-41-203	Use chrome face cap RP6036 (P-41-201) Use black face cap RP6045 (P-41-202) Use tumbler series P-41-101/105		
			Uncoded service pack with factory alarm or automatic locking (1991-96 only)	D-41-216	NOTE: D-41-216 uses H keyway used on 1991-96 models only. Uncoded service package not available with other keyways as used 1990 Use chrome face cap RP6036 (P-41-201) Use black face cap RP6045 (P-41-202) Use tumbler series P-41-101/105		
Pontiac	Trans Sport	1997-05	Replacement locks available from Strattec Use tumbler series P-41-161/164				
Pontiac	Ventura II	1969-78	Uncoded service pack	DL1580U	Coded pair	DL1580	Use face cap RP6036 (P-41-201) Use tumbler series P-41-101/105
Pontiac	Vibe	2003-07	If the original shaft (pawl) can be reused, the following locks can be used: D-30-529 for right side D-30-530 for left side Complete locks including shaft (pawl) are available from Toyota dealers only Use face cap P-30-268 Use tumbler series P-30-131/134				
Pontiac	Wave hatchback	2004-08	Complete lock RH	D-50-115	Complete lock LH	D-50-116	Use tumbler series P-13-101/104 (P-21-111/114)
Pontiac	Wave sedan	2004-06	Complete lock RH	D-50-115	Complete lock LH	D-50-116	Use tumbler series P-13-101/104 (P-21-111/114)
Pontiac	Wave sedan	2007-08	Complete lock RH	D-50-117	Complete lock LH	D-50-118	Use tumbler series P-13-101/104 (P-21-111/114)
Porsche	911, 912, 930, Carrera	1970-84	Uncoded plug RH	D-26-101	Uncoded plug LH	D-26-102	Discontinued when out, now available from Porsche dealers only Use tumbler series P-26-101/104
Porsche	911, 930, Carrera	1985-94	Complete lock RH	D-26-115	Complete lock LH	D-26-116	Discontinued when out, now available from Porsche dealers only Use tumbler series P-26-101/104
Porsche	911, 930 Carrera	1995-98	Complete lock RH	D-26-117	Complete lock LH	D-26-118	Discontinued when out, now available from Porsche dealers only Use tumbler series P-26-101/104
Porsche	914	1968-76	Complete lock RH	D-26-103	Complete lock LH	D-26-104	Discontinued when out, now available from Porsche dealers only Use tumbler series P-26-101/104
Porsche	924	1977-79	Uncoded plug	D-31-306	Use tumbler series P-31-111/114		
			Complete lock and handle R&L, chrome handle black strip	D-31-106	Complete lock and handle R&L black handle chrome strip	D-31-186	Use tumbler series P-31-111/114
Porsche	924	1980-82	Uncoded plug	D-31-306	Use tumbler series P-31-111/114		
			Complete lock & handle RH	D-26-111	Complete lock & handle LH	D-26-112	Use tumbler series P-31-111/114
Porsche	924	1986-88	Uncoded plug	D-31-306	Use tumbler series P-31-111/114		
Porsche	928	1978-86	Complete lock R&L	D-26-107	Discontinued when out, now available from Porsche dealers only Use tumbler series P-26-111/114		
Porsche	928	1987-95	Complete lock RH	D-26-109	Complete lock LH	D-26-110	Discontinued when out, now available from Porsche dealers only Use tumbler series P-31-111/114
Porsche	944	1982-88	Uncoded plug	D-31-306	Use tumbler series P-31-111/114		

Check www.carlocks.com for the most up to date information

DOOR LOCKS

Subaru	Justy	1987-94	Lock service package	D-16-206 (D-16-106)	Coded pair	DP-16-106	If original pawl cannot be reused, use P-16-335 (RH) or P-16-336 (LH) Use face cap P-16-205 Use tumbler series P-16-161/164
Subaru	Legacy	1989-94	Complete lock RH	D-29-105	Complete lock LH	D-29-106	Use tumbler series P-16-161/164
Subaru	Legacy	1995-99	Complete lock RH	D-29-113	Complete lock LH	D-29-114	Use tumbler series P-16-161/164
Subaru	Legacy	2000-04	Complete lock RH	D-29-116	Complete lock LH	D-29-117	Use tumbler series P-16-181/184
Subaru	Legacy	2005-07	Replacement locks available from Subaru dealers only Use tumbler series P-16-181/184				
Subaru	Outback	all	Outback is a sub-model of Legacy and Impreza, see the appropriate year Legacy or Impreza				
Subaru	SVX	1992-97	Complete lock RH	D-29-111	Complete lock LH	D-29-112	Use tumbler series P-16-161/164
Subaru	WRX	All	see Impreza				
Subaru	XT Coupe	1985-91	Coded lock	D-29-107	If original pawl cannot be reused use P-16-337 (RH) or P-16-338 (LH) Use tumbler series P-16-161/164		
Sunbeam	Most models	All	Coded plug	D-15-201	Tumblers are not available		
Suzuki	Aerio	2002-07	Complete lock RH	D-33-111	Complete lock LH	D-33-112	Use tumbler series P-30-181/188
Suzuki	Esteem	1995-02	Uncoded service pack	D-33-205	Previously sold as D-33-105 (RH) and D-33-106 (LH) If original pawl cannot be reused, use P-33-301 (RH) or P-33-302 (LH) Use tumbler series P-30-161/164		
Suzuki	Forenza	2004-07	Complete lock RH	D-50-123	Complete lock LH	D-50-124	Use tumbler series P-13-101/104 (P-21-111/114)
Suzuki	Forsa	1985-88	Complete lock with reversible pawl R&L	D-33-101	Coded pair with pawls	DP-33-101	Use face cap P-24-203 (old part no. P-30-202). Use tumbler series P-30-141/144
Suzuki	Grand Vitara	1999-02	Uncoded service pack	D-33-204	Original pawls must be reused. Use face cap P-20-265 Use tumbler series P-33-101/105		
Suzuki	Grand Vitara	2003-05	Complete lock with reversible pawl R&L	D-33-113	Use face cap P-30-217 Use tumbler series P-30-181/188		
Suzuki	Grand Vitara	2006-07	Replacement locks available from Suzuki dealers only.				
Suzuki	Reno	2005-07	Complete lock RH	D-50-123	Complete lock LH	D-50-124	Use tumbler series P-13-101/104 (P-21-111/114)
Suzuki	Samurai	1986-92	Complete lock with reversible pawl R&L	D-33-101	Coded pair with pawls	DP-33-101	Use face cap P-24-203 (old part no. P-30-202). Use tumbler series P-30-141/144
Suzuki	Samurai	1993-95	Coded lock	D-22-110	Use face cap P-30-217 chrome or P-30-218 black Use tumbler series P-30-161/164		
Suzuki	Sidekick	1989-98	Coded lock without pawl	D-33-203	Pawls available as follows: right side P-30-322, left side P-30-323 Use face cap P-33-201 Use tumbler series P-33-101/105		
Suzuki	Swift	1985-88	Complete lock with reversible pawl R&L	D-33-101	Coded pair with pawls	DP-33-101	Use face cap P-24-203 (old part no. P-30-202). Use tumbler series P-30-141/144
Suzuki	Swift	1989-94	Uncoded service pack	D-33-205	Previously sold as D-33-105 (RH) and D-33-106 (LH) If original pawl cannot be reused, use P-33-301 (RH) or P-33-302 (LH) Use tumbler series P-30-161/164		
Suzuki	Swift	1995-97	Coded lock (no pawl)	D-33-207	Previously sold as D-33-107 (RH) and D-33-108 (LH) If the original pawl cannot be reused, use P-33-303 (RH) or P-33-304 (LH) Use face cap P-30-217 Use tumbler series P-30-161/164		
Suzuki	Swift	1998-01	Uncoded service pack	D-33-204	Original pawls must be reused. Use face cap P-20-265 Use tumbler series P-33-101/105		
Suzuki	Swift (Canada) hatchback	2004-08	Complete lock RH	D-50-115	Complete lock LH	D-50-116	Use tumbler series P-13-101/104 (P-21-111/114)
Suzuki	Swift (Canada) sedan	2004-06	Complete lock RH	D-50-115	Complete lock LH	D-50-116	Use tumbler series P-13-101/104 (P-21-111/114)
Suzuki	Swift (Canada) sedan	2007-08	Complete lock RH	D-50-117	Complete lock LH	D-50-118	Use tumbler series P-13-101/104 (P-21-111/114)
Suzuki	SX-4	2007-08	Replacement locks available from Suzuki dealers only. Use tumbler series P-20-131/155				
Suzuki	Verona	2004-06	Complete lock RH	D-50-121	Complete lock LH	D-50-122	Use tumbler series P-13-101/104 (P-21-111/114)
Suzuki	Vitara	1999-04	Uncoded service pack	D-33-204	Original pawls must be reused. Use face cap P-20-265 Use tumbler series P-33-101/105		
Suzuki	X90	1996-99	Uncoded service pack	D-33-204	Original pawls must be reused. Use face cap P-20-265 Use tumbler series P-33-101/105		
Suzuki	XL-7	2001-02	Uncoded service pack	D-33-204	Original pawls must be reused. Use face cap P-20-265 Use tumbler series P-33-101/105		
Suzuki	XL-7	2003-06	Complete lock with reversible pawl R&L	D-33-113	Use face cap P-30-217 Use tumbler series P-30-181/188		

ASP PART NUMBERING SYSTEM

The ASP Part Numbering System

Working with the ASP part numbers is easier if you have a basic understanding of the part numbering system, explained here:

The first letter or letters of the part number identify what type of product the part number is:

A	Keying kits and parts assortments
B	Luggage compartment locks
C	Ignition locks
D	Door locks (including complete locks that include the door handle)
DH	Door handles (except complete locks that include the door handle)
DP	Door locks (keyed alike pair)
E	Engine compartment locks
F	Fasteners (including lock retaining clips, shear-head bolts, door panel fasteners, etc.)
G	Glove compartment and stowage locks
KB	Key blanks
P	Lock service parts (including tumblers, face caps, and other parts)
RK	Remote head key blanks
S	Lock sets
T	Fuel tank locks
W	Ignition switches (wiring assembly only without lock cylinder)

The second two digits of the part number tell you the PRIMARY brand of vehicle that the item is used on:

00	Various cars
11	Alfa Romeo
12	Audi
13	BMW
14	British Cars (Austin, Jaguar, Land Rover, MG, Range Rover, Triumph)
15	British Chrysler (Plymouth Cricket, Sunbeam, Hillman)
16	Nissan / Datsun / Infiniti
17	Fiat
18	European Ford (Capri, Fiesta, Merkur)
19	Honda / Acura
20	Mazda
21	Mercedes-Benz
22	Mitsubishi
23	GM Europe (Cadillac Catera, Pontiac Lemans, Opel)

24	Isuzu (including General Motors brands)
25	Peugeot
26	Porsche
27	Renault
28	Saab
29	Subaru
30	Toyota / Lexus / Scion / Hino truck
31	Volkswagen
32	Volvo
33	Suzuki
34	Lada
35	Lancia
36	Hyundai
37	Daihatsu
38	Citroen
39	Yugo
40	Kia
41	General Motors USA (Buick, Cadillac, Chevrolet, GMC, Oldsmobile, Pontiac)
42	Ford / Lincoln / Mercury (USA)
43	American Motors (including some Heavy Trucks and Jeep)
44	Chrysler / Dodge / Jeep / Plymouth
45	Skoda
49	Saturn
50	Daewoo (including Chevrolet Aveo, Saturn Vue, other General Motors brands)
55	Renault truck (including some Mack trucks)
56	Freightliner truck
57	Kenworth truck
93	Harley Davidson Motorcycle
94	Honda Motorcycle
98	Yamaha Motorcycle

For example, if you have part number C-30-107, by understanding the part numbering system you will know that the part is an ignition lock (first letter C), which fits a Toyota (second two digits 30).

There are exceptions to this system created by the same part being used on more than one brand of car. Also some parts are used in more than one place on the car – for example, B-14-210 is numbered as a luggage compartment lock, but also is used as an ignition lock or door lock on some cars.

ASP PART NUMBERING SYSTEM

The same part being used on more than one brand of car is explained by lock families, as follows:

Audi - also found on some Porsche and Volkswagen

Ford USA – also found on some Mazda and Nissan

Honda / Acura - also found on some Isuzu

Mazda – also found on some Chrysler imports, Ford imports, General Motors imports, GEO, Mitsubishi, Suzuki

Nissan - also found on some Subaru and Isuzu truck

Toyota – also found on some Chrysler imports, Daihatsu, General Motors imports, GEO, Hyundai, Isuzu, Kia, Mazda, Mitsubishi, Suzuki.

Volkswagen - also found on some Audi and Porsche (tumblers also used on BMW)

You will also find some parts that are used among the brands of the following groups of cars:

British cars - Aston Martin, Austin, English Ford, Jaguar, Jensen, Land Rover, MG, Morgan, Range Rover, Rover car, Sterling car, Triumph, TVR, Volvo.

French cars - Peugeot, Renault, Citroen

German cars - Audi, BMW, Daewoo, General Motors (Cadillac Catera, Chevrolet Aveo, Pontiac Lemans, others), Mini, Porsche, Mercedes-Benz, Volkswagen

Italian cars - Alfa Romeo, Bertone, Ferrari, Fiat, Iveco, Lada, Lamborghini, Lancia, Maserati, Pininfarina, Yugo

Lockcraft Part Numbers

The first two letters of the part number identify what type of product the part number is:

DL	Door lock
LC	Ignition lock
LS	Lock set
RP	Lock service parts (including tumblers, face caps, and other parts)
SK	Keying kits and parts assortments
TL	Luggage compartment locks

Lockcraft part numbers that end in “U” are uncoded locks.

There have been many changes to the Lockcraft part numbers over the past years, explained as follows:

Most old Lockcraft part numbers had no letter prefix. For example, old part number 1426 was changed to LC1426 to identify the type of product.

Some old Lockcraft part numbers had a letter prefix “A”, which was changed to “RP”. For example, part number A6001 was changed to RP6001. This could be confusing if you have an old Lockcraft or All Lock keying kit or parts assortment which identified the parts inside by the letter prefix “A”. When reordering simply change the “A” to “RP”.

Some old Lockcraft part numbers had a digit “3” at the end of the part number, which designated poly bag packaging. For example, part number LC14263 designated the LC1426 ignition lock in a poly bag. The currently used part numbers now eliminate the “3” at the end and using the example LC14263 is now simply LC1426.

Some old Lockcraft part numbers had a digit “8” at the end of the part number, which designated that it was an uncoded lock. For example, part number LC14268 designated the LC1426 ignition lock in uncoded form. The currently used part numbers now use “U” at the end of the part number instead of the “8”. Using the example LC14268 is now LC1426U.

PART NUMBER LISTING and POPULARITY RATINGS

Part Number Listings and Popularity Ratings

Pages 214-233 contain a complete listing of ASP part numbers, with the 2008 popularity rating for each part number. The popularity ratings are explained as follows:

A = Most popular items (lock cylinders and replacement parts)

B = Second most popular group of lock cylinders

Y = Replacement parts (keying kit refill tumblers, face caps, etc.), popularity equivalent to B-rated lock cylinders

C = Third most popular group of lock cylinders

Z = Replacement parts (keying kit refill tumblers, face caps, etc.), popularity equivalent to C-rated lock cylinders

H = Items not recommended for stock by distributors, these parts are normal stock items for the ASP warehouse and available for drop shipments (HI-SPEED delivery). Orders must be placed through your distributor, and are subject to stock on hand at ASP. Some distributors may have selected H-rated items in stock.

S = Special order items only, may not be in stock at ASP. These items may be subject to minimum order quantities if needed. Some distributors may have selected S-rated items in stock.

DWO = Discontinued when out. Some items may still have limited stock at ASP or at some distributors, but will not be restocked when existing supplies are sold out.

ASP products are sold through the network of locksmith supply distributors located throughout the USA and Canada.

With over 4,000 different part numbers in our range, it is impossible and impractical for distributors to keep every part number in stock. Thus we have assigned each of our part numbers a popularity rating to assist distributors in keeping stock. We have implemented new distributor stocking programs based on these popularity ratings. Please check www.carlocks.com for the most current information about our distributor stocking guidelines. ASP is working closely with our distributors to provide you the fastest delivery possible at the lowest possible cost.

Distributors who make a commitment to keep stock according to our recommendations are listed on www.carlocks.com. This list is subject to change at any time. Distributors who do not keep the stocking commitment will be removed from the list.

Explanation of other notes on the part number listing

a. Some items have (now use ...) to the right of the part number, with a rating of DWO.

For example: A-13-105 (now use A-31-110) – this means that A-13-105 has been superseded by A-31-110.

b. Some items have (substitute ...) to the right of the part number, with a rating of DWO.

For example: B-19-154 (substitute B-19-155) - this means that you can substitute B-19-155 for B-19-154, but there is some difference between the two parts. A complete listing of these part numbers with a brief explanation of the difference between each superseded part and the replacement part is provided on pages 234-237.

c. Some items have (see ...) to the right of the part number, with no popularity rating.

For example: B-16-105 (see B-16-205), with no popularity rating. Then go to B-16-205 and you will see it listed as B-16-205 (B-16-105) with the popularity rating of B. This is a result of our consolidating some similar interchangeable part numbers. In this example, whether you order B-16-105 or B-16-205, you will get the same part at the same price. A complete listing of these part numbers is provided on pages 238-239.