



▶▶ LinkRunner™ Pro and Duo Network Multimeters

LinkRunner Pro and Duo Network Multimeters empower technicians to resolve a broader range of today's connectivity problems. Unlike traditional 10/100 link testers, LinkRunner Pro and Duo verify Gigabit links – increasingly important for today's high-performance networks. They also ping up to 10 key devices, detect Power over Ethernet (PoE), resolve 802.1X security conflicts, verifies cable wiremap, and identifies the nearest switch port with Cisco, Extreme, and IEEE Link Layer Discovery Protocols (CDP/EDP/LLDP). Built-in IntelliTone digital toning precisely locates cables at patch panels and switches. Link status reports can be uploaded from USB port and routed with trouble tickets to expedite problem resolution.

- Choose LinkRunner Pro for 10/100/Gig copper or LinkRunner Duo for 10/100/Gig copper and just add an SFP for 100/Gig fiber
- Link at 10/100/Gig – identify device capabilities and confirm actual speed/duplex status
- Ping key devices – measure response of DHCP, router, DNS, and other devices or URLs
- Verify 802.1X settings – authenticate with EAP type, user name, certificates, and password (LinkRunner Duo supports up to 2k certificates. LinkRunner Pro supports up to 1k certificates.)
- Detect PoE service – verify voltage level and pairs to IEEE 802.3af specifications
- Identify switch port – supports Cisco, Extreme, and IEEE Link Layer Discovery Protocols
- Test cable wiremap – measure length, detect miswires, shorts, split pairs or opens
- Locate and ID cable – use IntelliTone or optional IDs to locate cables at patch panels
- Document results – upload link status reports with USB port for faster problem resolution

Model	Description
LRDUO	LinkRunner Duo Network Multimeter – includes LinkRunner Duo, Wireview Cable ID #1, LinkRunner Connect Software CD, USB cable, RJ-45 coupler, LinkRunner Duo getting started guide, four (4) AA alkaline batteries
LRPRO-1000	LinkRunner Pro Network Multimeter – includes LinkRunner Pro, WireView Cable ID #1, LinkRunner Connect software CD, USB cable, LinkRunner Pro Getting Started Guide (English, Spanish, French, German, Japanese, Simplified Chinese), four (4) AA alkaline batteries
LRPRO-REFLECT	LinkRunner Pro with Reflector option
LINKRUNNER	LinkRunner Network Multimeter 10/100 Mbps
GLD-LR	1-year of Gold Support – LinkRunner
Kits	
CIQ-GSV	CableIQ Gigabit Service Kit – includes CableIQ Qualification Tester, LinkRunner Pro Network Multimeter, IntelliTone Pro 200 Probe, CableIQ Remote Identifiers #1-7, WireView Cable ID #1 and CableIQ Reporter Software CD
LRPRO-KIT	LinkRunner Pro Extended Test Kit – includes LinkRunner Pro, IntelliTone Pro 200 Probe, WireView Cable IDs #1-6, clip-set RJ-45 to eight alligator clip bare wire adapter and LinkRunner Connect software CD
LRDUO-FTK	LinkRunner Duo copper/fiber network troubleshooting kit – includes LinkRunner DUO and a Simplifiber Pro multimode fiber verification kit
Options	
LRPRO-Reflect-opt	Reflector option for LinkRunner Pro
Accessories	
MS-SX	SX Gig Fiber DMM SFP transceiver (required for fiber testing)
MS-LX	LX Gig Fiber DMM SFP transceiver (required for fiber testing)
ES2-ZX	ZX Gig Fiber DMM SFP transceiver (required for fiber testing)
LRPRO-LION	Lithium-Ion battery pack for LinkRunner Pro with AC adapter