Product Specifications

COMMSCOPE®

103801254 | 110C-5

110 Connecting Block, 5 pair count, 10 per package

Dimensions

Depth	23.62 mm | 0.93 in
Height	6.35 mm | 0.25 in
Width	38.10 mm | 1.50 in

Environmental Specifications

Operating Temperature	-10 °C to +60 °C (+14 °F to +140 °F)
Safety Standard	cUL | UL

General Specifications

Product Type	Block
Color	White
Lug Attachment	Field attached
Package, quantity	10
Pairs, quantity	5

Mechanical Specifications

Conductor Gauge, stranded	22 AWG | 23 AWG | 24 AWG | 26 AWG
Material Type	Copper alloy
Outlet/Module Contact Plating	Nickel
Plug Insertion Life, minimum	200 times

Regulatory Compliance/Certifications

Agency	Classification
RoHS 2002/95/EC	Compliant
ISO 9001:2008	Designed, manufactured and/or distributed under this quality management system

©2012 CommScope, Inc. All rights reserved. All trademarks identified by ® or ™ are registered trademarks, respectively, of CommScope.
All specifications are subject to change without notice. See www.commscope.com for the most current information. Revised: February 19, 2012