

COMPLEMENTARY
PRODUCTSMDVO Multimedia
Module
6.7.20-AIBDN Copper
SolutionsWorkstation Outlets
MediaFlex KitsMediaFlex Faceplate Kit
6.7.6-A

MediaFlex Inserts

MediaFlex MDVO
(style) Insert
6.7.8-A

Interface Plates

Interface Plate, Flush
6.7.10-A

MDVO Faceplates

MDVO Faceplate, Flush
6.7.11-AMDVO Angled
Entry Faceplates**6.7.12-A**

MDVO Side Entry Boxes

6.7.14-A

MDVO 106 Adapters

6.7.15-A


MDVO Deco Adapters

6.7.16-AMDVO Modular
Furniture Adapters**6.7.17-A**European Style
Faceplates & AdaptersEuropean "6C" Shuttered
Module Holder**6.7.18-B**French Style Faceplate
6.7.18-CMDVO Multimedia
Outlet Boxes**6.7.19-A**

Multi-User Outlet Boxes

6.7.21-A**6.7.20-A MDVO Multimedia Module**

A0649254 SC Duplex Adapter



A0407008 MDVO ST Compatible Fiber Module



A0406997 MDVO BNC Coaxial Module



A0407000 MDVO Video F Coaxial Module



AX101467 MDVO MT-RJ Fiber Module



A0407005 MDVO SC Fiber Module

DESCRIPTION

MDVO Multimedia Modules address audio/video and fiber applications. Fiber modules are available for ST Compatible multimode and MT-RJ multimode & singlemode connections. The SC Duplex Adapter is a fiber adapter sleeve with flanges that mounts into the SC Duplex mounting bezel (included in the MDVO Multimedia Outlet box). Audio/video modules are available for S-VHS, RCA, BNC and Video F connections. For custom multimedia connections, consult your NORDX/CDT sales representative.

APPLICATIONS

- Multi-user telecommunications outlets
- Consolidation points
- Patch panels.

TECHNICAL SPECIFICATIONS

- SC Duplex Adapter: 9.5 x 35 x 28 mm (0.38 x 1.38 x 1.10 in.)
- ST Compatible, SC simplex, S-VHS, RCA, BNC Coaxial, Video F Coaxial: 20 x 20 x 33 mm (0.78 x 0.78 x 1.30 in.)
- MT-RJ: 20 x 20 x 28 mm (0.78 x 0.78 x 1.10 in.).

INSTALLATION TIPS

- Verify clearance space before inserting into MDVO faceplates, adapters or boxes
- Label each port carefully for future reference and ease of administration
- Preferably use MDVO Multimedia or Multi-User Outlet Boxes for fiber optic installations.

PACKAGING

10 units packaged in a clear plastic bag.

ORDERING INFORMATION

6.7.20-A MDVO Multimedia Module

DETAIL	COLOR	INSERT	UPC	ORDERING NUMBER
RCA, feedthrough	Gray	Black		AX101823
RCA, feedthrough	Almond	Black		AX101824
RCA, feedthrough	White	Black		AX101825
RCA, feedthrough	Black	Black		AX101826
RCA, feedthrough	Gray	Black		AX101827
RCA, feedthrough	Almond	Black		AX101828
RCA, feedthrough	White	Red		AX101829
RCA, feedthrough	Black	Red		AX101830
RCA, feedthrough	Gray	Black		AX101831
RCA, feedthrough	Almond	Black		AX101832
RCA, feedthrough	White	Black		AX101833
RCA, feedthrough	Black	Black		AX101834
RCA, feedthrough	Gray	Black		AX101835
RCA, feedthrough	Almond	Black		AX101836
RCA, feedthrough	White	Black		AX101837
RCA, feedthrough	Black	Black		AX101838
S-VHS, feedthrough	Gray			AX101839
S-VHS, feedthrough	Almond			AX101840
S-VHS, feedthrough	White			AX101841
S-VHS, feedthrough	Black			AX101842
SC simplex	Gray	Red		A0407003
SC simplex	Almond	Red		A0407004
SC simplex	White	Red		A0407005
SC Duplex Adapter	Almond	Black		A0649254
MT-RJ, Singlemode	Blue	Yellow		AX101466
MT-RJ, Multimode	Almond	Yellow		AX101467
ST Compatible	Gray	Red		A0407007
ST Compatible	Almond	Black		A0407008
ST Compatible	White	Black		A0407009
ST Compatible	Black	Black		A0407010
Coaxial, BNC	Gray	phosphor bronze sleeve		A0406995
Coaxial, BNC	Almond	phosphor bronze sleeve		A0406996
Coaxial, BNC	White	phosphor bronze sleeve		A0406997
Coaxial, BNC	Black	phosphor bronze sleeve		A0406998
Coaxial, VIDEO F	Gray	phosphor bronze sleeve		A0406999
Coaxial, VIDEO F	Almond	phosphor bronze sleeve		A0407000
Coaxial, VIDEO F	White	phosphor bronze sleeve		A0407001
Coaxial, VIDEO F	Black	Red		A0407002