THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



PANDUIT P/N	WEIGHT
SRM19X25A1	21.1 LBS/EACH 9.6 Kg/EACH

NOTES:
1. VISIT OUR ON-LINE CATALOG AT WWW.PANDUIT.COM FOR A CURRENT LIST OF PRODUCTS APPLICABLE FOR USE WITH THIS PART.
2. COMPONENTS:
   1- SHELF
   2- MOUNTING BRACKETS
   4- #10-32 X 3/8" UNDERCUT SCREWS
   8- #12-24 X 1/2" SCREWS
   8- M6 METRIC SCREWS
3. SHELF CAN BE ADJUSTED TO 2 POSITIONS.
4. DIMENSIONS IN PARENTHESIS ARE METRIC.
5. LOAD CAPACITY OF 250 LBS.





MODEL FILENAME: V10254AB_NF_25SHLF_ASSY_01.PRT

CAD FILENAME/LAYERS: V10254AB_DC_01A.PRT

PANDUIT CORP. TINLEY PARK, ILLINOIS

19" X 25" ADJUSTABLE RACK MOUNT SHELF (SRM19X25A1) CUSTOMER DRAWING

UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE:
(.X) ± .03 (.XXX) ± .005
(.XX) ± .015 ANGLES ± 1°

UNLESS OTHERWISE SPECIFIED, ALL DIMENSIONS ARE GIVEN IN INCHES, THIRD ANGLE PROJECTION.

DRAWN BY: TKW
DATE: 10-19-04
CHK'D:
MAT'L: STEEL- POWDER COATED BLACK
SCALE: NONE
DRAWING NO.: 10254-04
DWG SIZE: A

REV	DATE	BY	CHK	DESCRIPTION	ECN - R	CUST	SUP	OTH
R	10-19-04	TKW		RELEASED TO PRODUCTION	10254-04			