

Basket Trays

Cablofil

EZ-Path Firestop

EZ-Path from Cablofil provides total containment and fire protection in both data communications cabling, low and high voltage wiring network applications. It installs in minutes and new cables can be added or existing wiring removed without the need for additional fire stopping.

EZ-Path offers maximum resistance to fire whether it is empty or 100% visually full. Fast-acting intumescent performance: features a built-in firestopping system that automatically adjusts to the number of cables installed. Exposed to fire or high temperatures, this intumescent material responds to flames or heat by quickly sealing the pathway and preventing the passage of flames and smoke.

Certified product: EZ-Path installations offer fire-rated floor and wall constructions up to 240 minutes in accordance with the main European standards, BS 476: Part 20, DIN 4102-9 and EN 1366-3, and the American standard ASTM E814(UL1479).



Anixter No	Vendor No	Description
EZ-PATH COMPLETE KIT		
319461	250028	EZ-Path firestop device kit 75mm high x 75mm wide x 267mm long, includes 2 wall plates 102mm x 102mm
319464	250518	EZ-Path Mini fire-rated device kit, 37mm high x 37mm wide x 267mm long, includes 2 wall plates 76mm wide x 76mm long
325419	250068	EZ-Path Max firestop device kit, 102mm high x 116mm wide x 353mm long, includes 2 wall plates 191mm high x 178mm wide



EZ-Path Firestop EZD 33



Anixter No	Vendor No	Description
EZ-PATH DEVICES AND ACCESSORIES		
319462	250018	EZ-Path firestop device, 75mm high x 75mm wide x 267mm long, does NOT include wall plates
319465	250110	Single wall plates, one pair for installing one EZ-Path device Anixter Number 319462, 102mm x 102mm
319466	250120	Double wall plates, one pair for installing two EZ-Path devices Anixter Number 319462, 185mm wide x 108mm high
319467	250130	Triple wall plates, one pair for installing three EZ-Path devices Anixter Number 319462, 26mm wide x 108mm high
319468	250140	Four-gang wall plates, one pair for installing four EZ-Path devices Anixter Number 319462, 406mm wide x 108mm high
319469	250170	Seven-gang wall plates, one pair for installing seven EZ-Path devices Anixter Number 319462, 610mm wide x 108mm high
319470	250210	Single, large type 'renovation' wall plates, one pair used for installing one EZ-Path device Anixter Number 319462, 203mm wide x 253mm high
319471	250220	Single wall plate, round, diameter 139mm used for installing one EZ-Path device Anixter Number 319462
319472	250206	Exit module for cable radius control, one pair
325422	250078	EZ-Path extension module 75mm high x 75mm wide x 150mm long, increases EZ-Path device Anixter Number 319462 (length for thicker walls)

1
2
3
4
5
6
7
8
9
10
11
12
13
14
15
16
17
18
19

Basket Trays

Cablofil

EZ-Path Firestop EZD 44

Anixter No	Vendor No	Description
EZ-PATH DEVICES AND ACCESSORIES		
325418	250058	EZ-Path Max firestop device, 102mm high x 116mm wide x 353mm long, does NOT include wall plate
325420	250111	Single wall plates, one pair for installing one EZ-Path Max device Anixter Number 325418, 191mm high x 178mm wide
325421	250250	Wall plates, one pair for installing one to five EZ-Path Max devices Anixter Number 325418

