THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



PANDUIT P/N	WEIGHT
FR12USB	4.67 LB/PC. (2116g /PC.)

NOTES:

1. SEE CURRENT CATALOG FOR ADDITIONAL PART SUFFIXES TO INDICATE PACKAGE QUANTITY.
2. THE FR12USB KIT INCLUDES:
   - ONE (1) UNDERFLOOR STRUT ASSEMBLY CONTAINING:
     - ONE (1) UNDERFLOOR STRUT,
     - TWO (2) FIBERRUNNER STRUT CLIPS,
     - TWO (2) 1/4-20 CHANNEL NUT,
     - TWO (2) 1/4 HELICAL SPRING LOCKWASHER,
     - TWO (2) 1/4-20 X 7/8 HEX HEAD MACHINE SCREW.
   - TWO (2) UNDERFLOOR SUPPORT BRACKETS,
   - TWO (2) 3/8-16 HEX NUT,
   - TWO (2) 3/8-16 X 3/4 HEX HEAD CAP SCREW,
   - TWO (2) 3/8 HELICAL SPRING LOCKWASHER,
   - TWO (2) 5/16-18 X 5 SQUARE BEND U-BOLT,
   - TWO (2) 5/16 RETAINING WASHER,
   - FOUR (4) 5/16-18 HEAVY HEX NUT,
   - FOUR (4) 5/16 HELICAL SPRING LOCKWASHER.
3. FINISH COLOR: BLACK (EXCEPT HARDWARE)
4. DIMENSIONS IN PARENTHESIS ARE IN METRIC.



ENG. REF.: D37797EP_DC_FR12USB_01A.prt

CAD FILENAME/LAYERS: 37797-98.PDF

PANDUIT CORP. TINLEY PARK, ILLINOIS

FIBERRUNNER™ 12x4 UNDER FLOOR SUPPORT BRACKET (FR12USB)
CUSTOMER DRAWING

UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE:
(.X) ± (.XXX) ±
(.XX) ±.03(.8) ANGLES ±

UNLESS OTHERWISE SPECIFIED, ALL DIMENSIONS ARE GIVEN IN INCHES, THIRD ANGLE PROJECTION.

REV	DATE	BY	CHK	DESCRIPTION	ECN	CHK	CUST	SUP
1	11-12-01	JHNU		A. REVISED PART GEOMETRY.	37797-98			
R	5-16-01	JHNU	CFG	RELEASED TO PRODUCTION.	37797-98	HIW	HIW	

DRAWN BY: JHNU
DATE: 5-16-01
CHECKED BY: CFG
MAT'L: STEEL
SCALE: NONE
DRAWING NO.: 37797-98
DWG SIZE: A