THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

A

PANDUIT PART NUMBER	WEIGHT
FRRF126RSC	0.54 LB/EACH (243g/EACH)

E



D NOTES:

1. SEE CURRENT CATALOG FOR ADDITIONAL PART SUFFIXES TO INDICATE COLOR AND/OR PACKAGE QUANTITY.
2. THE FIBERRUNNER 12x4 TRANSITION RIGHT WITH 6" EXIT SPLIT COVER REQUIRES NO TOOLS FOR INSTALLATION AND/OR REMOVAL. THE SPLIT COVER CREATES A 1/2" (12.7) RADIUSED OPENING TO ALLOW FOR NEW CABLES TO BE ADDED WITHOUT THE NEED FOR REMOVING THE COVERS.
3. DIMENSIONS IN PARENTHESES ARE IN METRIC.







ENG. REF.: D37617E0_DC_FRRF126RSC_01.prt

CAD FILENAME/LAYERS C FRRF126RSC.pdf

PANDUIT CORP TINLEY PARK, ILLINOIS

FIBERRUNNER 12x4 TRANSITION RIGHT WITH 6" EXIT SPLIT COVER (FRRF126RSC)

B CUSTOMER DRAWING

UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE:
(.X) ± (.XXX) ±
(.XX) ±.03 (.8) ANGLES ±

UNLESS OTHERWISE SPECIFIED, ALL DIMENSIONS ARE GIVEN IN INCHES, THIRD ANGLE PROJECTION.

REV	DATE	BY	CHK	DESCRIPTION	ECN	-	R	CUST	SUP	GMBH
-	--------	---	---	E. REVISED PART WEIGHT	--------		--	--		
-	--------	---	---	D. REVISED GENERAL NOTES C. REVISED CAD FILENAME	--------		--	--		
1	7-17-06	DTP	RN	B. REVISED DRAWING TITLE A. REVISED AND REDRAWN	37617-115		RN	RN		

DRAWN BY: JHNU
DATE: 5-25-01
CHK'D: HIW
MAT'L: ABS
SCALE: NONE
DRAWING NO.: 37617-115
DWG SIZE: A