THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

B



PANDUIT PART NUMBER	WEIGHT
FRSLNKT12 FRSLNKT12M	0.20 LB/EACH (90g/EACH)

E

F NOTES:

1. SEE CURRENT CATALOG FOR ADDITIONAL PART SUFFIXES TO INDICATE PACKAGE QUANTITY.
2. THE FIBER ROUTING SPLIT LOCK NUT KIT - 1/2" (M12) THREADED ROD INCLUDES;
   TWO (2) 1/2-13 SPLIT LOCK NUTS (FRSLNKT12 ONLY),
   TWO (2) M12x1.75 SPLIT LOCK NUTS (FRSLNKT12M ONLY)
3. FINISH COLOR: CLEAR ZINC PLATE
4. DIMENSIONS IN PARENTHESES ARE IN METRIC.







ENG. REF.: D38241BG_DC_FRSLNKT12_01.prt

CAD FILENAME/LAYERS C FRSLNKT12.pdf

PANDUIT CORP TINLEY PARK, ILLINOIS

D FIBER ROUTING SPLIT LOCK NUT KIT - 1/2" (M12) THREADED ROD (FRSLNKT12, FRSLNKT12M)
CUSTOMER DRAWING

UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE:
(.X) ± (.XXX) ±
(.XX) ±.03 (.8) ANGLES ±

UNLESS OTHERWISE SPECIFIED, ALL DIMENSIONS ARE GIVEN IN INCHES, THIRD ANGLE PROJECTION.

DRAWN BY JHNU
MAT'L: STEEL
SCALE NONE
DATE 11-7-01
CHK'D HIW
DRAWING NO. 38241-06
DWG A SIZE

REV	DATE	BY	CHK	DESCRIPTION	ECN	-	R	CUST	SUP	GMBH
-	--------	---	--	F. REVISED GENERAL NOTES.	--------		--	--		
-	--------	---	--	E. REVISED PART WEIGHT. D. REVISED DRAWING TITLE.	--------		--	--		
2	12-29-06	MSO	RN	C. REVISED CAD FILENAME. B. REVISED AND REDRAWN.	38241-06		RN	RN		