


IP Infrastructure Solutions

Glide Cable Manager Vertical and Horizontal Cable Management



Upper and lower crossover managers with vertical cable managers enable easy, intuitive cable routing.

Features

- Integrated front, rear, horizontal, and vertical cable management
- Patented rib cage design eliminates horizontal support trays and bars
- Supports up to 912 ports on a single rack
- Built-in bend radius protection ensures network integrity
- Designed for quick and easy moves, adds, and changes
- Optional slack managers available for 8-, 10-, and 12-inch widths
- Fits standard EIA rack with three-inch channel
- Used for single rack or as inter-rack unit
- Optional crossover troughs and horizontal cable managers available
- Optional EIA-standard horizontal support bars available




IP Infrastructure Solutions

Glide Cable Manager

7104 • 1292848 Glide Cable Manager

Ordering Information

Description	Ordering Number
Glide cable manager, vertical mount – to equip both sides of a 7-foot rack, order two Glide Cable Manager units	
6", front only, without slack manager	ADCCMVIB06F-2
6", front only, with slack manager	ADCCMVIBS06F-2
6", without slack manager	ADCCM-06
8", without slack manager	ADCCM-08
10", without slack manager	ADCCM-10
12", without slack manager	ADCCM-12
8", with slack manager	ADCCMS-08
10", with slack manager	ADCCMS-10
12", with slack manager	ADCCMS-12
Crossover trough, 2 RU	ADCCMTG02
Crossover trough, 4 RU	ADCCMTG04
Hinged black metal cover kits: to equip both sides of a 7' rack (front and back), order 2 cover kits.	
41" x 6"	ADCCMVIBC06B4
41" x 8"	ADCCMVIBC08B4
41" x 10"	ADCCMVIBC10B4
41" x 12"	ADCCMVIBC12B4
Hinged black metal cover kits: to equip both sides of a 7' rack (front only), order 2 cover kits. These covers are for Glide Cable Managers ADCCMVIB06F-2 and ADCCMVIBS06F-2 only.	
41" x 6", two per pack	ADCC06-2



Glide Cable Manager
Shown in Cabinet




Cover in Black Metal

Ordering Information

Description	Ordering Number
Glide cable manager, cabinet mount – ships 4 per pack	
6" x 10 RU	ADCCMVIB-CB10-4
6" x 20 RU	ADCCMVIB-CB-4
Glide cable manager, cabinet mount, with cable retention – ships 4 per pack	
3" x 20 RU	ADCCMVIB-3CB20-4
6" x 20 RU	ADCCMVIB-6CB20-4

Notes: Equips standard 7' cabinet with front or rear cable management.
Order two 4-packs to equip front and rear of cabinet.



Glide Cable Manager,
Cabinet Mount



IP Infrastructure Solutions

Glide Cable Manager

Glide Cable Manager

7104 • 1292848

Ordering Information

Description	Ordering Number
Crossover troughs	
2 RU, black	ADCCMTG02
4 RU, black, 23" rack	ADCCMTG04-23
4 RU, black	ADCCMTG04
Horizontal cable managers	
2 RU	ADCCMHIB-2U
3 RU	ADCCMHIB-3U
4 RU	ADCCMHIB-4U
With slack managers, 3 RU	ADCCMHIBS-3U
With slack managers, 4 RU	ADCCMHIBS-4U
Rear cable management bar, 19"	
1" extension	ADCCMRSB
Rear cable management bar, 19"	
4" extension	ADCCMRSB-4
Slack manager	ADCCMVIBSP
Stabilizers	
6.18"	ADCCMVESB06
8.38"	ADCCMVESB08
10.18"	ADCCMVESB10
12.18"	ADCCMVESB12
Extender brackets, 19" to 23"	
1 RU	EB-17B
2 RU	EB-35B
4 RU	EB-70B



2 RU Crossover Trough



4 RU Crossover Trough



Horizontal Cable Manager



Stabilizer



Slack Manager

Note: Stabilizer used at end of line-up for each Vertical Integrator section.

Ordering Information

Description	Spacing	Ordering Number
7' equipment racks		
Self-assembly aluminum relay rack, 3" channel		
Black	19" EIA	ADCRACKBLK73
Brushed aluminum	19" EIA	ADCRACKMF73
Welded steel relay rack, 3" channel, black	19" EIA	ADCRACKBLK73WS
Welded steel relay rack, Zone 4 rated, black		
Unequal flange	19" EIA	ADCRACKBLK73UE-75
Network unequal flange	23" EIA	PWUEF-7ERN-BLK



Web Site: www.adc.com

From North America, Call Toll Free: 1-800-366-3891 • Outside of North America: +1-952-938-8080 Fax: +1-952-917-3237
For a listing of ADC's global sales office locations, please refer to our web site.

ADC Telecommunications, Inc., P.O. Box 1101, Minneapolis, Minnesota USA 55440-1101

Specifications published here are current as of the date of publication of this document. Because we are continuously improving our products, ADC reserves the right to change specifications without prior notice. At any time, you may verify product specifications by contacting our headquarters office in Minneapolis. ADC Telecommunications, Inc. views its patent portfolio as an important corporate asset and vigorously enforces its patents. Products or features contained herein may be covered by one or more U.S. or foreign patents. An Equal Opportunity Employer

