THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

N

PANDUIT PART NUMBER	WEIGHT
FRUIB-X	0.55 LB/10 PCS (249g/10 PCS)

O

NOTES:

1. SEE CURRENT CATALOG FOR ADDITIONAL PART SUFFIXES TO INDICATE PACKAGE QUANTITY.
2. THE FIBER ROUTING UNIVERSAL INNERDUCT BRACKET ALLOWS FOR INNERDUCT OR CORRUGATED LOOM TUBING TO BE MOUNTED TO ANY FLAT SURFACE.
3. THE FIBER ROUTING UNIVERSAL INNERDUCT BRACKET KIT INCLUDES:
   ONE (1) UNIVERSAL INNERDUCT BRACKET,
   TWO (2) 1/4-20 HEX KEPS NUTS.
4. DIMENSIONS IN PARENTHESES ARE IN METRIC.





ENG. REF.: D37363CK_DC_FRUIB_03.prt

CAD FILENAME/LAYERS: FRUIB-X.pdf

PANDUIT CORP TINLEY PARK, ILLINOIS

FIBER ROUTING UNIVERSAL INNERDUCT BRACKET (FRUIB-X)
CUSTOMER DRAWING

UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE:
(.X) ± (.XXX) ±
(.XX) ±.03 (.8) ANGLES ±

UNLESS OTHERWISE SPECIFIED, ALL DIMENSIONS ARE GIVEN IN INCHES, THIRD ANGLE PROJECTION.

REV	DATE	BY	CHK	DESCRIPTION	ECN	-	R	CUST	SUP	GMBH
-	--------	---	--	P. ADDED LOCAL NOTE	--------		--	--		
3	7-25-06	DTP	RN	O. REVISED PART WEIGHT N. REVISED AND REDRAWN	37363-24		RN	RN		

DRAWN BY: JHNU
DATE: 6-22-00
CHK'D: JAWA
MAT'L: STEEL
SCALE: NONE
DRAWING NO.: 37363-24
DWG SIZE: A