



CS70N™ Professional Wireless Headset System

No compromises. Performance, style and comfort all in one.

Beauty and brains. Style and smarts. Get the best of both worlds with the CS70N professional wireless headset system — the perfect marriage of premium audio performance and sleek styling. Link the CS70N to any business phone, and let the no-compromises design make you more accessible, more comfortable, and more productive. Intelligent, high-performance features make this headset perfect for intensive, all-day phone use, technology connoisseurs that demand cutting-edge electronics — or anyone in a cubicle that just wants a great headset.

- **Crystal-clear conversation.** Featuring a top-of-the-line, Noise-Canceling microphone for clear speech in environments with distracting background noise
- **Talk anywhere.** Enables both speaker and listener to communicate distinctly and intelligibly — even in noisy cubicle environments
- **All-day comfort.** Behind-the-ear design keeps the CS70N discreet and comfortable enough that it's easy to forget you're wearing it
- **VoIP performance.** Superior microphone and speaker combine to create a high-performance headset that yields great results for traditional phone lines and IP Telephony systems

The Professional Wireless Series

Plantronics professional wireless headsets are designed to allow workplace mobility while boosting reachability — with models to fit every need. Based on best-in-class wireless technology, each conversation is kept crystal clear and secure, and with plenty of battery in-use time. Benefits include:

- **Talk hands-free:** use a keyboard and mouse, lead a Webinar, reach for a file
- **Increase mobility:** bring landline calls to the conference room, printer, fax
- **Move naturally:** un-tangle from cords, work ergonomically, all day
- **Stay available:** remote answer/end means no more missed calls
- **Block interference:** from other wireless devices with voice-dedicated 1.9GHz DECT™ radio frequency



CS70N Key Features

Radio Frequency Technology	1.9GHz DECT™
Wearing Style	Behind ear
Recommended Environment	All environments, even those with average-to-loud ambient noise
Digital Encryption	64-bit
Roaming Range	Up to 300 ft.
Headset Weight	0.75 oz
Headset Controls	Volume, mute, call answer/end
Battery Recharge Time	1.5 hours for 80% charge, 3 hours for 100% charge
In-Use Battery Life	6 hours
Microphone Style	Noise-Canceling
Remote Ring Notification	Yes*
Single Button Call Control	Yes
Integrated Base/Charging Cradle	Yes



>>> >> CS70N Wireless Headset System with HL10
Telephone not included

*Optional HL10 Handset Lifter Accessory

The HL10 Handset Lifter adds the convenience of remote ring notification and one-touch answering and ending calls while away from your desk by lifting your deskphone handset when a call comes in.



The CS70N is currently approved for use in the United States and Canada.



PLANTRONICS
SOUND INNOVATION™



For more information about CS70N or other Plantronics products, please visit our Web site at: www.plantronics.com

TEL: 800-544-4660 (USA AND CANADA)
831-458-7700 (OUTSIDE USA)

©2007 Plantronics, Inc. All rights reserved. Plantronics, the logo design, CS70N, and Sound Innovation are trademarks or registered trademarks of Plantronics, Inc. All other trademarks are the property of their respective owners. DECT is a trademark of ETSI. Space photo imagery courtesy of NASA. Printed 03.07. OPS-14

Sound Innovation for missions to the moon. And for everyday life on this planet, too.

In 1969, a Plantronics headset carried the historic first words from the moon: "That's one small step for man, one giant leap for mankind." Today, we're the headset of choice in mission-critical applications such as air traffic control and 911 dispatch. This history of proven sound innovation is the basis for every product we build—whether it's for work, for home or on the go.

