

# UniCam® Pretium™ -Performance Single-Mode Connectors LC, SC, ST® Compatible

A LANscape® Pretium Solutions Product

## Applications

- Local area networks, including main cross-connect, intermediate cross-connect, horizontal cross-connect
- Ideal for fiber-to-the-workstation applications where installation setup and teardown time is critical
- Anywhere low-loss connectivity is critical
- Data centers

## Description


With UniCam® Pretium™ -Performance Connectors, best-in-class optical performance is available in a fast, easy field-termination solution for single-mode fibers.

These patented, high-precision ceramic ferrule LC, SC and ST® Compatible single-mode connectors offer Pretium-performance capability – an outstanding 0.2 dB typical/0.5 dB maximum insertion loss per connector pair when installed with the UniCam Pretium Tool Kit. This lightweight, handheld installation tool and the high-performance cleaver virtually eliminate human variability from installation, for terminations that are performed right, the first time, every time. The result: the superior optical performance that you require for your most demanding single-mode applications.


While UniCam Pretium-Performance Single-Mode Connectors are compatible with the standard UniCam Connectors Tool Kit, the true Pretium-performance capability of these connectors can only be guaranteed with the UniCam Pretium Tool Kit.

The UniCam Pretium Tool Kit can quickly install a UniCam Connector in about 45 seconds. From the cleaver, with its integrated fiber scrap bin and dual-clamp precision hold, to the installation tool with its immediate go/no-go feedback signal, the UniCam Pretium Tool Kit was thoughtfully designed with the needs of network installers in mind.

Installation is as easy as strip, clean, cleave, cam and crimp – with exceptional optical performance guaranteed. Every UniCam Connector is 100 percent guaranteed to meet the published specification at the time of installation, or Corning Cable Systems will replace it.



UniCam Pretium-Performance  
SC Single-Mode Connectors | Photo LAN620



UniCam Pretium-Performance  
LC Single-Mode Connector | Photo LAN625

CORNING

LANscape®  
Pretium™ Solutions

Product Specifications

# UniCam® Pretium™ -Performance Single-Mode Connectors LC, SC, ST® Compatible

A LANscape® Pretium Solutions Product

## Features / Benefits

- Typical insertion loss of 0.2 dB and maximum insertion loss of 0.5 dB for best-in-class optical performance, when installed using the UniCam® Pretium™ Tool Kit
- Broad operating temperature range (-40° to +75°C) for true utility and flexibility, when installed using the UniCam Pretium Tool Kit
- UniCam Pretium Tool Kit virtually eliminates human variability in installation, ensuring consistent, reliable results
- Available in single packs and the new UniCam Connector organizer packs
- Fast termination, high-installation yields and no consumables mean lowest installed cost
- Factory-polished end-face for consistent optical performance and factory quality
- 100 percent factory tested for insertion loss
- 100 percent guaranteed\*
- Direct 250 µm termination SC and LC connectors available
- Reliable, proven technology, with more than 40 million sold

\* UniCam Connectors are guaranteed to meet the published specification at the time of installation.



UniCam Pretium Installation Tool | Photo LAN770



Pretium Cleaver | Photo LAN805



UniCam Connector Organizer Pack (Multimode SC Connectors shown)  
Photo LAN809



UniCam Pretium Tool Kit | Photo LAN769

# UniCam® Pretium™ -Performance Single-Mode Connectors

## LC, SC, ST® Compatible

A LANscape® Pretium Solutions Product

### Specifications

| Connector Style | Polish | Insertion Loss<br>Typical<br>Maximum (dB) <sup>1</sup> | Reflectance (dB) <sup>2</sup> | Housing<br>Color Code | Boot Color <sup>3</sup> |
|-----------------|--------|--|-------------------------------|-----------------------|-------------------------|
| LC              | SPC    | 0.2/.50  | ≤-40                          | Blue                  | White                   |
| LC              | UPC    | 0.2/.50  | -55                           | Blue                  | Blue                    |
| SC              | SPC    | 0.2/.50  | ≤-40                          | Blue                  | White                   |
| SC              | UPC    | 0.2/.50  | -55                           | Blue                  | Blue                    |
| ST® Compatible  | SPC    | 0.2/.50  | ≤-40                          | Amber                 | White                   |
| ST Compatible   | UPC    | 0.2/.50  | -55                           | Amber                 | Blue                    |

<sup>1</sup> Insertion loss values given for installation using a UniCam® Pretium™ Tool Kit. When installed using a UniCam Connectors Standard Installation Tool Kit, the insertion loss values are 0.3 dB typical and 0.75 dB maximum.

<sup>2</sup> Reflectance values for SM are for 18° to 26°C.

<sup>3</sup> LC connectors are sold with one 900 µm boot, one 2.0/1.6 boot, and one 2.9 mm boot; SC and ST compatible connectors are sold with one 900 micron boot and one 2.9 mm boot.

| Parameter                    | Description   |
|------------------------------|---|
| <b>Intermateability</b>      | Connectors are FOCIS compliant with TIA/EIA 604-10A (LC); TIA/EIA 604-3 (SC); TIA/EIA 604-2 (ST Compatible) |
| <b>Qualification</b>         | Passed TIA/EIA 568-B.3  |
| <b>Durability</b>            | 0.2 dB change, 500 rematings, FOTP-21   |
| <b>Tensile Strength</b>      | 10 lb ≤ 0.2 dB change on jacketed cable; 0.5 lb ≤ 0.2 dB change on 900 µm cable; FOTP-6                     |
| <b>Operating Temperature</b> | -40° to +75°C, exceeding TIA/EIA 568-B.3  |

### Ordering Information

Organizer packs are packs of 25 unassembled UniCam® Connectors separated into components.

| Part Number          | Description  |
|----------------------|--|
| <b>LC Connectors</b> |  |
| 95-200-96            | UniCam Pretium™-Performance LC Connector, SPC polish, single-mode, ceramic ferrule, logo, single pack          |
| 95-200-96-Z          | UniCam Pretium-Performance LC Connector, SPC polish, single-mode, ceramic ferrule, logo, organizer pack        |
| 95-200-99            | UniCam Pretium-Performance LC Connector, UPC polish, single-mode, ceramic ferrule, logo, single pack           |
| 95-200-99-Z          | UniCam Pretium-Performance LC Connector, UPC polish, single-mode, ceramic ferrule, logo, organizer pack        |
| 95-200-99P           | UniCam Pretium-Performance LC 250 µm Connector, UPC polish, single-mode, ceramic ferrule, logo, single pack    |
| 95-200-99P-Z         | UniCam Pretium-Performance LC 250 µm Connector, UPC polish, single-mode, ceramic ferrule, logo, organizer pack |
| <b>SC Connectors</b> |  |
| 95-200-41            | UniCam Pretium-Performance SC Connector, SPC polish, single-mode, ceramic ferrule, logo, single pack           |
| 95-200-41-Z          | UniCam Pretium-Performance SC Connector, SPC polish, single-mode, ceramic ferrule, logo, organizer pack        |
| 95-200-42            | UniCam Pretium-Performance SC Connector, UPC polish, single-mode, ceramic ferrule, logo, single pack           |
| 95-200-42-Z          | UniCam Pretium-Performance SC Connector, UPC polish, single-mode, ceramic ferrule, logo, organizer pack        |
| 95-200-42P           | UniCam Pretium-Performance SC 250 µm Connector, UPC polish, single-mode, ceramic ferrule, logo, single pack    |
| 95-200-42P-Z         | UniCam Pretium-Performance SC 250 µm Connector, UPC polish, single-mode, ceramic ferrule, logo, organizer pack |

# UniCam® Pretium™ -Performance Single-Mode Connectors LC, SC, ST® Compatible

A LANscape® Pretium Solutions Product

## Ordering Information (continued)

Organizer packs are packs of 25 unassembled UniCam® Connectors separated into components.

| Part Number                      | Description  |
|----------------------------------|--|
| <b>ST® Compatible Connectors</b> |  |
| 95-200-51                        | UniCam Pretium-Performance ST® Compatible Connector, SPC polish, single-mode, ceramic ferrule, logo, single pack   |
| 95-200-51-Z                      | UniCam Pretium-Performance ST Compatible Connector, SPC polish, single-mode, ceramic ferrule, logo, organizer pack |
| 95-200-52                        | UniCam Pretium-Performance ST Compatible Connector, UPC polish, single-mode, ceramic ferrule, logo, single pack    |
| 95-200-52-Z                      | UniCam Pretium-Performance ST Compatible Connector, UPC polish, single-mode, ceramic ferrule, logo, organizer pack |

## Tool Kits and Accessories

|                   |  |
|-------------------|--|
| TKT-UNICAM-PFC    | UniCam Pretium Installation Tool Kit, includes UniCam Pretium Installation Tool, Pretium Flat Cleaver and all required fiber preparation and cleaning supplies |
| TKT-UNICAM        | UniCam Connector Standard Installation Tool Kit, includes Score and Snap cleaver, installation tool and all required fiber preparation and cleaning supplies   |
| FBC-015           | Pretium Cleaver, individual flat fiber cleaver   |
| FBC-PRETIUM-BLADE | Replacement Blade for the Pretium Cleaver  |
| VFL-A125          | LC 1.25 mm Ferrule VFL Adapter (for UniCam Pretium Installation Tool only)   |
| VFL-A250          | SC and ST Compatible 2.5 mm ferrule VFL adapter (for UniCam Pretium Installation Tool only)  |
| VFL-AKIT          | LC 1.25 mm and SC and ST Compatible 2.5 mm Ferrule VFL Adapter (for UniCam Pretium Installation Tool only)   |
| TER-CTS-SC        | Continuity Test Set for SC Connectors  |
| TER-CTS-ST        | Continuity Test Set for ST Compatible Connectors   |
| VFL-350           | Visual Fault Locator   |
| TL-UCP            | UniCam Pretium Installation Tool   |
| TL-UC01           | UniCam Connector Elite™ Installation Tool  |
| 95-400-50-BP2N    | 2.0 mm SC boot, black, bulk pack of 100 boots  |
| 95-400-51-BP2N    | 2.0 mm ST Compatible/FC boot, blue, bulk pack of 100 boots   |
| TKT-FCC           | Fiber Cleaning Kit   |
| CLEANR-TAPE-SFC   | Woven cleaning tape for single-fiber connectors  |
| FCC-WIPES         | Canister of 90 lint-free cleaning wipes  |
| FCC-CLEANER-FIBER | Fiber Optic Cleaning Fluid, 3 oz. can  |