

Product Specifications



360GS10E-L-GN

Material ID: CPCSSZ2-04

GigaSPEED® X10D 360GS10E Solid Low Smoke Zero Halogen Cordage Modular Patch Cord, Spring Green Jacket



CHARACTERISTICS

Dimensions

| | |
|----------------------|---------------|
| Cord Length, maximum | 100 ft 30 m |
| Cord Length, minimum | 1 m 3 ft |

Electrical Specifications

| | |
|------------------------|----------|
| ANSI/TIA Category | 6A |
| dc Resistance, maximum | 0.30 ohm |
| Safety Voltage Rating | 300 V |

Environmental Specifications

| | |
|-----------------------|--------------------------------------|
| Environmental Space | Low Smoke Zero Halogen (LSZH) |
| Flammability Rating | UL 94 V-0 |
| Operating Temperature | -10 °C to +60 °C (+14 °F to +140 °F) |
| Safety Standard | cETL ETL |

General Specifications

| | |
|--------------------------------|-----------------------------|
| Cable Type | U/UTP (unshielded) |
| Interface, connector A | RJ45 plug |
| Interface, connector B | RJ45 plug |
| Jacket Color | Spring green |
| Brand | GigaSPEED® X10D SYSTIMAX® |
| Interface Feature, connector A | Standard |
| Interface Feature, connector B | Standard |
| Package, quantity | 1 |
| Pairs, quantity | 4 |

Mechanical Specifications

| | |
|----------------|-------|
| Conductor Type | Solid |
|----------------|-------|

Product Specifications



360GS10E-LGN - Material ID: CPCSSZ2-04

Material Type Copper alloy | Polycarbonate
Outlet/Module Contact Plating Gold over nickel
Plug Insertion Life, minimum 750 times
Plug Retention Force, minimum 133 N | 30 lbf
Wiring T568B

Wiring Diagram

| | Connector A | Connector B |
|------------|--------------|--------------|
| Position 1 | White/Orange | White/Orange |
| Position 2 | Orange | Orange |
| Position 3 | Lt. Green | Lt. Green |
| Position 4 | Blue | Blue |
| Position 5 | Lt. Blue | Lt. Blue |
| Position 6 | Green | Green |
| Position 7 | Lt. Brown | Lt. Brown |
| Position 8 | Brown | Brown |

Regulatory Compliance/Certifications

Agency

RoHS 2002/95/EC
ISO 9001:2000

Classification

Compliant
Compliant



INCLUDED PRODUCTS

1095B SG 4/24 RVAR (Product Component—not orderable)

GigaSPEED® X10D 1095B Category 6A U/UTP Cable, non-plenum, spring green jacket, 4 pair count, variable length, reel