THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

PART NUMBER		TAB SIZE	WIRE RANGE AWG (mm²)	DIMENSIONS		HOUSING COLOR	TOOL CHART
PREFIX	PK			A ±.030	B MAX (.8)		RECOMMENDED PRESSES CP-861, CP-860 CP-851, CP-862 CA-800/CA9 DIE INSERTS
DV18-145MB	-3K	.145 X .032 (3.7 X 0.8)	22-18 (0.38-1.0)	.90 (22.9)	.155 (3.94)	RED	CD-800-1 CD9-1A
DV14-145MB	-3K	.145 X .032 (3.7 X 0.8)	16-14 (1.5-2.5)	.90 (22.9)	.175 (4.45)	BLUE	CD-800-2 CD9-2A

NOTES:

1. USED FOR:
   A. 600V MAX. VOLTAGE RATING.
   B. 90° C (194° F) MAX. TEMP. RATING.
   C. STRANDED COPPER WIRE ONLY.

2. PACKAGE QTY: -3K = 3000 PC. REEL

3. MATERIAL:
   A. STAMPING: .032 (0.8) THICK ETP 110 COPPER, TIN PLATED.
   B. HOUSING: VINYL

4. WIRE STRIP LENGTH: $1/4\ ^{+1/32}_{-0}$ $(6.4\ ^{+.8}_{-0})$

5. DIMENSIONS IN BRACKETS ARE IN MM OR MM².



A41532_04

REV	DATE	BY	CHK	DESCRIPTION	ECN #	QA	CUST	PM	APP
04	2/05	KLFU	SKB	ADDED CP-862, CD9 & CA9 TO CHART					
03	1/01	RM		FILESPEC WAS N41532AA_PCD_02	8933		JAC	CCH	
02	5/95	MS		REMOVED UL - CSA LOGOS	03248				
01	4/94	DL	DL	REMOVED COIN FROM TAB END OF PART	03036		LA	KS	

PANDUIT CORP. TINLEY PARK, ILLINOIS

REELSMART™, DISCO™, VINYL BARREL INSUL, FUNNEL ENTRY, MALE DISCONNECTS (.145 X .032 TAB SIZE)

DRAWN BY	CHK'D	SCALE	DRAWING NO.
BDK	RLS	NONE	A41532