

Environmental Housing

Outdoor IP67 Vandal Proof Housing



HSG1-O-W Housing with Heater, Blower and Wall Mount



Megapixel Camera Accessories

The HSG1 environmental housing provides excellent protection for the entire MegaVideo® line of Arecont Vision cameras. Combining this high quality indoor/outdoor housing with the superior imaging of AV cameras provides the perfect solution for environments that require protection from the elements.

Arecont Vision Advantages:

Superior Solution for Various Environments

- Designed for Indoor or outdoor applications

Excellent Enclosure Protection

- Waterproof complies with the IP67 standard

Vandal Resistant

- Die-cast aluminum, resistant to impact and salt damage
- 6mm tempered glass cover

Compatibility

- Designed to house the entire line of MegaVideo® cameras

Easy Installation

- Side opening, easy to install a camera

Other key features:

- Light ivory powder coating
- Internal cable management
- Cable feed through wall mount included
- Sunshield (SS-HSG1) sold separately
- Heater and blower (24 VAC) and more

Designed to House the Entire Line of Color and Day/Night MegaVideo® Cameras

Learn more about our products at www.arecontvision.com

www.arecontvision.com avsales@arecontvision.com +1.818.937.0700 877.CAMERA.8

Specifications

HSG1-O-W

Outdoor IP67 vandal proof housing

Model Numbers:

HSG1-O-W

Mechanical

- Housing material:
Aluminum
- Color:
White
- Dimensions (WxHxD):
422mm x 174mm x 145 mm (16.5" x 6.5" x 5.5")
- Wall Mount Dimensions (WxHxD):
172mm x 144 mm x 114 mm (6.5" x 5.5" x 4.5")
- Weight w/o camera:
Housing: 2300g (5lbs)
Wall Mount: 600g (1.3lbs)

HSG1-O-W =



Housing

+



Wall Mount

Electrical

- Power Supply:
24 VAC Heater/Blower
- Power Consumption:
25 Watts maximum

Environmental

- Operating Temperature - 30°C (-22°F) to 50°C (122°F)
- Operating Humidity 90% RH (max)



Compatible Cameras

AV1300M, AV1300DN, AV1300-AI
AV1305, AV1305DN, AV1305-AI
AV2100M, AV2100DN, AV2100-AI
AV2105, AV2105DN, AV2105-AI
AV3100M, AV3100DN, AV3100-AI
AV3105, AV3105DN, AV3105-AI
AV5100, AVAV5100DN, AV5100-AI
AV5105, AV5105DN, AV5105-AI
AV3130, AV3135

Related Accessories



Sunshield/SS-HSG1



Arecont Vision
megapixel technology...
beyond imagination

Revised on 09/11/08