THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



PANDUIT PART NO.	DESCRIPTION	AVAILABLE LENGTHS
F6Z6P-12M*	62.5/125um OR 50/125um MULTIMODE RISER RATED PATCHCORD FIBER JACK PLUG TO MT-RJ	1, 2, 3, 5, & 10 METER
F5Z6P-12M*		

COMPONENT	TYPE/DESCRIPTION	COLOR	MAXIMUM LOSS
CABLE	62.5 OR 50/125um 1.8mm ZIPCORD CABLE RISER RATED	ORANGE	
CONNECTORS	OPI-JACK PLUG	ELECTRIC IVORY	.35 dB
	MULTIMODE MT-RJ	BLACK	.35 dB

PANDUIT PART NO.	DESCRIPTION	AVAILABLE LENGTHS
F6LZ6P-12M*	62.5/125um OR 50/125um MULTIMODE LS-ZH PATCHCORD FIBER JACK PLUG TO MT-RJ	1, 2, 3, 5, & 10 METER
F5LZ6P-12M*		

COMPONENT	TYPE/DESCRIPTION	COLOR	MAXIMUM LOSS
CABLE	62.5 OR 50/125um 1.8mm ZIPCORD CABLE LOW SMOKE-ZERO HALOGEN	ORANGE	
CONNECTORS	OPI-JACK PLUG	ELECTRIC IVORY	.35 dB
	MULTIMODE MT-RJ	BLACK	.35 dB

NOTES:
1. SEE CURRENT CATALOG FOR PACKAGE QUANTITY.
2. FOR LENGTHS OTHER THAN THOSE SHOWN, CONTACT YOUR PANDUIT SALES PERSON.
3. TESTED TO EIA/TIA 568-B.3.
4. PATCH CORD ROUTING CONFIGURATION A TO B.

REV	DATE	BY	CHK	DESCRIPTION	ECN - R	CUST	SUP	OTH
R	06-30-06	JH		RELEASED FOR PRODUCTION	02412-08			

FIBER OPTIC PATCH CORD
FIBER JACK PLUG TO MT-RJ CONFIGURATION
CUSTOMER DRAWING

PANDUIT™ CORP.
TINLEY PARK, ILL 60477

THIRD ANGLE PROJECTION

ALL DIMENSIONS ARE GIVEN IN INCHES UNLESS OTHERWISE SPECIFIED.
DIMENSIONAL TOLERANCES ARE:
(.X) (.XXX)±.010 [0.3]
(.XX)±.03 [0.8] ANGLES

DRAWN BY MC
DATE 11-07-05
CHK'D
REVIEW DRAWING NUMBERS

DRAWING FILENAME M02412BT_DC_00A.prt
SCALE NONE
PART NO. SEE TABLE
DRAWING NO. 02412-08
SIZE A