THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



NOTES:
1. SEE SHEET 2 FOR PRODUCT DESCRIPTIONS AND TECHNICAL SPECIFICATIONS.
2. SEE CURRENT CATALOG FOR PIGTAIL LENGTHS AND PACKAGE QUANTITY.
3. FOR LENGTHS OTHER THAN THOSE LISTED IN CATALOG, CONTACT YOUR PANDUIT SALES PERSON.
4. TESTED TO EIA/TIA 568-B.3.
5. ALL MATERIALS AND COMPONENTS USED MEET THE MATERIAL RESTRICTIONS OF RoHS, (EUROPEAN DIRECTIVE 2002/95/EC ON THE RESTRICTION OF HAZARDOUS SUBSTANCES) AS PROPOSED BY THE RoHS TECHNICAL ADAPTATION COMMITTEE.

REV	DATE	BY	CHK	DESCRIPTION	ECN - R	CUST	SUP	OTH
R	06-05-07	MC		RELEASED TO PRODUCTION	02779-32			

900um BUFFERED FIBER OPTIC ST PIGTAIL
CUSTOMER DRAWING

PANDUIT™ CORP.
TINLEY PARK, ILL 60477

THIRD ANGLE PROJECTION

ALL DIMENSIONS ARE GIVEN IN INCHES, UNLESS OTHERWISE SPECIFIED.
DIMENSIONAL TOLERANCES ARE:
(.X) (.XXX)
(.XX) ANGLES

DRAWN BY: MC
DATE: 05-22-07
CHK'D:
MAT'L:

DRAWING FILENAME: M02779CB_DC_00A.prt
SCALE: NONE
PART NO.: SEE TABLE, SHT. 2
DRAWING NO.: 02779-32 (SHT. 1 of 2)
SIZE: A

THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

900um BUFFERED FIBER OPTIC ST PIGTAIL								
PANDUIT PART NO.	BUFFERED FIBER				ST CONNECTOR		
	RATING	FIBER TYPE	COUNT	COLOR	MAX. IL	RL	COLOR
F6B2-NM*Y	NO FLAME RATING	62.5/125um OM1	SIMPLEX 900um BUFFERED FIBER	BLUE	0.30dB	20dB	METALLIC FINISH
F9B2-NM*Y		9/125um OS1		BLUE	0.75dB	55dB	METALLIC FINISH

* - DENOTES PIGTAIL LENGTH, WHERE M = METERS AND F = FEET

REV	DATE	BY	CHK	DESCRIPTION	ECN - R	CUST	SUP	OTH
R	06-05-07	MC		RELEASED TO PRODUCTION	02779-32			

900um BUFFERED FIBER OPTIC ST PIGTAIL
CUSTOMER DRAWING

PANDUIT™ CORP.
TINLEY PARK, ILL 60477

THIRD ANGLE PROJECTION

ALL DIMENSIONS ARE GIVEN IN INCHES UNLESS OTHERWISE SPECIFIED.
DIMENSIONAL TOLERANCES ARE:
(.X) (.XXX)±.010 [0.3]
(.XX)±.03 [0.8] ANGLES

DRAWN BY: MC
DATE: 05-22-07
CHK'D:
REVIEW DRAWING NUMBERS

DRAWING FILENAME: M02779CB_DC_00A.prt
SCALE: NONE
PART NO.: SEE TABLE
DRAWING NO.: 02779-32 (SHT. 2 of 2)
SIZE: A