THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION 20
© COPYRIGHT 20 BY - ALL RIGHTS RESERVED.

LOC	DIST
CE	00

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	F	CHANGE BULK PACKAGING	21MAR2011	DLF	CB

△1 MATERIAL:
CONNECTOR ASSEMBLY:
CONNECTOR HOUSING: PPSU, COLOR: BEIGE *
REAR BODY: METAL
COMPRESSION SPRING: METAL
FERRULE SUB ASSEMBLY: ZIRCONIA/ METAL
INTERNAL SPLICE: PEI *
PLUNGER: METAL
BOOT: TPE, SEE TABLE FOR COLOR
BUILD-UP TUBE: TPE
TERMINATION COVER: PBT, COLOR: BLACK
REAR PROTECTIVE COVER: VINYL, COLOR: RED

* UL 94 V-0 RATED AT QUALIFYING THICKNESS

2. INSTRUCTION SHEET: 408-8925 AVAILABLE FOR DOWNLOAD AT www.tycoelectronics.com/documents OR www.ampnetconnect/foguide.

△3 MARK WITH "50" OR "62", LOCATED APPROXIMATELY AS SHOWN.

△4 BULK PACKAGED





BOOT COLOR	DESCRIPTION	PART NO.
BEIGE	62.5/125um	6754483-7
BLACK	50/125um	6754483-6
AQUA	XG 50/125um	6754483-5
AQUA	XG 50/125um	6754483-4
GRAY	XG 50/125um	6754483-3
BLACK	50/125um	6754483-2
BEIGE	62.5/125um	6754483-1

△4

SUPERCEDED BY: 6754483-4

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS: mm

TOLERANCES UNLESS OTHERWISE SPECIFIED:
0 PLC ±-
1 PLC ±0.5
2 PLC ±0.13
3 PLC ±0.013
4 PLC ±0.0001
ANGLES ±-
FINISH -

MATERIAL △1 -

DWN D ERDMAN 24DEC2005
CHK M GURRERI 24DEC2005
APVD RAFCHTLF 24DEC2005
PRODUCT SPEC -
APPLICATION SPEC -
WEIGHT -

TE Connectivity

NAME KIT, CONNECTOR, LightCrimp Plus LC SIMPLEX, MM 250-900um BUFFER
-

SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
A2	00779	C-6754483	-

CUSTOMER DRAWING | SCALE 5:1 | SHEET 1 OF 1 | REV F