



- 01 6 SCREWS M3x5 TAPTITE POSI PAN ZINC PLATED INCLUDED WITH ENCLOSURE ASSY
- 02 DZUS Fastener
Pilot 1/4 turn fastener range
Part no's: 275-201-040 retainer
285-102-161 receptacle
290-718-191 stud assembly
OR EQUIVALENT TO BE APPROVED BY TYCO

- 03 COUPLER FIXINGS WITH 48 SELFTAPPING SCREWS, SURPLUS PACKED IN PLASTIC BAG
POZI PAN HEAD NR2 x 3/8" - DIN 7981 TYPE B (ST2,2 x 6,5MM - DIN 7981 F-H)
PART NUMBER 4-1201271-7
- 04 CABLE MANAGEMENT AND CABLE GLANDS PACKED IN PLASTIC BAG
(SHOWN ON DRAWING IN SUGGESTED POSITION)
- 05 LASER LOGO AND LASER TEXT LABEL INCLUDED IN PLASTIC BAG

-	-	-	-	-	-	-	-	-	-	-	0-0504640-2	24	4-1206343-4
(10) BLANKING PLUG SC-STYLE	24	(9) OFN SADDLE	(8) CABLE MANAGM. SPIDER	(7) CABLE GLAND M25	(6) CABLE GLAND M20	(5) R.H. BRACKET	(4) L.H. BRACKET	(3) COVER	(2) TRAY	(1) COUPLING RECEPTACLE KIT	-	-	0-1206343-4
PART NUMBER	QTY	QTY = 8	QTY = 2	QTY = 1	QTY = 1	QTY = 1	QTY = 1	QTY = 1	QTY = 1	PART NUMBER	QTY	PART NUMBER	

CUSTOMER DRAWING

AMP drawing N° : 1206343

MAT: MILD STEEL ZINTEC COATED

DRAWING STATUS		REVISION DESCRIPTION: - Design changes sliding tray.	
RELEASED	DRAWING BY NAME: H. BLEUS DATE: 21-FEB-03	DRAWING REVISION BY NAME: H. BLEUS DATE: 05-MAY-04	VOLUME OF MOULDED PART OR AREA OF UNFOLDED SHEET/METAL PART. Cm³ / Cm²
SCALE: 1000	DRAWING FORMAT A1	DRAWING TITLE F.O. 1U PANEL 24 SC DUPLEX MM	
ISO-SYMBOL	GENERAL TOLERANCE	DRAWING SHEET, REVISION NUMBER	
		D.0010580.01.AE	
tyco Electronics		REVISION AE	
TYCO Electronics - Raychem N.V. DIESTSESTEENWEG 692 B-3010 HESSEL-LO, BELGIUM		THIS DRAWING AND INFORMATION SET FORTH HEREON ARE THE PROPERTY OF TYCO/Electronics/Raychem N.V. AND ARE TO BE HELD IN TRUST AND CONFIDENCE. PUBLICATION, DUPLICATION, DISCLOSURE OR USE FOR ANY PURPOSE NOT EXPRESSLY AUTHORIZED IN WRITING BY TYCO/Electronics IS PROHIBITED.	