

Desktop Barcode and Label Printers

Thermal Transfer Printers for Tough & Durable Laminated Labels

Brother™ PT-9700PC and PT-9800PCN desktop barcode and label printers come as complete solutions that include a laminating label printer, label design and print software, and HG tape to help you get started right out of the box – all this for the price of just the printer! With HG tape, these small footprint printers produce professional looking glossy laminated labels at high 360 dpi resolution, up to 3.1ips and feature a built-in automatic cutter that trims a continuous “tape” to virtually any length, one at a time or as a strip of many labels cut for easy removal. Brother tapes come in an easy to load, drop in cartridge that is available in different adhesive types, sizes and colors. Compatible with Windows® 7 or print from many legacy software applications using a variety of software development tools available from Brother.



PT-9700PC



PT-9800PCN

PT-9700PC & PT-9800PCN

Desktop Barcode and Label Printers

Technical Specifications

Features	PT-9700PC	PT-9800PCN
Model Type	Desktop Barcode and Label Printer	Desktop Barcode and Label Printer (Network)
Tape Families	HG/HGe, TZ/TZe	
Tape Sizes	3.5mm, 6mm, 9mm, 12mm, 18mm, 24mm, 36mm	
Tape Length	Most tapes are 8m (26.25')	
Tape Technology	Laminated Thermal Transfer	
Tape Types	High Grade, Standard Adhesive, Extra-Strength Adhesive, Flexible ID, Tamper-Evident	
Max. Print Speed	HG Tape: Up to 3.15 ips (80 mm/sec); TZ Tape: Up to 0.78 ips (20 mm/sec)	
Cutter	Automatic (Built-In) Cutter: full-cut mode and crack-and-peel mode	
Interface	USB (1.1 or 2.0), Serial (RS-232C)	USB (1.1 or 2.0), Host USB, Serial (RS-232C), Ethernet (10/100 Base-TX)
Software	P-touch® PT-Editor 5.0, PT-Editor for Mac® 5.0, Transfer Manager 2.1, Library 2.1	BRAdmin Light 1.14, P-touch® PT-Editor 5.0, Editor Lite Lan, PT-Editor for Mac® 5.0, Transfer Manager 2.1, Library 2.1
Database file compatibility	*.csv, *.txt, *.mdb, *.xls and Microsoft SQL Server	
Resident Fonts	Helsinki, Letter Gothic	
Resident Barcodes	Linear: Code39, ITF (I-2/5), UPC-A, UPC-E, EAN8, EAN13, Codabar (NW-7), Code128, GS1-128 (UCC/EAN-128), GS1 DataBar (RSS) 2-Dimensional: PDF417, QR Code, Data Matrix, Maxicode	
Operating System	Windows® 7/XP/2000 Professional, Windows Vista®, Mac OS® 10.3.9 - 10.6	Windows® 7/XP/2000 Professional, Windows Server® 2003/2008, Mac OS® 10.3.9 - 10.6
Carton Contents	Printer, AC Adapter, Power Cord, USB Cable, CD, HG-251 Tape (26.25'), User Guide	
Power Supply	120VAC 60Hz	
Warranty	2 Year Limited Warranty	

Accessories*



High Speed/Resolution Tapes



Standard Performance Tapes

PT-9700PC / PT-9800PCN Laminated Tape Sizes	6mm (0.23in)	9mm (0.35in)	12mm (0.47in)	18mm (0.7in)	24mm (0.94in)	36mm (1.4in)
--	-----------------	-----------------	------------------	-----------------	------------------	-----------------

Standard Adhesive Tapes - Designed for use on smooth and flat surfaces

BLACK ON WHITE	TZe211	HGe2215PK	HGe2315PK	HGe2415PK	HGe2515PK	TZe261
BLACK ON YELLOW	TZe611	TZe621	TZe631	HGe6415PK	HGe6515PK	TZe661
BLACK ON MATTE SILVER				HGM9415PK	HGM9515PK	
BLACK ON CLEAR	TZe111	TZe121	TZe131	HG1415PK	HG1515PK	TZe161
BLACK ON FL. ORANGE				TZe841	TZe851	
RED ON WHITE			TZe232	TZe242	TZe252	
WHITE ON BLACK	TZe315	TZe325	TZe335	TZe345	TZe355	



Extra-Strength Adhesive Tapes

- Designed for use on plastic, textured & hard to stick surfaces

BLACK ON WHITE	HGeS2115PK	HGeS2215PK	HGeS2315PK	HGeS2415PK	HGeS2515PK	HGeS2615PK
BLACK ON YELLOW		HGeS6215PK	HGeS6315PK	HGeS6415PK	HGeS6515PK	HGeS6615PK
BLACK ON MATTE SILVER				HGeS9415PK	HGeS9515PK	HGeS9615PK
BLACK ON CLEAR		HGeS1215PK	HGeS1315PK	HGeS1415PK	HGeS1515PK	

Flexible ID Tapes - Designed for wrapping around & adhesive to adhesive label flags

BLACK ON WHITE		TZeFX231	TZeFX241	TZeFX251	TZeFX261
BLACK ON YELLOW			TZeFX631		

Tamper-Evident Tapes - Security pattern revealed when label is removed or disturbed

BLACK ON WHITE			TZeSE4	
----------------	--	--	--------	--

All tapes are 8m (26.2 ft) long except Black on FL. Orange which is 5m (16.4 ft) long

Ask us about our other products

Desktop Barcode and Label Printers

TD-4000

*Light, Industrial Thermal Printer
for Labels, Receipts, and Tags*



TD-4100N

*Light, Industrial Thermal Printer
with built-in networking for printing
Labels, Receipts, and Tags*



*Additional purchase required.

All specifications subject to change without notice.

Brother Mobile Solutions, Inc.

All specifications subject to change without notice.

**For more information, call 1-800-543-6144,
or visit www.brothermobilesolutions.com**

Brother™ is a trademark or registered trademark of Brother Industries, Ltd. in the United States. Microsoft®, Windows® and Windows Vista® are either registered trademarks or trademarks of Microsoft Corporation in the United States and/or other countries. All other trademarks and registered trademarks are the properties of their respective companies.

© 2011 Brother Mobile Solutions, Inc., 100 Technology Drive, Suite 250A, Broomfield, CO 80021

brother
at your side

DX-0501-01