


AX100041 Panels - FiberExpress Rack Mount Patch Panel 1U



For more Information
please call

1-800-Belden1

Description:

FiberExpress Patch Panel, Rack Mount, 1U, Black.

Usage (Overall)

Suitable Applications:	FiberExpress Solutions, Backbone, Telecommunications Room, Main Distribution Room
Related Parts:	FiberExpress Adapter Strips, Fiber Splice Organizer Trays and Kits, Front Cover, Offset Bracket Kit, Right Side Cable Entry Kit

Physical Characteristics (Connectivity)

Capacity

Max. Capacity:	2 Strips; 24 Fibers (SC, SCD, ST, FC); 48 Fibers (LCD, MT-RJ). One 8-inch splice tray (A0649869)
-----------------------	--

Access

Front Connection:	Flush
Termination Area:	Front Swing Out

Dimensions

Dimensions:

Height (in.)	Width (in.)	Depth (in.)
1.720	19.000	12.000

Materials

Materials:

Description	Material
Panel	Steel

Color

Color:	Black
---------------	-------

Weight

Weight:	11.300 lbs.
----------------	-------------

Included Parts

Included Parts:	4 Screws (10x32); 7 Tie Wraps; Identification Label; 2 Velcro Straps; Caution Label; Admin Label; Receptacle
------------------------	--

Packaging

Packaging:	Individually packaged in a cardboard box.
-------------------	---

Mechanical Characteristics (Connectivity)

Storage Temperature Range:	-40°C To +70°C
Operating Temperature Range:	-10°C To +60°C

Applicable Specifications and Agency Compliance (Overall)

Suitability

Suitability - Indoor:	Yes
------------------------------	-----

Transmission Characteristics (Connectivity)

Notes (Overall)

Notes: For proper installation refer to Installation Guide PX100103 included with the product or visit our web site at <http://www.belden.com>

Notes (Cont'd.): Optional Lexan Front Cover p/n AX100045.

AX100041 Panels - FiberExpress Rack Mount Patch Panel 1U

Product Family

Part Numbers:

Description	Item Number
FiberExpress Rack Mount PP 1U Black	AX100041
FiberExpress Rack Mount PP 2U Black	AX100068
FiberExpress Rack Mount PP 3U Black	AX100077
FiberExpress Rack Mount PP 4U Black	AX100116

Related Documents:

No related documents are available for this product

Put Ups and Colors:

Item #	Putup	Ship Weight	Color	Notes	Item Desc
AX100041	1 EA	10.406 LB			FIBEREXPRESS, RACK MOUNT
AX100041+CA	1 EA	10.406 LB			FIBEREXPRESS, RACK MOUNT

Revision Number: 0 Revision Date: 03-10-2010

© 2012 Belden, Inc
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.