

## AX100542 Panels - FiberExpress Wall Mount Patch Panel - Large Wall Mount



For more Information  
please call

1-800-Belden1

**Description:**

FiberExpress Patch Panel, Large Wall Mount, Black.

**Usage (Overall)**

**Suitable Applications:** FiberExpress Solutions, Backbone, Telecommunications Room, Main Distribution Room

**Related Parts:** FiberExpress Adapter Strips, Fiber Splice Organizer Trays and Kits

**Physical Characteristics (Connectivity)****Capacity**

**Max. Capacity:** 8 Strips;96 Fibers (SC, SCD, ST, FC);192 Fibers (LCD, MT-RJ);Four 8-inch Splice Tray kit (A0649869);Four 12-inch Splice Tray Kit (A0318904)

**Access**

**Front Connection:** Flush

**Dimensions****Dimensions:**

Height (in.)	Width (in.)	Depth (in.)
30.630	16.700	5.500

**Materials****Materials:**

Description	Material
Panel	Steel
LH Door	Steel
RH Door	Lexan

**Color**

**Color:** Black

**Weight**

**Weight:** 20.830 lbs.

**Included Parts**

**Included Parts:** 6 Wood Screws (#10x1inch); 2 Velcro Strap; 9 Tie Wrap; 1 Admin Label; 1 Caution Label, 1 Installation Manual

**Packaging**

**Packaging:** Individually packaged in a cardboard box.

**Mechanical Characteristics (Connectivity)**

**Storage Temperature Range:** -40°C To +70°C

**Operating Temperature Range:** -10°C To +60°C

**Applicable Specifications and Agency Compliance (Overall)****Suitability**

**Suitability - Indoor:** Yes

**Notes (Overall)**

**Notes:** For proper installation refer to Installation Guide PX101059 included with the product or visit our web site at <http://www.belden.com>

**Product Family****Part Numbers:**

Description	Item Number
-------------	-------------

**AX100542 Panels - FiberExpress Wall Mount Patch Panel - Large Wall Mount**

FiberExpress Wall Mount PP, Small, Black	AX100495
FiberExpress Wall Mount PP, Medium, Black	AX100540
FiberExpress Wall Mount PP, Large, Black	AX100542

**Related Documents:**

No related documents are available for this product

**Put Ups and Colors:**

Item #	Putup	Ship Weight	Color	Notes	Item Desc
AX100542	1 EA	0.000 EA			FIB EXPRESS WLMNT 48/96

Revision Number: 0    Revision Date: 05-28-2009

© 2012 Belden, Inc  
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.