

A0405255 Panels - MDVO Faceplate, 1 Port, Single Gang, Flush

For more Information
please call

1-800-Belden1

**Description:**

MDVO Faceplate, 1 Port, Single Gang, Flush

Usage (Overall)

Suitable Applications:	- Compatible with a variety of modules that are suitable for use with Belden IBDN Systems 10GX, 4800,3600, 2400 and 1200.
Related Parts:	- Compatible with 10GX, CAT6+ and CAT5E MDVO-style Modular Jacks, MDVO Multimedia Modules, EZ-MDVO

Physical Characteristics (Connectivity)**Capacity**

Max. Capacity:	1 ports
-----------------------	---------

Access

Front Connection:	Flush
--------------------------	-------

Dimensions**Dimensions:**

Height (in.)	Width (in.)	Depth (in.)
4.490	3.000	0.380

Materials**Materials:**

Description	Material
Plate	Plastic - UL94V-0

Color

Color:	Gray
---------------	------

Weight

Weight:	0.110 lbs.
----------------	------------

Included Parts

Included Parts:	blank, 6-32 screw, installation sheet
------------------------	---------------------------------------

Packaging

Packaging:	Individually packaged in a plastic bag.
-------------------	---

Mechanical Characteristics (Connectivity)

Connector/Hardware Retention:	20 lbs.
Storage Temperature Range:	-40°C To +70°C
Installation Temperature Range:	-10°C To +60°C
Operating Temperature Range:	-10°C To +60°C

Applicable Specifications and Agency Compliance (Overall)**Applicable Standards & Environmental Programs**

EU Directive 2002/95/EC (RoHS):	Yes
EU RoHS Compliance Date (mm/dd/yyyy):	07/01/2006
MII Order #39 (China RoHS):	EUP 50

A0405255 Panels - MDVO Faceplate, 1 Port, Single Gang, Flush

Safety Listing:	ACA, Bi-national (UL/CSA) Standard Listed
------------------------	---

Suitability

Suitability - Indoor:	Yes
------------------------------	-----

Transmission Characteristics (Connectivity)**Notes (Overall)**

Notes: For proper installation refer to Installation Guide P0744620 included with the product or visit our web site at <http://www.belden.com>

Product Family**Part Numbers:**

Description	Gray	Almond	White	Black	Ivory
MDVO Faceplate Flush Single Gang 1 port	A0405255	A0405256	A0405257	A0405258	AX102585
MDVO Faceplate Flush Single Gang 8 ports	A0405294	A0405295	A0405296	A0405298	AX102586
MDVO Faceplate Angled Single Gang 4 ports	A0645267	A0645268	A0645269	A0645270	AX102588
MDVO Faceplate Flush Double Gang 12 port	A0620806	A0620807	A0620808	A0620809	AX102587

Related Documents:

No related documents are available for this product

Put Ups and Colors:

Item #	Putup	Ship Weight	Color	Notes	Item Desc
A0405255	1 EA	0.051 LB			MDVO FP FLUSH 1P GREY

Revision Number: 0 Revision Date: 06-16-2010

© 2012 Belden, Inc
 All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with EU RoHS (Directive 2002/95/EC, 27-Jan-2003). Material manufactured prior to the compliance date may be in stock at Belden facilities and in our Distributor's inventory. The information provided in this Product Disclosure, and the identification of materials listed as reportable or restricted within the Product Disclosure, is correct to the best of Belden's knowledge, information, and belief at the date of its publication. The information provided in this Product Disclosure is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. This Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.