



A0407073 Panels - MDVO Modular Furniture Adapter, 3 Port

For more Information
please call

1-800-Belden1

Description:

MDVO Modular Furniture Adapter, 3 Port

Usage (Overall)**Suitable Applications:**

- Compatible with a variety of modules that are suitable for use with Belden IBDN Systems 10GX, 4800, 3600, 2400 and 1200.

Related Parts:

- Compatible with 10GX, CAT6+ and CAT5E MDVO-style Modular Jacks and MDVO Multimedia Modules

Physical Characteristics (Connectivity)**Capacity**

Max. Capacity: 3 ports

Access

Front Connection: Flush

Dimensions**Dimensions:**

Height (in.)	Width (in.)	Depth (in.)
3.300	1.570	0.500

Materials**Materials:**

Description	Material
Modular Furniture Adapter	Plastic - UL94V-0

Color

Color: White

Weight

Weight: 0.110 lbs.

Included Parts

Included Parts: installation sheet, blank

Packaging

Packaging: Individually packaged in a plastic bag.

Mechanical Characteristics (Connectivity)

Connector/Hardware Retention: 20 lbs.

Storage Temperature Range: -40°C To +70°C

Installation Temperature Range: -10°C To +60°C

Operating Temperature Range: -10°C To +60°C

Applicable Specifications and Agency Compliance (Overall)**Applicable Standards & Environmental Programs**

Safety Listing: ACA, Bi-national (UL/CSA) Standard Listed

Suitability

Suitability - Indoor: Yes

Transmission Characteristics (Connectivity)**Notes (Overall)**

A0407073 Panels - MDVO Modular Furniture Adapter, 3 Port

Notes: For proper installation refer to Installation Guide P0746008 included with the product or visit our web site at <http://www.belden.com>

Product Family**Part Numbers:**

Description	Gray	Almond	White	Black	Ivory
MDVO Modular Furniture Adapter 3 ports	A0407071	A0407072	A0407073	A0407074	AX102648
MDVO Modular Furniture Adapter 4 ports	AX100925	AX100926	AX100927	AX100928	AX102594

Related Documents:

No related documents are available for this product

Put Ups and Colors:

Item #	Putup	Ship Weight	Color	Notes	Item Desc
A0407073	1 EA	0.043 LB			MDVO MODULAR FURNITURE

Revision Number: 0 Revision Date: 06-02-2009

© 2012 Belden, Inc
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.