

AX102256 Panels - KeyConnect Faceplates 12-Port w/ID Windows Double-Gang



For more Information
please call

1-800-Belden1

**Description:**

KeyConnect Faceplates 12-Port, w/ ID Windows, Double Gang, Flush

Usage (Overall)

Suitable Applications:	- Compatible with a variety of modules that are suitable for use with Belden IBDN Systems 10GX, 4800, 3600, 2400, fiber and coax
Related Parts:	- Compatible with KeyConnect-style Modular Jacks 10GX, CAT6+, CAT5E and KeyConnect-style Fiber and Coax Connectors

Physical Characteristics (Connectivity)**Capacity**

Max. Capacity:	12-port
-----------------------	---------

Access

Front Connection:	Flush
--------------------------	-------

Dimensions**Dimensions:**

Height (in.)	Width (in.)	Depth (in.)
4.500	4.590	0.260

Materials**Materials:**

Description	Material
Plate	Plastic - UL94V-0

Color

Color:	Almond
---------------	--------

Weight

Weight:	0.110 lbs.
----------------	------------

Included Parts

Included Parts:	6-32 screw, carton label, clear window
------------------------	--

Packaging

Packaging:	Individually packaged in a plastic bag.
-------------------	---

Mechanical Characteristics (Connectivity)

Connector/Hardware Retention:	20 lbs.
Storage Temperature Range:	-40°C To +70°C
Installation Temperature Range:	-10°C To +60°C
Operating Temperature Range:	-10°C To +60°C

Applicable Specifications and Agency Compliance (Overall)**Applicable Standards & Environmental Programs**

EU Directive 2002/95/EC (RoHS):	Yes
EU RoHS Compliance Date (mm/dd/yyyy):	07/01/2006
MII Order #39 (China RoHS):	Yes

AX102256 Panels - KeyConnect Faceplates 12-Port w/ID Windows Double-Gang

Safety Listing:	Bi-national (UL/CSA) Standard Listed
------------------------	--------------------------------------

Suitability

Suitability - Indoor:	Yes
------------------------------	-----

Transmission Characteristics (Connectivity)**Notes (Overall)**

Notes: For proper installation refer to Installation Guide PX103826. Visit our web site at <http://www.belden.com>

Product Family**Part Numbers:**

Item Number	Stainless Steel	Dark Gray	Almond	Black	Ivory	Elec. White
1-Port w/ ID Windows Single-gang	AX104230	-	AX103922	AX104160	-	AX102660
2-Port w/ ID Windows Single-gang	AX104231	-	AX103923	AX104161	AX104197	AX102655
4-Port w/ ID Windows Single-gang	AX104232	AX104464	AX102248	AX104163	AX104198	AX102249
6-Port w/ ID Windows Single-gang	AX104233	-	AX102250	AX104164	AX104199	AX102251
12-Port w/ ID Windows Double-gang	AX104234	-	AX102256	AX104166	AX104200	AX102257
1-Port Single-gang	AX102006	-	-	-	-	-
2-Port Single-gang	AX102007	-	-	-	-	-
4-Port Single-gang	AX102009	-	-	-	-	-
6-Port Single-gang	AX102010	-	-	-	-	-
12-Port Double-gang	AX102013	-	-	-	-	-
Wall Mount Phone Plates	AX102005	-	-	-	-	AX102902
Single-gang Back Box 1.89 in.	-	-	AX104127	-	-	AX102657
Double-gang Back Box 1.89 in.	-	-	AX104130	-	-	AX104131

Related Documents:

No related documents are available for this product

Put Ups and Colors:

Item #	Putup	Ship Weight	Color	Notes	Item Desc
AX102256	1 EA	0.111 LB			KCONN FACEPLATE 12-PORT DG ALM

Revision Number: 1 Revision Date: 02-25-2010

© 2012 Belden, Inc
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with EU RoHS (Directive 2002/95/EC, 27-Jan-2003). Material manufactured prior to the compliance date may be in stock at Belden facilities and in our Distributor's inventory. The information provided in this Product Disclosure, and the identification of materials listed as reportable or restricted within the Product Disclosure, is correct to the best of Belden's knowledge, information, and belief at the date of its publication. The information provided in this Product Disclosure is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. This Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.