



## AX100068 Panels - FiberExpress Rack Mount Patch Panel 2U



For more Information  
please call

1-800-Belden1

### Description:

FiberExpress Patch Panel, Rack Mount, 2U, Black.

### Usage (Overall)

|                               |  |
|-------------------------------|--|
| <b>Suitable Applications:</b> | FiberExpress Solutions, Backbone, Telecommunications Room, Main Distribution Room                                      |
| <b>Related Parts:</b>         | FiberExpress Adapter Strips, Fiber Splice Organizer Trays and Kits, Offset Bracket Kit, Right Side Cable Entry Bracket |

### Physical Characteristics (Connectivity)

#### Capacity

|                       |  |
|-----------------------|--|
| <b>Max. Capacity:</b> | 4 Strips; 48 Fibers (SC, SCD, ST, FC); 96 Fibers (LCD, MT-RJ). Two 8-inch Splice Tray Kit (A0649869) |
|-----------------------|--|

#### Access

|                          |                 |
|--------------------------|-----------------|
| <b>Front Connection:</b> | Flush           |
| <b>Termination Area:</b> | Front Swing Out |

#### Dimensions

##### Dimensions:

| Height (in.) | Width (in.) | Depth (in.) |
|--------------|-------------|-------------|
| 3.450        | 19.000      | 12.000      |

#### Materials

##### Materials:

| Description | Material |
|-------------|----------|
| Panel       | Steel    |
| Cover       | Lexan    |

#### Color

|               |       |
|---------------|-------|
| <b>Color:</b> | Black |
|---------------|-------|

#### Weight

|                |         |
|----------------|---------|
| <b>Weight:</b> | 12 lbs. |
|----------------|---------|

#### Included Parts

|                        |   |
|------------------------|---|
| <b>Included Parts:</b> | 4 Screws (10x32); 20 Tie Wraps; Identification Label; 2 Velcro Straps; Caution Label; Admin Label; Receptacle |
|------------------------|---|

#### Packaging

|                   |   |
|-------------------|---|
| <b>Packaging:</b> | Individually packaged in a cardboard box. |
|-------------------|---|

### Mechanical Characteristics (Connectivity)

|                                     |                |
|-------------------------------------|----------------|
| <b>Storage Temperature Range:</b>   | -40°C To +70°C |
| <b>Operating Temperature Range:</b> | -10°C To +60°C |

### Applicable Specifications and Agency Compliance (Overall)

#### Suitability

|                              |     |
|------------------------------|-----|
| <b>Suitability - Indoor:</b> | Yes |
|------------------------------|-----|

### Notes (Overall)

**Notes:** For proper installation refer to Installation Guide PX100103 included with the product or visit our web site at <http://www.belden.com>

#### Product Family

##### Part Numbers:

## AX100068 Panels - FiberExpress Rack Mount Patch Panel 2U

| Description                         | Item Number |
|-------------------------------------|-------------|
| FiberExpress Rack Mount PP 1U Black | AX100041    |
| FiberExpress Rack Mount PP 2U Black | AX100068    |
| FiberExpress Rack Mount PP 3U Black | AX100077    |
| FiberExpress Rack Mount PP 4U Black | AX100116    |

### Related Documents:

No related documents are available for this product

### Put Ups and Colors:

| Item #   | Putup | Ship Weight | Color | Notes | Item Desc                      |
|----------|-------|-------------|-------|-------|--------------------------------|
| AX100068 | 1 EA  | 12.120 LB   |       |       | FIBEREXPRESS, RACK MOUNT BLACK |

Revision Number: 0    Revision Date: 05-31-2009

© 2012 Belden, Inc  
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.