

## AX101166 Cable Assemblies - FiberExpress Duplex Patch Cord



For more Information  
please call

1-800-Belden1

**Description:**

FiberExpress Duplex Patch Cord, MTRJ-female-ST, SPC-Polish, 3m (9ft 10in), Singlemode, OS2, SM

**Usage (Overall)**

**Suitable Applications:** Data Centers, Main Equipment Rooms, Telecommunications Rooms and Work Area

**Related Parts:** FiberExpress Adapter Strips, FiberExpress Manager Modules and FiberExpress Ultra Frames and Cassettes. Workstation Outlets

**Multi Conductor****Physical Characteristics****Overall Cabling**

**Overall Cabling Fillers:** Refer to cable Technical Specifications

**Overall Diameter**

**Overall Nominal Diameter:** 0.118 in.

**Physical Characteristics (Connectivity)****Fiber Type**

**Fiber Type:** SM, (OS2)

**Materials****Materials:**

Description	Type	Material	Color
Connector end 1	MTRJ Female	Plastic	Black
Boot end 1		Rubber	Black
Ferrule end 1	MT	Thermo-Plastic	Black
Connector end 2	ST	Metal	
Boot end 2		Rubber	White
Ferrule end 2	2.5mm	Zirconia-Ceramic	White
Jacket	3.0 mm Round	OFNR	Yellow

**Wiring Scheme**

**Wiring Scheme:** TIA/EIA 568-C.3

**Weight**

**Weight:** 0.148 lbs.

**Packaging**

**Packaging:** Individually packaged in a clear plastic bag.

**Mechanical Characteristics (Connectivity)**

**Storage Temperature Range:** -40°C To +75°C

**Operating Temperature Range:** -40°C To +75°C

**Applicable Specifications and Agency Compliance (Overall)****Applicable Standards & Environmental Programs**

**UL Rating:** Riser

**EU Directive 2002/95/EC (RoHS):** Yes

## AX101166 Cable Assemblies - FiberExpress Duplex Patch Cord

EU RoHS Compliance Date (mm/dd/yyyy):	01/01/2006
MII Order #39 (China RoHS):	EUP 50
Telecommunications Standards:	TIA 568.C.3
Safety Listing:	ACA, Bi-national (UL/CSA) Standard Listed

## Suitability

Suitability - Indoor:	Yes
-----------------------	-----

## Transmission Characteristics (Connectivity)

## Notes (Overall)

## Product Family

## Product List:

Description	Belden Part Number Multimode - OM1 - 62.5 µm	Belden Part Number Multimode - OM2 - 50 µm	Belden Part Number Multimode - OM3 - 50 µm	Single-mode - OS2
Duplex Patch Cord				
ST-ST - 2 m (6 ft.)	70102419	AX200341	AX200799	AX200090
ST-ST - 3 m (10 ft.)	70102420	AX200459	AX200795	AX200091
ST-ST - 5 m (16 ft.)	70102447	AX200413	AX200800	AX200092
568SC-568SC - 2 m (6 ft.)	AX200056	AX200084	AX200603	AX200094
568SC-568SC - 3 m (10 ft.)	AX200057	AX200082	AX200589	AX200095
568SC-568SC - 5 m (16 ft.)	AX200058	AX200280	AX200624	AX200096
LC duplex-LC duplex - 2 m (6 ft.)	AX200517	AX200527	AX200664	AX200507
LC duplex-LC duplex - 3 m (10 ft.)	AX200518	AX200528	AX200665	AX200508
LC duplex-LC duplex - 5 m (16 ft.)	AX200519	AX200529	AX200666	AX200509
MTRJ-MTRJ - 2 m (6 ft.)	AX101122	AX101139	AX200801	AX101157
MTRJ-MTRJ - 3 m (10 ft.)	AX101123	AX101138	AX200802	AX101156
MTRJ-MTRJ - 5 m (16 ft.)	AX101125	AX101137	AX200803	AX101155
Hybrid Patch Cord				
568SC-ST - 3 m (10 ft.)	AX200060	AX200196	AX200900	AX200421
LC duplex-ST - 3 m (10 ft.)	AX200699	AX200695	AX200809	AX200698
LC duplex-568SC - 3 m (10 ft.)	AX200580	AX200581	AX200668	AX200667
MTRJ-ST - 3 m (10 ft.)	AX101133	AX101151	AX200810	AX101166
MTRJ-568SC - 3 m (10 ft.)	AX101128	AX101143	AX200797	AX101161
Single-ended (pigtailed)				
ST-open - 2 m (6 ft.)	70100390	AX200458	AX200811	AX200097
SC-open - 2 m (6 ft.)	70101714	AX200192	AX200653	AX200098
LC-open - 2 m (6 ft.)	AX200657	AX200658	AX200660	AX200659
MTRJ(m)-open - 3 m (10 ft.)	AX101366	AX101367	AX200812	AX101368

## Related Documents:

No related documents are available for this product

## Put Ups and Colors:

Item #	Putup	Ship Weight	Color	Notes	Item Desc
AX101166	1 EA	0.148 LB			FOPC,R3.0,MTRJ(F)-ST/SPC

Revision Number: 0    Revision Date: 05-13-2009

© 2012 Belden, Inc  
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express,

## AX101166 Cable Assemblies - FiberExpress Duplex Patch Cord

statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale. Belden believes this product to be in compliance with EU RoHS (Directive 2002/95/EC, 27-Jan-2003). Material manufactured prior to the compliance date may be in stock at Belden facilities and in our Distributor's inventory. The information provided in this Product Disclosure, and the identification of materials listed as reportable or restricted within the Product Disclosure, is correct to the best of Belden's knowledge, information, and belief at the date of its publication. The information provided in this Product Disclosure is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. This Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.