Ha-VIS eCon 7000

Ethernet Switch
Ha-VIS eCon 7050-A1

5-port Ethernet Switch with extended input voltage range
for use in harsh industrial environments

Unmanaged	IP 65 / IP 67	PROFINET comatible X	EtherNet/IP compatible X

Number of ports, Copper / Termination	5x 10/100Base-T(X) / Han® 3 A RJ45 (female)
Input voltage / Termination	24 / 48 V DC / Han® 4 A, male, for redundant power supply
Permissible range (min./max.)	12 V ... 60 V DC
Input current	approx. 110 mA (at 24 V DC)
Housing material	zinc die-cast
Dimensions (W x H x D)	45 x 120 x 87 mm
Weight	approx. 0,8 kg
Working temperature	-40 °C ... +70 °C
MTBF	1.150.000 h

Identification	Part number	Drawing	Dimensions in mm
Ha-VIS eCon 7050-A1 Ethernet Switch with 5 RJ45 ports	20 70 305 3923