Detailed Specifications & Technical Data

ENGLISH MEASUREMENT VERSION



AX102032 Panels - FiberExpress 1U Manager







For more Information please call

1-800-Belden1

Description:

FiberExpress Cable Management Accessory, 1U, Black.

Usage (Overall)

Suitable Applications: FiberExpress Solutions, Backbone, Telecommunications Room, Main

Distribution Room

Related Parts: FiberExpress Manager 1U Rack Mount Patch Panel

Physical Characteristics (Connectivity)

Capacity

Max. Capacity: Bracket opening of 1.6 in. X 2.7 in. (1U)

Dimensions

Dimensions:

Height (in.) Width (in.) Depth (in.) 1.720 | 17.200 | 5.810

Materials

Materials:

Description MaterialPanel Steel

Color

Color: Black

Included Parts

Included Parts: 2 Screws (10-32); 1 Instruction Sheet; 1 Administration Label; 1 PFFA Label; 2

Velcro Straps.

Packaging

Packaging: Individually packaged in a cardboard box.

Mechanical Characteristics (Connectivity)

Storage Temperature Range: -40°C To +70°C

Operating Temperature Range: -10°C To +60°C

Applicable Specifications and Agency Compliance (Overall)

Suitability

Suitability - Indoor: Yes

Transmission Characteristics (Connectivity)

Notes (Overall)

Notes: For proper installation refer to Installation Guide PX103404 included with the product or visit our web site at http://www.belden.com

Product Family

Related Documents:

No related documents are available for this product

Put Ups and Colors:

Item #	Putup	Ship Weight	Color	Notes	Item Desc
AX102032	1 EA	2.076 LB			FXM 1U RACK MOUNT PANEL

Page 1 of 2 01-06-2012

Detailed Specifications & Technical Data

ENGLISH MEASUREMENT VERSION



AX102032 Panels - FiberExpress 1U Manager

Revision Date: 03-30-2010 Revision Number: 0

© 2012 Belden, Inc All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.