

## XDR8419-310 Racks - Distribution Racks



For more Information  
please call

1-800-793-2954

**Description:**

Steel Knockdown - 2 Post, 84" Distribution Rack, #10-32 Tapped 3" Channel w/Angle Base.

**Image**

Image:

**Physical Characteristics (Encl-CM)****Color**

Color: Black

**Construction**

Construction: Knockdown 2 Post

**Dimensions****Dimensions:**

Height	Width	Rail Tapping
84 inches	19 inches	10-32

Rack Unit: 45U

**Load Capacity**

Weight/Lbs.: 1000

**Material**

Material: Steel

**Applicable Specifications and Agency Compliance (Overall)****Applicable Standards & Environmental Programs**

UL Listing: UL & c-UL Listed 60950-1

EU Directive 2002/95/EC (RoHS): Yes

EU RoHS Compliance Date (mm/dd/yyyy): 06/01/2006

**XDR8419-310 Racks - Distribution Racks****Related Documents:**

No related documents are available for this product

**Put Ups and Colors:**

Item #	Putup	Ship Weight	Color	Notes	Item Desc
XDR8419-310	1 EA	62.400 LB			84" DISTRIBUTION RACK 19" MTG

Revision Number: 0    Revision Date: 01-27-2010

© 2012 Belden, Inc.  
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with EU RoHS (Directive 2002/95/EC, 27-Jan-2003). Material manufactured prior to the compliance date may be in stock at Belden facilities and in our Distributor's inventory. The information provided in this Product Disclosure, and the identification of materials listed as reportable or restricted within the Product Disclosure, is correct to the best of Belden's knowledge, information, and belief at the date of its publication. The information provided in this Product Disclosure is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. This Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.