speco technologies®
simply unique

HD 720p Indoor Cube IP Camera

VIP2C1P 2.6mm fixed lens

VIP series

sold individually



Features:

- Supports HD 720p @ 30fps
- Built-in standard PoE (IEEE 802.3af)
- PIR sensor & illumination LED
- Supports H.264, MPEG4, and MJPEG codecs
- 2-way audio communication with built-in microphone and speaker
- Digital Deterrent®
- Micro SD card slot (card not included)
- ONVIF Profile S listed*
- 2 year warranty

Camera Specifications

Image Sensor	Progressive scan 1/4" CMOS
Maximum Resolution	1600x1200 @ 15fps or 1280x720 @ 30fps
Minimum Illumination	1 lux (LED off); 0 lux (LED on)
IR LEDs	N/A
IR Range	N/A
White Balance	Automatic, Incandescent, Fluorescent, Outdoor
Exposure Control	Yes
Digital Slow Shutter	Yes
WDR/BLC	N/A
Day/Night	N/A
DNR	2D

Video Specifications

Supported Resolutions	1600x1200 @ 15fps 1280x1024 / 1280x720 / 800x600 / 704x576 / 704x480 / 640x480 / 352x288 / 352x240 / 320x240 @ 30fps
Compression	H.264 (HP/MP/BP), MPEG4 (SP), MJPEG
Bitrate Control	VBR, CBR
Multiple Streaming	3 simultaneous profiles

Audio Specifications

Mono Input	64Kbps G.711
Mono Output	64Kbps G.711

External Terminal Specifications

Ethernet	10/100 Mbps
Alarm	N/A
Video	N/A
Audio	Built-in mic/speaker
Power	5VDC jack
Storage	Micro SD slot

Network Specifications

Protocols	IPv4, IPv6, TCP, UDP, ARP, RTCP, RTP, RTSP, HTTP, HTTPS, SMTP, FTP, DHCP, UPnP, QoS, Zeroconf, Bonjour

Network Specifications (continued)

DDNS Support	Speco DDNS (free of charge)
Security	User ID & Password protection, IP address filtering, HTTPS
User Access	10 simultaneous users Performance may vary depending on resolution and number of connections

System Specifications

PoE	Standard (IEEE 802.3af)
Analytics	Motion detection (8 regions)
Alarm Triggers	Motion, on boot, network loss, manual, PIR, audio detection
Alarm Events	FTP video file upload, email image upload, micro SD card recording, HTTP server, boost, Digital Deterrent®, light
Video Buffer	Configurable pre-record & post-record
Image Settings	Privacy mask

Client Specifications

Web Browser Support	Windows (Internet Explorer 8 and up, Chrome, Firefox)
Mobile Apps	Speco VIP (iOS®, Android™)
PC Application	Speco VMS, Secure Guard®

Operating & Unit Specifications

Power Supply	PoE, 5VDC (power supply included)
Power Consumption	PoE, 73mA / 5VDC, 600mA
Operating Temperature	32° F – 104° F
Operating Humidity	0% – 90% RH
Unit Dimensions	2.44" (W) x 3.81" (H) x 1.51" (D)
Unit Weight	2.64 oz.
Certifications	FCC, RoHS
Included in Package	Unit, CD (manual, software), power supply, mounting bracket, mounting screws

*visit www.specotech.com/onvif.html for latest ONVIF support

iPhone is a trademark of Apple Inc., registered in the U.S. and other countries. Android is a trademark of Google Inc.
Speco Technologies is constantly developing and improving products.
We reserve the right to modify product design and specifications without notice and without incurring any obligation.

Rev. 10/28/13

For more information contact Speco Technologies
200 New Highway, Amityville, NY 11701 • Toll Free: 1-800-645-5516 • Fax: 631-957-9142 or 631-957-3880
www.specotech.com