

BHVB012 Cable Management - Vertical Cable Manager


For more Information
please call

1-800-793-2954


Description:

Single Sided High Density Vertical Cable Manager with doors, 12"W x 84"H.

Image

Image:


Physical Characteristics (Encl-CM)
Dimensions

Dimensions:

Height	Depth	Width	Mounting/Style
84 inches	9.38 inches	12 inches	Vertical

Applicable Specifications and Agency Compliance (Overall)
Applicable Standards & Environmental Programs

EU Directive 2002/95/EC (RoHS): Yes

EU RoHS Compliance Date (mm/dd/yyyy): 06/01/2006

Notes (Overall)
Product Accessories

Product Accessories:

Description	12 inches Wide
Vertical Manager Backcover	BHBC12X
Vertical Manager Doors (1 pr)	BHDK12X
Gate Kit	BHGL12X
Retention Gate (6)	BHGR12X
Divider Bar	BHDB12X
Slack Management Spool Kit	BHSP020
Slack Management Spools (2), blk	BHSP020
Fastener for Vertical Mgr (100/bag)	BHPF100
Tie Mount for Vertical Mgr (100/bag)	BHSM100

BHVVH012 Cable Management - Vertical Cable Manager**Related Documents:**

No related documents are available for this product

Put Ups and Colors:

Item #	Putup	Ship Weight	Color	Notes	Item Desc
BHVVH012	1 EA	71.600 LB			SGL SIDE HD VERTMGR W/DR 12X84

Revision Number: 0 Revision Date: 12-23-2009

© 2012 Belden, Inc.
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with EU RoHS (Directive 2002/95/EC, 27-Jan-2003). Material manufactured prior to the compliance date may be in stock at Belden facilities and in our Distributor's inventory. The information provided in this Product Disclosure, and the identification of materials listed as reportable or restricted within the Product Disclosure, is correct to the best of Belden's knowledge, information, and belief at the date of its publication. The information provided in this Product Disclosure is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. This Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.