THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



TECHNICAL SPECIFICATIONS			
MAXIMUM LOSS		SINGLEMODE MAXIMUM LOSS	
3.5dB/KM @ 850nm 1.5dB/KM @ 1300nm		.75dB/KM @ 1310nm .75dB/KM @ 1500nm	
TENSILE LOAD - OFCR		TENSILE LOAD - OFCR-LS/OFCP	
INSTALLATION	LONG TERM	INSTALLATION	LONG TERM
1320 N (300 lbf)	330 N (741 lbf)	660 N (150 lbf)	165 N (38 lbf)

	OFCR	OFCR-LS/OFCP
OPERATION	-20° C TO +50° C (-4° F TO +122° F)	0° C TO +50° C (+32° F TO +122° F)
INSTALLATION		
STORAGE	-40° C TO +65° C (-40° F TO +149° F)	

NOTES:
1. DIAMETER DIMENSION, SHOWN FOR REFERENCE ONLY.
2. DIMENSIONS IN BRACKETS [ ] ARE ENGLISH.
3. ALL MATERIALS AND COMPONENTS USED MUST MEET THE MATERIAL RESTRICTIONS OF RoHS (EUROPEAN DIRECTIVE 2002/95/EC ON THE RESTRICTION OF HAZARDOUS SUBSTANCES) AS PROPOSED BY THE RoHS TECHNICAL ADAPTATION COMMITEE.

REV	DATE	BY	CHK	DESCRIPTION	ECN - R	CUST	SUP	OTH
02	10-26-09	EFK		RELEASED TO PRODUCTION	02055-99			

OPTI-CORE 48 FIBER ARMORED DISTRIBUTION CABLE
WITH 4 SUB-UNITS OF 12 FIBERS
CUSTOMER DRAWING

PANDUIT™ CORP.
TINLEY PARK, ILL 60477

THIRD ANGLE PROJECTION

ALL DIMENSIONS ARE GIVEN IN INCHES, UNLESS OTHERWISE SPECIFIED.
DIMENSIONAL TOLERANCES ARE:
(.X) (.XXX) ±0.3 [.010]
(.XX) ±0.8 [.03] ANGLES

DRAWN BY: MC
DATE: 06-03-05
CHK'D: WMA
REVIEW DRAWING NUMBERS

DRAWING FILENAME: M02055BX_DC_48/01A
SCALE: NONE
PART NO. FSP**48Y FOP**48Y
DRAWING NO. 02055-99
SHEET 1 OF 2
SIZE A

THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

PANDUIT PART NUMBER	FIBER TYPE	JACKET RATING	DIAMETER	BEND RADIUS	
				INSTALLED	LONG TERM
FSPR948Y	SINGLEMODE 9/125uM	OFCR	22.1mm [0.870"]	53.0cm [20.9"]	26.5cm [10.4"]
FSPP948Y		OFCP			
FSPL948Y		OFCR-LS			
FSPR548Y	MULTIMODE 50/125uM	OFCR	22.1mm [0.870"]		
FSPP548Y		OFCP			
FSPL548Y		OFCR-LS			
FSPR648Y	MULTIMODE 62.5/125uM	OFCR	22.1mm [0.870"]		
FSPP648Y		OFCP			
FSPL648Y		OFCR-LS			
FOPRX48Y	MULTIMODE 50/125uM OM3	OFCR	22.1mm [0.870"]		
FOPPX48Y		OFCP			
FOPLX48Y		OFCR-LS			
FOPRZ48Y	MULTIMODE 50/125uM OM4	OFCR	22.1mm [0.870"]		
FOPPZ48Y		OFCP			

REV	DATE	BY	CHK	DESCRIPTION	ECN - R	CUST	SUP	OTH
02	10-26-09	EFK		RELEASED TO PRODUCTION	02055-98			

OPTI-CORE 48 FIBER ARMORED DISTRIBUTION CABLE
WITH 4 SUB-UNITS OF 12 FIBERS
CUSTOMER DRAWING

PANDUIT™ CORP.
TINLEY PARK, ILL 60477

THIRD ANGLE PROJECTION

ALL DIMENSIONS ARE GIVEN IN INCHES, UNLESS OTHERWISE SPECIFIED.
DIMENSIONAL TOLERANCES ARE:
(.X) (.XXX) ±0.3 [.010]
(.XX) ±0.8 [.03] ANGLES

DRAWN BY: MC
DATE: 06-03-05
CHK'D: WMA

REVIEW DRAWING NUMBERS

DRAWING FILENAME: M02055BX_DC_48/01A
SCALE: NONE
PART NO. FSP**48Y FOP**48Y
DRAWING NO. 02055-99
SHEET 2 OF 2
SIZE A